


M57726R


144-148MHz, 12.5V, 43W, FM MOBILE RADIO

OUTLINE DRAWING

Dimensions in mm



BLOCK DIAGRAM



PIN :

- ①Po : RF OUTPUT
- ②Vcc2 : 2nd. DC SUPPLY
- ③Vcc1 : 1st. DC SUPPLY
- ④Pin : RF INPUT
- ⑤GND : FIN

ABSOLUTE MAXIMUM RATINGS (T_c = 25 °C unless otherwise noted)

Symbol	Parameter	Conditions	Ratings	Unit
V _{cc}	Supply voltage		17	V
I _{cc}	Total current		14	A
P _{in(max)}	Input power	Z _G = Z _L = 50 Ω	0.6	W
P _{o(max)}	Output power	Z _G = Z _L = 50 Ω	55	W
T _{c(OP)}	Operation case temperature		- 30 to 110	°C
T _{stg}	Storage temperature		- 40 to 110	°C

Note. Above parameters are guaranteed independently.

ELECTRICAL CHARACTERISTICS (T_c = 25 °C unless otherwise noted)

Symbol	Parameter	Test conditions	Limits		Unit
			Min	Max	
f	Frequency range	P _{in} = 0.3W V _{cc} = 12.5V Z _G = Z _L = 50 Ω	144	148	MHz
P _o	Output power		43		W
η _T	Total efficiency		50		%
2f _o	2nd. harmonic			- 35	dBc
3f _o	3rd. harmonic			- 45	dBc
ρ _{in}	Input VSWR			2.8	-
-	Load VSWR tolerance	V _{cc} = 15.2V, P _o = 45W (P _{in} : controlled) Load VSWR=20:1 (All phase), 5sec. Z _G = 50Ω	No degradation or destroy		-

Note. Above parameters, ratings, limits and conditions are subject to change.