



LOC	DIST	REVISIONS				
G	14	P	LTR	DESCRIPTION	DATE	OWN
						APVD
			N2	REVISED PER ECO-11-004820	11MAR11	RK



AMP WIRE RANGE	Listed FILE E13288
6 AWG SOLID OR STRANDED	6 AWG STRANDED
LR7189 Certified	MILITARY P/N AND CLASS
6 AWG SOLID OR STRANDED	MS 20659-131 CLASS 2 P/N 33466 & 2-33466-3 ONLY

- 1 STAMP AMP 6* APPROX AS SHOWN
- 2 0.00254 [.000100] MIN TIN PLATE PER ASTM B-545.
- 3 GOLD PLATE 0.00127 [.000050] MIN THK PER ASTM B-488, TYPE 2, GRADE C OVER NICKEL PLATE 0.00076 [.000030] MIN THK PER QQ-N-290.
- 4 SUPERSEDED BY 8-33466-3
- 5 COPPER PER ASTM B-152, ANNEALED

OBSOLETE	2	25	LOOSE PIECE, BAG	8-33466-5
	2	25	LOOSE PIECE, BOX	8-33466-3
	2	500	LOOSE PIECE, BOX	2-33466-4
	2	750	33466 ON TAPE	2-33466-3
	3	----	LOOSE PIECE	2-33466-1
	2	----	LOOSE PIECE	33466
FINISH		QTY	PACKAGE TYPE	PART NO

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 170°C
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: N/A
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	CIRCULAR MIL AREA: 10.5-16.8mm² [20,800-33,100] SOLID OR STRANDED
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TA BRINKMAN 3-24-93	TE Connectivity	
		CHK DA PATTERSON 3-24-93		
		APVD JL MECKLEY 3-24-93		
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	PRODUCT SPEC	NAME TERMINAL, RING TONGUE, SOLISTRAND	
	0 PLC ± -	APPLICATION SPEC	SIZE A2	
	1 PLC ± -		CAGE CODE 00779	
	2 PLC ± -		DRAWING NO G-33466	
	3 PLC ± -		RESTRICTED TO -	
MATERIAL - 5	4 PLC ± -		WEIGHT -	
	ANGLES FINISH		CUSTOMER DRAWING	
SEE TABLE			SCALE 4:1	SHEET 1 of 1
			REV N2	