



LOC —	DIST —	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			A	Obsolescence of P/N 826539-6	24JULY2013	SMT	RP

POLZ.	L±0.5	BESTELL-NR.
1	3.3	826 539-1
2	7.3	-2
3	11.3	-3
4	15.2	-4
5	19.2	-5
6	23.1	-6
7	27.1	-7
8	31.1	-8
9	35.1	-9
10	39.0	1-
11	43.0	1-
12	46.9	1-
13	50.9	1-
14	54.8	1-
15	58.8	1-
16	62.8	1-
17	66.7	1-
18	70.7	1-
19	74.7	1-
20	78.6	2-
21	82.6	2-
22	86.5	2-
23	90.5	2-
24	94.4	2-
25	98.4	2-
26	102.4	2-
27	106.3	2-
28	110.3	2-
29	114.2	2-
30	118.2	2-
31	122.2	3-
32	126.1	2-
33	130.1	2-
34	134.0	3-
35	138.0	3-
36	141.6	2- 826 539-6

ZEICHNUNG GÜLTIG AB 20/90



BOHRBILD



- 1 STECKSEITE: IM BEREICH "F" 0.8 μm GOLD ÜBER 1.27 μm NICKEL IM BEREICH "B"
- 2 LÖTSEITE: MIN. 2.5 μm ZINN ÜBER 1.27 μm NICKEL
- 3 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- OBSOLETE

KONTAKTSTIFT	Cu Sn	1
STIFTGEHÄUSE	PBT-GV	GRÜN
BENENNUNG	WERKSTOFF	OBERFLÄCHE FARBE

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

By -


COPYRIGHT -

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.3mm

0 PLC	± -
1 PLC	± -
2 PLC	± -
3 PLC	± -
4 PLC	± -
ANGLES	± -



DWN 23.11.84 AUGUSTINIAK

CHK 24.01.85 SCHAARSCHMIDT

APVD -

PRODUCT SPEC -

APPLICATION SPEC -

WEIGHT -

MATERIAL -

FINISH -



TE Connectivity

NAME

AMPMODU I STIFTL. RASTER 3.96
EINREIHIG

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A4

00779

C-826539

-

CUSTOMER DRAWING

SCALE

4:1

SHEET

1 OF 1

REV A