



© 1967 BY AMP INCORPORATED. ALL RIGHTS RESERVED. AMP PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING.

REVISIONS				
ZONE	LTR	DESCRIPTION	DATE	APPROVED
	R	REV. PER E.C.N. OF 0378	5-6-85	CT
	S	REV. OF 0301	7-88	
		0000-2117-94		ABM



INDICATES WIRE RANGE OF 20, 22 & 24 AWG.
WIRE RANGE: 20, 22, & 24 AWG.
INSULATION RANGE: .062 MAX.
HAND TOOL: AMP # 90260-1.
EXTRACTION TOOL: AMP # 91038-3.
INSERTION TOOL: AMP # 91042-1.

- 203802-1 1. AS SHOWN:
2. STRIP PART
3. BODY - BRASS, .000030 AU/.00005 NI.
1. SLEEVE, STAINLESS STEEL
-2 1. SAME AS -1, EXCEPT:
2. BODY, SELECTIVE .000030 AU/.000050 NI.
-3 1. SAME AS -1, EXCEPT:
2. LOOSE PIECE PART
-4 1. SAME AS -2, EXCEPT:
2. LOOSE PIECE PART
OBSOLETE AS -1, EXCEPT:
2. BODY, TIN PLATED (A) (K)
-6 1. SAME AS -5, EXCEPT:
2. LOOSE PIECE PART (A) (K)

- 203802-7 OBSOLETE EXCEPT:
-8 OBSOLETE EXCEPT:
OBSOLETE 1. SAME AS -5 EXCEPT:
2. REVERSE REELED FOR STANDARD APPLICATOR. (A) (K)
OBSOLETE 1. SAME AS -2 EXCEPT:
2. REVERSE REELED FOR STANDARD APPLICATOR.
OBSOLETE 1. SAME AS -3 EXCEPT:
2. CUSTOMER PART NO. TO BE MARKED ON INNERMOST PACKAGE.
OBSOLETE 1. SAME AS -1 EXCEPT:
2. CUSTOMER PART NO. TO BE MARKED ON INNERMOST PACKAGE.

UNLESS OTHERWISE SPECIFIED DIM. ARE IN INCHES. TOLERANCES ON: DECIMALS ± .005 ANGLES ± °		CONTRACT NO.		AMP INCORPORATED HARRISBURG, PENNSYLVANIA	
MATERIAL SEE CALLOUT		DR 5-9-67	CHK 10/14/67	NAME CONTACT ASSY-SOCKET	
OTHER APPD		APPD 12-15-67	DSGN APPD	SIZE 20 (20-24 GA)	
AMP INFO		OTHER APPD	FINISH SEE LAST NO.	SIZE B	CODE IDENT NO. 00779
HEAT TREAT		SCALE H	WT CALC ACTUAL	NUMBER 203802	
SHEET		CUSTOMER DRAWING			