






REV.	DATE	DESCRIPTION
A	02/24/03	UPDATE DRAWING FORMAT



RECOMMENDED
CABLE STRIPPING DIM'S



- NOTE:
1. CRIMPED FERRULE
HEX CRIMP SIZE .429"
 2. CRIMPED CONTACT PL
HEX CRIMP SIZE .100"

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.	APPROVALS	DATE	Amphenol Connex N CRIMP PLUG (FOR RG-8/U, 213/U, 393/U CABLE) 172102			
						DRAWN	G.R.S.				
8					UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 - 8mm ± 0.20mm 8 - 30mm ± 0.40mm 30 - 120mm ± 0.50mm						
7					UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 - .315 = ± 0.007" .315 - 1.180 = ± 0.015" 1.180 - 4.724 = ± 0.020"						
6	FERRULE	COPPER	NEXCOTE	1	PART DESCRIPTION	CHECKED					
5	CONTACT PIN	BRASS	GOLD	1		ISSUED					
4	RETAINER RING	SUS 304	NATURAL	1	PART NO.	SHEET	1 OF 1				
3	GASKET	SILICONE	RED	1							
2	INSULATOR	TEFLON	NATURAL	1	DWG. NO.	172102					
1	SHELL/BODY	BRASS	NEXCOTE	1		172102.DWG					
	DESCRIPTION	MATERIAL	FINISH	QTY	CAD FILE	REV.	SIZE	SCALE			
					C:/172/172102.DWG	A	A	NA			