




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AJ	16		F	REVISED PER EC OS14-0499-04	11JULY05	BM	JL



SUGGESTED PCB CONFIGURATION

- 1 BERYLLIUM COPPER PER ASTM-B-197.
- 2 BRASS PER QQ-B-626.
- 3 ZINC PER QQ-Z-363.
- 4 PTFE PER MIL-P-19468.
- 5 SILVER PLATE PER QQ-S-365
2.54μm [.000100] MINIMUM THICK.
- 6 TIN PLATE PER ASTM-B-545
2.54μm [.000100] MINIMUM THICK.
- 7 NICKEL PLATE PER QQ-N-290
3.81μm [.000150] MINIMUM THICK.
- 8. SEE INSTRUCTION SHEET 408-9889.

413986-1
PART
NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. LIPPERT	10-15-90	tyco Electronics Tyco Electronics Corporation Harrisburg, Pa 17105-3608				
DIMENSIONS: INCHES		CHK R.E.RUTH	10-25-90	NAME JACK, 75 OHM, VERTICAL, PCB, BNC				
		APVD A. GABNY	10-25-90					
		PRODUCT SPEC 108-12078						
		APPLICATION SPEC —		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
MATERIAL SEE NOTES 1 THRU 4		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± 0.20 [.008] 3 PLC ± — 4 PLC ± — ANGLES ± — FINISH		WEIGHT —	A2	00779	C=413986	—
		CUSTOMER DRAWING				SCALE 5:1	SHEET 1 OF 1	REV F