

MATERIALS AND FINISHES






BODY, NUT, LOCKWASHER SEE TABLE

CENTER CONTACT BERYLLIUM COPPER
PLATED GOLD

CRIMP TUBE BRASS
PLATED NICKEL

INSULATOR TEFLON

SHRINK TUBE VERSAFIT OR EQUIVALENT




INSULATOR


73251-0102	73251-0100 BY TRAY (20 CAV.)
PART NO.	PACKAGING

ES-89675-1550	CABLE ASSY INSTR
PS-89675-1160	ELECTRO/MECH PERFORM
MIL-STD-348A, FIG. 310.2	INTERFACE
SPECIFICATION	DESCRIPTION


CHG: ADD CABLE TYPE TO TITLE	EC NO: URF2008-0601	2008/05/22	DRWN: JWIENER	2008/05/22	CHKD: SSHAH	2008/05/22	APPR: JWIENER	2008/05/22	DESCRIPTION
A5	REV								



INSULATOR



SHRINK TUBE



RECOMMENDED MOUNTING HOLE

73251-0101	BRASS	NICKEL	PH BRONZE	NICKEL
73251-0100	ST STEEL	PASSIVATED	ST STEEL	PASSIVATED
PART NO.	MATERIAL	PLATING	MATERIAL	PLATING
	BODY/NUT		LOCK WASHER	

QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)	DIMENSION STYLE MM/IN	SCALE	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION
▽=0	4 PLACES ± --- ± ---	DRAWN BY GMH DATE 1997/11/07	TITLE		
▽=0	3 PLACES ± --- ± ---	CHECKED BY DATE	SMA JACK BLKHD STR CLAMP		
	2 PLACES ± --- ± ---	DHG 1997/11/07	RG58/RG141 50 OHMS		
	1 PLACE ± --- ± ---	APPROVED BY GMH DATE 1997/11/07	SMA-JC		
	ANGULAR ± 2 °	MATERIAL NO.	MOLEX INCORPORATED		
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	SEE TABLE	SD-73251-010		
		SIZE C	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		

