

NAME: H+ DATE: 10.1.79

THIS INFORMATION IS CONFIDENTIAL AND IS DISCLOSED TO YOU ON CONDITION THAT NO FURTHER DISCLOSURE IS MADE BY YOU TO OTHER THAN AMP PERSONNEL WITHOUT WRITTEN AUTHORIZATION FROM AMP INCORPORATED, HARRISBURG, PA.

WAS 78-9833

NOTE

- 1 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- 2 OBSOLETE

DRAWING VALID FROM
ZEICHNUNG GÜLTIG AB

		H1	ECO-10-000445	AEG	12JAN10		
P	F	LTR	REVISION RECORD	APP	DATE		

H	REV. PER ECN 8809	Q.40	15.2.83
	WIN NO. 8-327949-2		
	WAS 1-926 009-3		
G	REV. PER ECN 8809	Q.40	22.9.83
	WIN NO. 8-327 949-2		
	WAS 1-926 009-3		
F	REV. PER ECN 8847	Q.40	22.9.83
E	REV. PER ECN 8539	Q.40	11.12.83
D	REV. PER ECN 8197	Q.40	5.7.83
C	REV. PER ECN 3641	Q.40	26.9.83
B	REV. PER ECN 3153	Q.40	11.9.83
A	REV. PER ECN 3090	Q.40	26.9.83
P	REVISION RECORD	APP	DATE

DWG SIZE		PART NO		DESCRIPTION		ITEM NO	
← REVISION OF EACH ASSY NO (WHICH BLANK) ← DWG REVISION							
QTY REQD PER ASSY		PARTS LIST					
DIMENSIONS IN INCHES. TOLERANCES UNLESS OTHERWISE SPECIFIED:		MATERIAL		HEAT TREAT		FINISH	
2 PL DEC ±		DR 9.179 1/4"		APP REL		 AMP DEUTSCHLAND GmbH Langer, b. l. m.	
3 PL DEC ± .006 (±0.15)		CHK 73.279 1/4"					
4 PL DEC ±							
ANGLES ±		NAME AMP MODU II PIN HEADER					
SURF TEXTURE: ✓		SCALE		DWG NO 826 634		SHEET REV	
REMOVE BURRS, BREAK SHARP EDGES .015R MAX		C				H1	