



Panel Cutout



Cinch Connectivity Solutions
7-13 Russel Way,
Widford Industrial Estate,
Chelmsford, Essex,
CM1 3AA, UK.
Tel: +44 (0) 1245 359515
Fax: +44 (0) 1245 358938

SCALE: Not To Scale

DIMENSIONS: mm

TOLERANCES:
± 0.2mm unless
otherwise stated

DRAWN BY:

CHECKED BY:

APPROVED BY:

DATE: 20 Sept 05

M Terry

M Terry

A Herbert

TITLE:

F Panel Mount Jack (rear
entry)

PART NUMBER:

VF311

PAGE: 1 of 1

Electrical Characteristics

Nominal Impedance: 75 ohms
Frequency Range: DC to 2 GHz

Mechanical Characteristics

Mating Cycles: 200 cycles minimum

Environmental Characteristics

Temperature Range: -55 °C to +85 °C

PART	DESCRIPTION
1	Body Brass, nickel plated
2	Dielectric Polypropylene
3	Contact Phosphor Bronze, tin plated
4	Washer Steel, nickel plated
5	Nut Steel, nickel plated

Panel cutout: PCD-7

Update on Item-4	JT	3	03 June 10
CAD Issue	MT	2	20 Sept 05
First Issue	MT	1	20 Sept 05
DESCRIPTION OF REVISION			APPVD ISS DATE