






CIRCUIT: SPST

NOTES:

1. ALL DIMENSIONS IN MM [INCH]
 $x.x = \pm 0.4$
 $x.xx = \pm 0.25$
2. TERMINAL NUMBERS FOR REF. ONLY
3. CONTACT MATERIAL: SILVER
4. CONTACT RATING: 20mA; 15VDC
5. TRAVEL: 0.15 $\pm$ 0.1mm
- ▲ 6. OPERATING FORCE: 160 $\pm$ 50 GRAMS
7. ELECTRICAL LIFE: 100,000 CYCLES
8. CONTACT RESISTANCE: 500m Ω MAX.
9. ▲ DENOTES CRITICAL PARAMETER
10. BOUNCE: 10m SECONDS MAX
11. INSULATION RESISTANCE: 100M Ω MIN.
12. DIELECTRIC STRENGTH: 250VAC FOR 1 MINUTE WITH NO BREAK DOWN
13. 2002/95/EC (ROHS) COMPLIANT; HALOGEN FREE
14. PACKAGING: TAPE & REEL, 8000 PARTS PER REEL.



D	21339	Revised housing	12/30/13	rc
C	20937	Update to new Actuator	12/21/12	rc
B	19700	UPDATE RATING	02/22/11	BMA
A	19549	New Release	12/27/10	rc
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED



TITLE TL3700AF160QG

SCALE 10:1

DATE 12/20/2010

DR rc

DWG P003000

REV D