


Technical drawing of a rectangular box. The drawing shows a perspective view of the box with dashed lines indicating the internal structure. The dimensions are labeled on the left: 1.24 (height) and 31.51 (width).

1.24  
[ 31.5 ]




- ADHESIVE TAPE: PRESSURE SENSITIVE FOAM 0.04 [1.0] THICK WITH RUBBER ADHESIVE AND PROTECTIVE LINER. MOUNT IS DESIGNED TO SUPPORT 0.91 lbs. [411g] MAXIMUM WEIGHT ON A CLEAN, DRY, SMOOTH, AND GREASE-FREE SURFACE.

PANDUIT PART NO. *	WEIGHT LBS / 100 [ G ] / PCS.
BEC38-A	0.95 [ 430 ]
BEC38-AT	0.95 [ 430 ]


NO WARRANTY, EXPRESSED OR IMPLIED, IS MADE BY PANDUIT WITH RESPECT TO ADHESIVE BOND PERFORMANCE. AMONG OTHER THINGS, THE CONDITIONS UNDER WHICH THESE MOUNTS MAY BE APPLIED AND/OR THE SURFACE TO WHICH THEY MAY BE APPLIED ARE BEYOND PANDUIT'S CONTROL.

NOTES:

- \* 1. SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND PART COLOR.
2. TO APPLY MOUNT: a) REMOVE PROTECTIVE LINER:  
b) PLACE IN DESIRED LOCATION: c) APPLY PRESSURE TO TOP OF MOUNT.



**SCALE: FULL**

DIMENSIONS IN BRACKETS ARE METRIC [ mm ]			
CAD FILENAME/LAYERS G00239CG_PB_BEC38_00			
		TINLEY PARK, ILLINOIS	
BEC38 BEVEL ENTRY CLIP			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: ( .X ) ± N/A    ( .XXX ) ± N/A ( .XX ) ± .020 ( .5 ) ANGLES ± N/A		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
DRAWN BY GDH	MAT'L:  6/6 NYLON	SCALE 1 1/2 X	DRAWING NO. GB0239CG
DATE 11-30-94			DWG A SIZE
CHK'D			