

PHB108NQ03LT

N-channel TrenchMOS logic level FET

Rev. 04 — 2 February 2009

Product data sheet

1. Product profile

1.1 General description

Logic level N-channel enhancement mode Field-Effect Transistor (FET) in a plastic package using TrenchMOS technology. This product is designed and qualified for use in computing, communications, consumer and industrial applications only.

1.2 Features and benefits

- Low conduction losses due to low on-state resistance
- Simple gate drive required due to low gate charge
- Suitable for logic level gate drive sources

1.3 Applications

- DC-to-DC convertors
- Switched-mode power supplies



1.4 Quick reference data

Table 1. Quick reference

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
V_{DS}	drain-source voltage	$T_j \geq 25\text{ °C}$; $T_j \leq 175\text{ °C}$	-	-	25	V
I_D	drain current	$T_{mb} = 25\text{ °C}$; $V_{GS} = 5\text{ V}$; see Figure 1 ; see Figure 3	-	-	75	A
P_{tot}	total power dissipation	$T_{mb} = 25\text{ °C}$; see Figure 2	-	-	187	W
Dynamic characteristics						
Q_{GD}	gate-drain charge	$V_{GS} = 4.5\text{ V}$; $I_D = 25\text{ A}$; $V_{DS} = 12\text{ V}$; $T_j = 25\text{ °C}$; see Figure 12 ; see Figure 13	-	5.6	-	nC
Static characteristics						
$R_{DS(on)}$	drain-source on-state resistance	$V_{GS} = 10\text{ V}$; $I_D = 25\text{ A}$; $T_j = 25\text{ °C}$; see Figure 10 ; see Figure 11	-	5.3	6	mΩ

2. Pinning information

Table 2. Pinning information

Pin	Symbol	Description	Simplified outline	Graphic symbol
1	G	gate	 SOT404 (D2PAK)	 <i>mbb076</i>
2	D	drain [1]		
3	S	source		
mb	D	mounting base; connected to drain		

[1] It is not possible to make a connection to pin 2

3. Ordering information

Table 3. Ordering information


Type number	Package		Version
	Name	Description	
PHB108NQ03LT	D2PAK	plastic single-ended surface-mounted package (D2PAK); 3 leads (one lead cropped)	SOT404

4. Limiting values

Table 4. Limiting values


In accordance with the Absolute Maximum Rating System (IEC 60134).

Symbol	Parameter	Conditions	Min	Max	Unit
V_{DS}	drain-source voltage	$T_j \geq 25\text{ }^{\circ}\text{C}$; $T_j \leq 175\text{ }^{\circ}\text{C}$	-	25	V
V_{DGR}	drain-gate voltage	$T_j \geq 25\text{ }^{\circ}\text{C}$; $T_j \leq 175\text{ }^{\circ}\text{C}$; $R_{GS} = 20\text{ k}\Omega$	-	25	V
V_{GS}	gate-source voltage		-20	20	V
I_D	drain current	$V_{GS} = 5\text{ V}$; $T_{mb} = 25\text{ }^{\circ}\text{C}$; see Figure 1 ; see Figure 3	-	75	A
		$V_{GS} = 5\text{ V}$; $T_{mb} = 100\text{ }^{\circ}\text{C}$; see Figure 1	-	75	A
I_{DM}	peak drain current	$t_p \leq 10\text{ }\mu\text{s}$; pulsed; $T_{mb} = 25\text{ }^{\circ}\text{C}$; see Figure 3	-	240	A
P_{tot}	total power dissipation	$T_{mb} = 25\text{ }^{\circ}\text{C}$; see Figure 2	-	187	W
T_{stg}	storage temperature		-55	175	$^{\circ}\text{C}$
T_j	junction temperature		-55	175	$^{\circ}\text{C}$
Source-drain diode					
I_S	source current	$T_{mb} = 25\text{ }^{\circ}\text{C}$	-	75	A
I_{SM}	peak source current	$t_p \leq 10\text{ }\mu\text{s}$; pulsed; $T_{mb} = 25\text{ }^{\circ}\text{C}$	-	240	A
Avalanche ruggedness					
$E_{DS(AL)S}$	non-repetitive drain-source avalanche energy	$V_{GS} = 10\text{ V}$; $T_{j(\text{init})} = 25\text{ }^{\circ}\text{C}$; $I_D = 43\text{ A}$; $V_{sup} \leq 25\text{ V}$; unclamped; $t_p = 0.25\text{ ms}$; $R_{GS} = 50\text{ }\Omega$	-	180	mJ




$$I_{der} = \frac{I_D}{I_{D(25^\circ\text{C})}} \times 100\%$$

Fig 1. Normalized continuous drain current as a function of mounting base temperature



$$P_{der} = \frac{P_{tot}}{P_{tot(25^\circ\text{C})}} \times 100\%$$

Fig 2. Normalized total power dissipation as a function of mounting base temperature



$$T_{mb} = 25^\circ\text{C}; I_{DM} \text{ is single pulse}; V_{GS} = 5\text{V}$$

Fig 3. Safe operating area; continuous and peak drain currents as a function of drain-source voltage

5. Thermal characteristics

Table 5. Thermal characteristics

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
$R_{th(j-a)}$	thermal resistance from junction to ambient	vertical in still air; mounted on a printed-circuit board; minimum footprint	-	50	-	K/W
$R_{th(j-mb)}$	thermal resistance from junction to mounting base	see Figure 4	-	-	0.8	K/W




Fig 4. Transient thermal impedance from junction to mounting base as a function of pulse duration

6. Characteristics

Table 6. Characteristics

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
Static characteristics						
$V_{(BR)DSS}$	drain-source breakdown voltage	$I_D = 250\ \mu A$; $V_{GS} = 0\ V$; $T_j = -55\ ^\circ C$	22	-	-	V
		$I_D = 250\ \mu A$; $V_{GS} = 0\ V$; $T_j = 25\ ^\circ C$	25	-	-	V
$V_{GS(th)}$	gate-source threshold voltage	$I_D = 1\ mA$; $V_{DS} = V_{GS}$; $T_j = 175\ ^\circ C$; see Figure 8 ; see Figure 9	0.5	-	-	V
		$I_D = 1\ mA$; $V_{DS} = V_{GS}$; $T_j = -55\ ^\circ C$; see Figure 8 ; see Figure 9	-	-	2.2	V
		$I_D = 1\ mA$; $V_{DS} = V_{GS}$; $T_j = 25\ ^\circ C$; see Figure 8 ; see Figure 9	1	1.5	2	V
I_{DSS}	drain leakage current	$V_{DS} = 25\ V$; $V_{GS} = 0\ V$; $T_j = 175\ ^\circ C$	-	-	500	μA
		$V_{DS} = 25\ V$; $V_{GS} = 0\ V$; $T_j = 25\ ^\circ C$	-	-	1	μA
I_{GSS}	gate leakage current	$V_{GS} = 10\ V$; $V_{DS} = 0\ V$; $T_j = 25\ ^\circ C$	-	0.02	100	nA
		$V_{GS} = -10\ V$; $V_{DS} = 0\ V$; $T_j = 25\ ^\circ C$	-	0.02	100	nA
$R_{DS(on)}$	drain-source on-state resistance	$V_{GS} = 5\ V$; $I_D = 25\ A$; $T_j = 175\ ^\circ C$; see Figure 10 ; see Figure 11	-	12.1	13.5	m Ω
		$V_{GS} = 10\ V$; $I_D = 25\ A$; $T_j = 25\ ^\circ C$; see Figure 10 ; see Figure 11	-	5.3	6	m Ω
		$V_{GS} = 5\ V$; $I_D = 25\ A$; $T_j = 25\ ^\circ C$; see Figure 10 ; see Figure 11	-	6.7	7.5	m Ω
R_G	internal gate resistance (AC)	$f = 1\ MHz$; $T_j = 25\ ^\circ C$	-	1.2	-	Ω
Dynamic characteristics						
$Q_{G(tot)}$	total gate charge	$I_D = 25\ A$; $V_{DS} = 12\ V$; $V_{GS} = 4.5\ V$; $T_j = 25\ ^\circ C$; see Figure 12 ; see Figure 13	-	16.3	-	nC
		$I_D = 0\ A$; $V_{DS} = 0\ V$; $V_{GS} = 4.5\ V$; $T_j = 25\ ^\circ C$	-	12.5	-	nC
Q_{GS}	gate-source charge	$I_D = 25\ A$; $V_{DS} = 12\ V$; $V_{GS} = 4.5\ V$; $T_j = 25\ ^\circ C$; see Figure 12 ; see Figure 13	-	4	-	nC
Q_{GS1}	pre-threshold gate-source charge		-	2.5	-	nC
Q_{GS2}	post-threshold gate-source charge		-	1.5	-	nC
Q_{GD}	gate-drain charge		-	5.6	-	nC
$V_{GS(pl)}$	gate-source plateau voltage	$I_D = 25\ A$; $V_{DS} = 12\ V$; $T_j = 25\ ^\circ C$; see Figure 12 ; see Figure 13	-	2.4	-	V
C_{iss}	input capacitance	$V_{DS} = 12\ V$; $V_{GS} = 0\ V$; $f = 1\ MHz$; $T_j = 25\ ^\circ C$; see Figure 14	-	1375	-	pF
		$V_{DS} = 0\ V$; $V_{GS} = 0\ V$; $f = 1\ MHz$; $T_j = 25\ ^\circ C$	-	2120	-	pF
C_{oss}	output capacitance	$V_{DS} = 12\ V$; $V_{GS} = 0\ V$; $f = 1\ MHz$; $T_j = 25\ ^\circ C$; see Figure 14	-	640	-	pF
C_{rss}	reverse transfer capacitance		-	250	-	pF

Table 6. Characteristics ...continued

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
t _{d(on)}	turn-on delay time	V _{DS} = 12 V; R _L = 0.5 Ω; V _{GS} = 4.5 V; R _{G(ext)} = 5.6 Ω; T _j = 25 °C	-	15	-	ns
t _r	rise time		-	38	-	ns
t _{d(off)}	turn-off delay time		-	32	-	ns
t _f	fall time		-	25	-	ns
Source-drain diode						
V _{SD}	source-drain voltage	I _S = 25 A; V _{GS} = 0 V; T _j = 25 °C; see Figure 15	-	0.86	1.2	V
t _{rr}	reverse recovery time	I _S = 20 A; dI _S /dt = -100 A/μs; V _{GS} = 0 V;	-	34	-	ns
Q _r	recovered charge	V _{DS} = 25 V; T _j = 25 °C	-	21	-	nC




Fig 5. Output characteristics: drain current as a function of drain-source voltage; typical values




Fig 6. Transfer characteristics: drain current as a function of gate-source voltage; typical values




Fig 7. Input and reverse transfer capacitances as a function of gate-source voltage; typical values




Fig 8. Gate-source threshold voltage as a function of junction temperature




Fig 9. Sub-threshold drain current as a function of gate-source voltage






Fig 10. Drain-source on-state resistance as a function of drain current; typical values



$$a = \frac{R_{DSon}}{R_{DSon(25^{\circ}\text{C})}}$$

Fig 11. Normalized drain-source on-state resistance factor as a function of junction temperature



$$I_D = 25\text{ A}; V_{DS} = 12\text{ V and } 19\text{ V}$$

Fig 12. Gate-source voltage as a function of gate charge; typical values






Fig 13. Gate charge waveform definitions



$$V_{GS} = 0\text{ V}; f = 1\text{ MHz}$$

Fig 14. Input, output and reverse transfer capacitances as a function of drain-source voltage; typical values



$T_J = 25^\circ\text{C}$ and $175^\circ\text{C}; V_{GS} = 0\text{V}$

Fig 15. Source current as a function of source-drain voltage; typical values

7. Package outline

Plastic single-ended surface-mounted package (D2PAK); 3 leads (one lead cropped)

SOT404




Fig 16. Package outline SOT404 (D2PAK)

8. Revision history

Table 7. Revision history

Document ID	Release date	Data sheet status	Change notice	Supersedes
PHB108NQ03LT_4	20090202	Product data sheet	-	PHB_PHD_PHU108NQ03LT_3
Modifications:	• The format of this data sheet has been redesigned to comply with the new identity guidelines of NXP Semiconductors. • Legal texts have been adapted to the new company name where appropriate.			
PHB_PHD_PHU108NQ03LT_3 (9397 750 14707)	20050418	Product data sheet	2004070095	PHP_PHB_PHD108NQ03LT-02
PHP_PHB_PHD108NQ03LT-02 (9397 750 10159)	20020911	Product data	-	PHP_PHB_PHD108NQ03LT-01
PHP_PHB_PHD108NQ03LT-01 (9397 750 09065)	20011218	Product data	-	-

9. Legal information

9.1 Data sheet status

Document status ^{[1][2]}	Product status ^[3]	Definition
Objective [short] data sheet	Development	This document contains data from the objective specification for product development.
Preliminary [short] data sheet	Qualification	This document contains data from the preliminary specification.
Product [short] data sheet	Production	This document contains the product specification.

[1] Please consult the most recently issued document before initiating or completing a design.

[2] The term 'short data sheet' is explained in section "Definitions".

[3] The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the Internet at URL <http://www.nxp.com>.

9.2 Definitions

Draft — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. NXP Semiconductors does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local NXP Semiconductors sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

9.3 Disclaimers

General — Information in this document is believed to be accurate and reliable. However, NXP Semiconductors does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information.

Right to make changes — NXP Semiconductors reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use — NXP Semiconductors products are not designed, authorized or warranted to be suitable for use in medical, military, aircraft, space or life support equipment, nor in applications where failure or malfunction of an NXP Semiconductors product can reasonably be expected to result in personal injury, death or severe property or environmental damage. NXP Semiconductors accepts no liability for inclusion and/or use of NXP Semiconductors products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

Applications — Applications that are described herein for any of these products are for illustrative purposes only. NXP Semiconductors makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Quick reference data — The Quick reference data is an extract of the product data given in the Limiting values and Characteristics sections of this document, and as such is not complete, exhaustive or legally binding.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) may cause permanent damage to the device. Limiting values are stress ratings only and operation of the device at these or any other conditions above those given in the Characteristics sections of this document is not implied. Exposure to limiting values for extended periods may affect device reliability.

Terms and conditions of sale — NXP Semiconductors products are sold subject to the general terms and conditions of commercial sale, as published at <http://www.nxp.com/profile/terms>, including those pertaining to warranty, intellectual property rights infringement and limitation of liability, unless explicitly otherwise agreed to in writing by NXP Semiconductors. In case of any inconsistency or conflict between information in this document and such terms and conditions, the latter will prevail.

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

9.4 Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

TrenchMOS — is a trademark of NXP B.V.

10. Contact information

For more information, please visit: <http://www.nxp.com>

For sales office addresses, please send an email to: salesaddresses@nxp.com

11. Contents

1 Product profile1

1.1 General description1

1.2 Features and benefits1

1.3 Applications1

1.4 Quick reference data1

2 Pinning information2

3 Ordering information2

4 Limiting values3

5 Thermal characteristics5

6 Characteristics6

7 Package outline11

8 Revision history12

9 Legal information13

9.1 Data sheet status13

9.2 Definitions13

9.3 Disclaimers13

9.4 Trademarks13

10 Contact information13



Please be aware that important notices concerning this document and the product(s) described herein, have been included in section 'Legal information'.