

You are here: Home > Products > Uninterruptible Power Supply (UPS) > Computer and Peripheral > Back-UPS Pro

- Product Category
- Computer and Peripheral
 - > Back-UPS
 - > **Back-UPS Pro**
 - Network and Server (3)
 - Data Center and Facility 3 Phase (10)
 - UPS Management (7)

< Return to Uninterruptible Power Supply (UPS)

Back-UPS Pro

APC Power-Saving Back-UPS Pro 1300



APC Back-UPS Pro, 780 Watts / 1300 VA, Input 120V / Output 120V

Includes: CD with software, USB cable, User Manual

Standard Lead Time: Usually in Stock

Average Customer Review  4.3

35 of 39 (90%) customers would recommend this product to a friend.

[Read all reviews](#) | [Write a review](#)

Share this Product:   

BR1300G

Add to Cart

Add Options

-  Email Technical Specifications
-  Printer Friendly


Energy Management Services



[+ More Images](#)

- Technical Specifications
- Product Overview
- Documentation
- Software & Firmware
- Options
- Ratings and Reviews

Output	
Output Power Capacity	780 Watts / 1300 VA
Nominal Output Voltage	120V
Efficiency at Full Load	87.0%
Output Frequency (sync to mains)	50/60 Hz +/- 3 Hz user adjustable +/- 0.1
Waveform Type	Stepped approximation to a sinewave
Output Connections	(5) NEMA 5-15R (Battery Backup) 
	(5) NEMA 5-15R (Surge Protection) 
Efficiency at Half Load	86%
Input	
Nominal Input Voltage	120V
Input Frequency	50/60 Hz +/- 3 Hz (auto sensing)
Input Connections	NEMA 5-15P 
Cord Length	6 feet (1.83 meters)
Batteries & Runtime	
Battery Type	Maintenance-free sealed Lead-Acid battery with suspended electrolyte : leakproof
Included Battery Modules	1
Typical recharge time	8 hour(s)
Replacement Battery	APCRBC124
RBC™ Quantity	1
Runtime Graph	



Hover over the line on the graph above to view the runtime at any desired load

This graph is based on actual measured runtime data. All measurements were taken with new, fully charged batteries and a balanced resistive load (PF = 1.0). Actual runtimes may vary from the values of this graph. Actual runtimes are dependent on several variables including battery age, battery charge level, environmental conditions and characteristics of the connected load.

[View Enlarged Graph](#)

[View Runtime Chart](#)

Communications & Management

Control panel	Multi-function LCD status and control console
Audible Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm

Surge Protection and Filtering

Surge energy rating	354 Joules
Filtering	Full time multi-pole noise filtering :5% of IEEE surge let-through : zero clamping response time: instantaneous
Data Line Protection	Cable modem / Video protection,Network line - 10/100/1000 Base-T Ethernet (RJ-45 connector)

Physical

Maximum Height	11.85 inches (301 mm)
Maximum Width	4.41 inches (112 mm)
Maximum Depth	14.96 inches (380 mm)
Net Weight	23.10 lbs. (10.50 kg)
Shipping Weight	28.27 lbs. (12.85 kg)
Shipping Height	15.24 inches (387 mm)
Shipping Width	9.37 inches (238 mm)
Shipping Depth	19.21 inches (488 mm)
Master Carton Units	1.00
SCC Codes	1073130426876 2
Units per Pallet	24.00

Environmental

Operating Environment	32 - 104 °F (0 - 40 °C)
Operating Relative Humidity	0 - 95%
Operating Elevation	0-30000 feet (0-9000 meters)
Storage Temperature	5 - 113 °F (-15 - 45 °C)
Storage Relative Humidity	0 - 95%
Storage Elevation	0-50000 feet (0-15000 meters)
Audible noise at 1 meter from surface of unit	45.00 dBA

Conformance

Regulatory Approvals	FCC Part 15 Class B,NOM,TUV,UL 1778
Standard Warranty	3 years repair or replace
Equipment protection policy	Lifetime :
Environmental Compliance	RoHS,REACH: Contains No SVHCs

*Except where noted, all prices are Estimated Resale Price (ERP) - Without Tax/VAT. Pricing in other locations and sites may vary.

**The time to recharge to 90% of full battery capacity following a discharge to shutdown using a load rated for 1/2 the full load rating of the UPS.