

Broadband Solutions

CX3399677 | 125G110PP200ROPE COEX

ConQuest® Empty Conduit, 1 1/4 in, SDR 11, gray, with pull rope

Dimensions

Nominal Size	1-1/4 in
Wall Thickness Designation	SDR 11
Inner Diameter, nominal	33.985 mm 1.338 in
Length	914.40 m 3000.00 ft
Outer Diameter, nominal	42.164 mm 1.660 in
Wall Thickness, minimum	3.835 mm 0.151 in
Weight	320.0 lb/kft

General Specifications

Color	Gray
Conduit Type	Non-toneable
Wall Type	Smooth
Brand	ConQuest®
Warranty	One year

Material Specifications

Density Test Method	ASTM D792A
Density, maximum	0.955 g/cm ³
Density, minimum	0.941 g/cm ³
Design Standard	ASTM D3350-05
Environmental Stress Crack Resistance	Failure rate of 10% within 96 hours
Environmental Stress Test Method	ASTM D1693, ESCR Condition B
Flexural Modulus, minimum	552 N/mm ² 80000 psi
Flexural Property Test Method	ASTM D790
Hydrostatic Design Basis	Not pressure rated
Hydrostatic Design Test Method	ASTM D2837
Material Type	High density polyethylene (HDPE)
Melt Flow Rate Test Method	ASTM D1238
Melt Flow Rate, maximum	0.39 g/10 min
Tensile Property Test Method	ASTM D638
Tensile Strength at yield, minimum	21 N/mm ² 3000 psi

Mechanical Specifications

Minimum Bend Radius, unsupported	457.2 mm 18.0 in
----------------------------------	--------------------

Product Specifications



CX3399677 | 125G110PP200ROPE COEX

Pulling Tension, maximum 689.5 kg | 1520.0 lb

Pull Line Specifications

Breaking Strength	90.7 kg 200.0 lb
Material Type	Polypropylene
Pull Line Type	Rope

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

* Footnotes

Environmental Stress Crack Resistance ESCR—Environmental Stress Crack Resistance