






LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
AD	00	B1		REVISED PER ECO-08-001445	1/18/08	SS
		B2		REVISED PER ECO-10-000444	19JAN10	KK

SPECIFICATIONS:

MATERIAL:

CASE: PBT 30% GLASS UL94V-O
TERMINAL: COPPER ALLOY, TIN OVER NICKEL PLATE

- 1 ALL MATERIALS AND FINISHES SHALL COMPLY WITH EU DIRECTIVE 2002/95/EC OF 27JAN2003 (ROHS)
- 2 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



RECOMMENDED BOARD LAYOUT

2 OBSOLETE	30.48 [1.200]	12	1-1825190-0
	25.40 [1.000]	10	1825190-9
	22.86 [.900]	9	1825190-8
	20.32 [.800]	8	1825190-7
	17.78 [.700]	7	1825190-6
2 OBSOLETE	15.24 [.600]	6	1825190-5
	12.70 [.500]	5	1825190-4
	10.16 [.400]	4	1825190-3
2 OBSOLETE	7.62 [.300]	3	1825190-2
	2.54 [.200]	2	1825190-1
DIM A		POSITION	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN <u>B.S.VISWESWARA</u> 06MAY05		 Tyco Electronics Corporation Harrisburg, Pa 17105-3608			
DIMENSIONS: mm [INCHES]			CHK <u>M.S.SARVER</u>	—				
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD <u>M.S.SARVER</u>	—	NAME SHUNT, DIP, PROGRAMMABLE — —			
	0 PLC ± — 1 PLC ± — 2 PLC ± 0.03[.001] 3 PLC ± — 4 PLC ± — ANGLES ± —		PRODUCT SPEC —					
			APPLICATION SPEC —					
	MATERIAL SEE TABLE		FINISH —	WEIGHT —	SIZE A2	CAGE CODE 00779	DRAWING NO C=1825190	RESTRICTED TO —
CUSTOMER DRAWING					SCALE 4:1	SHEET 1 of 1	REV B2	