

COMMON MODE CHOKE  
CATALOG  
Suited for LAN and Telecom Applications



TABLE of CONTENTS


**Common Mode Chokes for Datacom Applications**

Surface Mount Common Mode Chokes .....2-6

Through Hole Common Mode Chokes .....7-12



**Pulse**  
A TECHNITROL COMPANY




- ### Electrical Specifications @ 25°C

| Part Number | No. of Lines | Primary Inductance OCL (μH MIN) | Common Mode Attenuation (dB TYP) |       |        |        |        |         |         |         |       | DCR (Ω MAX) | Page Number of Mech. & Schem |
|-------------|--------------|---------------------------------|----------------------------------|-------|--------|--------|--------|---------|---------|---------|-------|-------------|------------------------------|
|             |              |                                 | 100 KHz                          | 1 MHz | 10 MHz | 30 MHz | 50 MHz | 100 MHz | 300 MHz | 500 MHz | 1 GHz |             |                              |
| PE-68624    | 2            | 47                              | 11                               | 27    | 40     | 44     | 42     | 36      | 26      | 17      | —     | 0.40        | 2                            |
| PE-65855    | 2            | 4700                            | 41                               | 43    | 49     | 39     | 34     | 26      | 20      | 20      | 12    | 1.0         | 4                            |
| B2013       | 2            | 6300                            | 46                               | 47    | 43     | 32     | 25     | 29      | 21      | 14      | 16    | 1.0         | 3                            |
| B4003       | 2            | 4700                            | 42                               | 41    | 48     | 38     | 33     | 21      | 22      | 23      | 17    | 1.0         | 6                            |
| R0003       | 3            | 20                              | 6                                | 14    | 27     | 30     | 30     | 30      | 30      | 28      | 25    | 0.40        | 2                            |
| 23Z87SM     | 3            | 69                              | 9                                | 24    | 31     | 30     | 29     | 27      | 21      | 16      | —     | 0.20        | 4                            |
| PE-65857    | 4            | 22.5                            | 7                                | 20    | 30     | 37     | 38     | 34      | 24      | 13      | —     | 0.22        | 4                            |
| PE-68627    | 4            | 24                              | 8                                | 21    | 32     | 36     | 37     | 36      | 30      | 20      | —     | 0.25        | 4                            |
| T8003       | 4            | 33                              | 9                                | 13    | 32     | 32     | 30     | 27      | 16      | 17      | 13    | 0.20        | 6                            |
| 23Z4000SMD  | 4            | 36                              | 7                                | 23    | 35     | 38     | 38     | 36      | 29      | 24      | —     | 0.50        | 5                            |
| PE-65738    | 4            | 37                              | 8                                | 21    | 28     | 28     | 28     | 27      | 25      | 22      | —     | 0.30        | 3                            |
| PE-65854    | 4            | 47                              | 3                                | 19    | 32     | 36     | 35     | 29      | 12      | 6       | —     | 0.40        | 3                            |
| 23Z104SM    | 4            | 68                              | 8                                | 22    | 28     | 28     | 27     | 25      | 20      | 15      | —     | 0.20        | 5                            |
| PE-67540    | 4            | 100                             | 14                               | 33    | 44     | 48     | 49     | 44      | 34      | 29      | 20    | 0.60        | 4                            |
| PE-65853    | 4            | 4700                            | 40                               | 51    | 38     | 30     | 25     | 20      | 14      | 13      | —     | 1.20        | 3                            |
| PE-68602    | 6            | 21                              | 6                                | 19    | 28     | 34     | 35     | 36      | 34      | 29      | 1     | 0.35        | 3                            |
| 23Z106SM    | 6            | 68                              | 8                                | 22    | 29     | 30     | 30     | 29      | 24      | 19      | —     | 0.20        | 5                            |
| PE-69011    | 8            | 36                              | 8                                | 24    | 36     | 39     | 35     | 29      | 18      | 11      | —     | 0.35        | 3                            |
| 23Z105SM    | 8            | 68                              | 8                                | 24    | 30     | 29     | 27     | 24      | 16      | 11      | —     | 0.20        | 5                            |
| 23Z109SM    | 10           | 7.5                             | 4                                | 9     | 20     | 25     | 26     | 24      | 16      | 11      | —     | 0.20        | 5                            |
| T8008       | 16           | 47                              | 7                                | 27    | 40     | 44     | 42     | 36      | 26      | —       | —     | 0.40        | 6                            |


**NOTE:** Additional common mode cokes are available. Please contact Applications Engineering.

## Schematics

$\frac{.360}{9.14}$  MAX  
 $\frac{.285}{7.24}$   
 1 6  
**Pulse**  
**PE-68624**  
 or  
**R0003**  
 DATE CODE  
 COUNTRY OF ORIGIN  
 3 4  
 $\frac{.100}{2.54}$   
 $\frac{.260}{6.60}$  MAX  
 $\frac{.200}{5.08}$



R0003



Connect unused pin to logic ground for optimum performance.

**PE-68624**




# SURFACE MOUNT COMMON MODE CHOKES

## Suited for LAN and Telecom Applications



### Mechanicals


#### PE-65738, PE-68602, PE-69011




**Dimensions:**  $\frac{\text{Inches}}{\text{mm}}$   
Unless otherwise specified,  
all tolerances are  $\pm \frac{.010}{0.25}$

**Weight** . . . . .0.83 grams  
**Tape & Reel** . . . . .900/reel  
**Tube** . . . . .40/tube


### Schematics



#### PE-69011




#### PE-65853




**Dimensions:**  $\frac{\text{Inches}}{\text{mm}}$   
Unless otherwise specified,  
all tolerances are  $\pm \frac{.010}{0.25}$

**Weight** . . . . .4.0 grams  
**Tape & Reel** . . . . .150/reel  
**Tube** . . . . .35/tube

#### PE-65853



#### B2013




**Dimensions:**  $\frac{\text{Inches}}{\text{mm}}$   
Unless otherwise specified,  
all tolerances are  $\pm \frac{.010}{0.25}$

**Weight** . . . . .9.5 grams  
**Tray** . . . . .30/tray

#### B2013




#### PE-65854



**Dimensions:**  $\frac{\text{Inches}}{\text{mm}}$   
Unless otherwise specified,  
all tolerances are  $\pm \frac{.010}{0.25}$

**Weight** . . . . .0.3 grams  
**Tape & Reel** . . . . .1500/reel  
**Tube** . . . . .60/tube

#### PE-65854



# SURFACE MOUNT COMMON MODE CHOKES


## Suited for LAN and Telecom Applications



### Mechanicals

### Schematics

#### PE-65855




**Dimensions:** Inches  
mm  
Unless otherwise specified,  
all tolerances are  $\pm .010$   
0,25

**Weight** ..... 0.69 grams  
**Tape & Reel** ..... .800/reel  
**Tube** ..... .40 /tube

#### PE-65855



#### PE-65857, PE-67540





**Dimensions:** Inches  
mm  
Unless otherwise specified,  
all tolerances are  $\pm .010$   
0,25


**Weight** ..... 2.0 grams  
**Tape & Reel** ..... .250/reel  
**Tube** ..... .40 /tube

#### PE-65857

#### PE-67540




#### PE-68627




**Dimensions:** Inches  
mm  
Unless otherwise specified,  
all tolerances are  $\pm .010$   
0,25

**Weight** ..... 0.3 grams  
**Tape & Reel** ..... .1500/reel  
**Tube** ..... .55 /tube

#### PE-68627



#### 23Z87SM



**Dimensions:** Inches  
mm  
Unless otherwise specified,  
all tolerances are  $\pm .005$   
0,13

**Weight** ..... 0.5 grams  
**Tape & Reel** ..... .750/reel  
**Tube** ..... .100 /tube

#### 23Z87SM





## Schematics

# SURFACE MOUNT COMMON MODE CHOKES


## Suited for LAN and Telecom Applications



### Mechanicals

### Schematics


#### T8003




**Dimensions:**  $\frac{\text{Inches}}{\text{mm}}$   
Unless otherwise specified,  
all tolerances are  $\pm .005$   
 $0,13$

**Weight** ..... 0.84 grams  
**Tape & Reel** ..... .750/reel  
**Tube** ..... 100/tube

#### T8003




#### T8055




**Dimensions:**  $\frac{\text{Inches}}{\text{mm}}$   
Unless otherwise specified,  
all tolerances are  $\pm .010$   
 $0,25$

**Weight** ..... 0.2 grams  
**Tape & Reel** ..... .1750/reel  
**Tube** ..... 80/tube

#### T8055



#### B4003




**Dimensions:**  $\frac{\text{Inches}}{\text{mm}}$   
Unless otherwise specified,  
all tolerances are  $\pm .010$   
 $0,25$

**Weight** ..... 1.0 grams  
**Tape & Reel** ..... .425/reel  
**Tube** ..... 50/tube

#### B4003




#### T8008



**Dimensions:**  $\frac{\text{Inches}}{\text{mm}}$   
Unless otherwise specified,  
all tolerances are  $\pm .010$   
 $0,25$

**Weight** ..... 4.0 grams  
**Tape & Reel** ..... .250/reel  
**Tube** ..... 15/tube


#### T8008



**NOTE:** The common mode test circuit for surface mount is the same as for through hole and is on the back page.

# THROUGH HOLE COMMON MODE CHOKES

Suited for LAN and Telecom Applications



-  Reduces radiated EMI emissions
-  Filters common mode noise for EMI reduction
-  Common mode attenuation from 100 KHz to 1 GHz
-  Tube packaging available for through hole parts

Electrical Specifications @ 25°C

| Part Number | No. of Lines | Primary Inductance OCL (μH MIN) | Common Mode Attenuation (dB TYP) |       |        |        |        |         |         |         |       | DCR (Ω MAX) | Page Number of Mech. & Schem |
|-------------|--------------|---------------------------------|----------------------------------|-------|--------|--------|--------|---------|---------|---------|-------|-------------|------------------------------|
|             |              |                                 | 100 KHz                          | 1 MHz | 10 MHz | 30 MHz | 50 MHz | 100 MHz | 300 MHz | 500 MHz | 1 GHz |             |                              |
| PE-65944    | 2            | 24                              | 1                                | 14    | 28     | 32     | 33     | 28      | 13      | 5       | —     | 0.30        | 9                            |
| 23Z107      | 2            | 68                              | 8                                | 25    | 33     | 32     | 30     | 27      | 18      | 12      | —     | 0.20        | 10                           |
| PE-67531    | 2            | 140                             | 14                               | 34    | 45     | 49     | 50     | 47      | 38      | 32      | 25    | 0.60        | 9                            |
| B2005       | 2            | 9000                            | 47                               | 47    | 41     | 30     | 22     | 33      | 21      | 15      | 15    | 1.0         | 10                           |
| PE-65554    | 4            | 24                              | —                                | 21    | 32     | 38     | 39     | 34      | 24      | 13      | —     | 0.30        | 8                            |
| 42Z4000     | 4            | 36                              | 8                                | 24    | 37     | 40     | 40     | 38      | 30      | 24      | —     | 0.20        | 10                           |
| PE-67501    | 4            | 50                              | 14                               | 34    | 45     | 49     | 50     | 47      | 20      | 15      | 10    | 0.30        | 9                            |
| PE-68002    | 4            | 68                              | 7                                | 24    | 37     | 41     | 42     | 40      | 31      | 27      | —     | 0.35        | 9                            |
| 23Z104      | 4            | 85                              | 8                                | 23    | 29     | 29     | 28     | 25      | 17      | 11      | —     | 0.20        | 10                           |
| PE-67539    | 4            | 140                             | 14                               | 33    | 44     | 48     | 48     | 43      | 33      | 28      | 19    | 0.60        | 9                            |
| PE-65542    | 4            | 1000                            | 28                               | 41    | 42     | 32     | 22     | —       | —       | —       | —     | 0.70        | 8                            |
| PT5039      | 4            | 3600                            | 42                               | 43    | 42     | 32     | 27     | 17      | 15      | 9       | 13    | 0.50        | 8                            |
| J0010D11    | 4            | —                               | 9                                | 13    | 32     | 35     | 35     | 29      | 13      | 24      | 19    | 0.50        | 11                           |
| PE-65950    | 4            | 4700±30%                        | 40                               | 51    | 37     | 28     | 23     | 20      | —       | —       | —     | 1.00        | 8                            |
| PE-65541    | 4            | 6000                            | 44                               | 54    | 33     | 32     | 29     | —       | —       | —       | —     | 1.40        | 8                            |
| PE-68613    | 4            | 3290                            | 40                               | 51    | 37     | 28     | 23     | 20      | —       | —       | —     | 1.00        | 11                           |
| PE-64683    | 6            | 25                              | 6                                | 18    | 32     | 38     | 37     | 32      | 21      | 17      | —     | 0.35        | 8                            |

# THROUGH HOLE COMMON MODE CHOKES


Suited for LAN and Telecom Applications



## Mechanicals

## Schematics


### PE-64683




**Dimensions:**  $\frac{\text{Inches}}{\text{mm}}$   
Unless otherwise specified,  
all tolerances are  $\pm \frac{.010}{0,25}$

**Weight** .....0.27 grams  
**Tube** .....30/tube

### PE-64683




### PE-65541, PE-65542, PE-65950




**Dimensions:**  $\frac{\text{Inches}}{\text{mm}}$   
Unless otherwise specified,  
all tolerances are  $\pm \frac{.010}{0,25}$

**Weight** .....0.38 grams  
**Tube** .....35/tube

### PE-65541 PE-65542 PE-65950




### PE-65554




**Dimensions:**  $\frac{\text{Inches}}{\text{mm}}$   
Unless otherwise specified,  
all tolerances are  $\pm \frac{.010}{0,25}$

**Weight** .....2.5 grams  
**Tube** .....35/tube

### PE-65554




### PT5039



**Dimensions:**  $\frac{\text{Inches}}{\text{mm}}$   
Unless otherwise specified,  
all tolerances are  $\pm \frac{.010}{0,25}$

**Weight** .....2.5 grams  
**Tube** .....35/tube

### PT5039





# THROUGH HOLE COMMON MODE CHOKES

Suited for LAN and Telecom Applications




**Pulse**  
A TECHNITROL COMPANY

## Mechanicals

## Schematics

### PE-65944




Dimensions:  $\frac{\text{Inches}}{\text{mm}}$   
Unless otherwise specified,  
all tolerances are  $\pm \frac{.010}{0,25}$

Weight .....1.07 grams  
Tube ..... .30/tube

### PE-65944




### PE-67501, PE-67539




Dimensions:  $\frac{\text{Inches}}{\text{mm}}$   
Unless otherwise specified,  
all tolerances are  $\pm \frac{.010}{0,25}$

Weight .....2.4 grams  
Tube ..... .40/tube

### PE-67501 PE-67539



### PE-67531




Dimensions:  $\frac{\text{Inches}}{\text{mm}}$   
Unless otherwise specified,  
all tolerances are  $\pm \frac{.010}{0,25}$

Weight .....0.76 grams  
Tube ..... .40/tube

### PE-67531




### PE-68002



Dimensions:  $\frac{\text{Inches}}{\text{mm}}$   
Unless otherwise specified,  
all tolerances are  $\pm \frac{.010}{0,25}$

Weight .....1.4 grams  
Tube ..... .50/tube

### PE-68002



# THROUGH HOLE COMMON MODE CHOKES


Suited for LAN and Telecom Applications



## Mechanicals

## Schematics

### B2005



Dimensions:  $\frac{\text{Inches}}{\text{mm}}$


Unless otherwise specified,  
all tolerances are  $\pm .005$   
0,13

Weight . . . . .3.7 grams

Tube . . . . .40/tube



### 23Z104




Dimensions:  $\frac{\text{Inches}}{\text{mm}}$

Unless otherwise specified,  
all tolerances are  $\pm .005$   
0,13


Weight . . . . .1.0 grams

Tube . . . . .50/tube

### 23Z104



### 23Z107



Dimensions:  $\frac{\text{Inches}}{\text{mm}}$

Unless otherwise specified,  
all tolerances are  $\pm .005$   
0,13


Weight . . . . .0.45 grams

Tube . . . . .100/tube

### 23Z107



### 42Z4000




Dimensions:  $\frac{\text{Inches}}{\text{mm}}$

Unless otherwise specified,  
all tolerances are  $\pm .010$   
0,25

Weight . . . . .1.5 grams

Tube . . . . .47/tube

### 42Z4000



# THROUGH HOLE COMMON MODE CHOKES

## Suited for LAN and Telecom Applications




**Pulse**  
A TECHNITROL COMPANY

### Mechanicals

### Schematics


#### PE-68613





Dimensions: Inches  
mm  
Unless otherwise specified,  
all tolerances are  $\pm .005$   
0,127

Weight .....3.5 grams  
Tube .....40/tube

#### PE-68613



#### J0010D11 - Filtered Connector




# THROUGH HOLE COMMON MODE CHOKES

## Suited for LAN and Telecom Applications



### Common Mode Test Circuit for Surface Mount and Through Hole



#### Test Notes:

1. Network analyzer calibrated to compensate for 50  $\Omega$  resistors.
2. All windings on a core are connected in parallel for the test.
3. For multi-core chokes, test data is for one core only. The windings on the other core(s) are left unconnected (i.e. open).

#### For More Information:

##### Pulse Worldwide Headquarters

12220 World Trade Dr.  
San Diego, CA 92128  
U.S.A.  
[www.pulseeng.com](http://www.pulseeng.com)

##### Pulse European Headquarters

Einsteinstrasse 1  
71083 Herrenberg  
Germany

##### Pulse China Headquarters

B402, Shenzhen  
Tech-Innovation International  
10th Kejinan Rd.  
High-Tech Industrial Park  
Nanshan District, Shenzhen  
China

##### Pulse North China

Room 1503  
XinYin Building  
No. 888 YiShan Road  
Shanghai 200233  
China

##### Pulse South Asia

150 Kampong Ampat  
#07-01/02  
KA Centre  
Singapore 368324

##### Pulse North Asia

No. 26  
Kao Ching Road  
Yang Mei Chen  
Taoyuan Hsien  
Taiwan, R. O. C.

TEL: 858 674 8100  
FAX: 858 674 8262

TEL: 49 7032 7806 0  
FAX: 49 7032 7806 12

TEL: 86 755 33966678  
FAX: 86 755 33966700

TEL: 86 21 54643211/2  
FAX: 86 21 54643210

TEL: 65 6287 8998  
FAX: 65 6280 0080

TEL: 886 3 4641811  
FAX: 886 3 4641911

Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners.

© Copyright, 2007. Pulse Engineering, Inc. All rights reserved.