


ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.


REVISIONS				DOC. NO. SPC-F005	Effective: 12/21/98 * DCP No. 480			
DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKED	DATE	APPRVD	DATE
809	A	RELEASED	DJC	8/20/99	JJC	2/29/00	JWM	3/1/00



SPECIFICATIONS:

- MATERIAL:
- CONNECTOR:
- HOUSING: THERMOPLASTIC, GLASS FIBER FILL, UL94V-0
- CONTACT: PHOSPHOR BRONZE, GOLD PLATING ON CONTACT INTERFACE
- SHELL: STEEL, TIN-LEAD PLATING OVER COPPER UNDERPLATING
- CABLE: USB STANDARD FULL SPEED TYPE, UL94V-0
- OVERMOLD: PVC, UL94V-0
- ELECTRICAL:
- VOLTAGE: 30 V AC
- CURRENT: 1A MAXIMUM PER CONTACT
- MECHANICAL:
- RANDOM VIBRATION: NO DISCONTINUITY OF 1uS OR LONGER DURATION
- PHYSICAL SHOCK: NO DISCONTINUITY OF 1uS OR LONGER DURATION
- INSERTION FORCE: 4KG MAX
- WITHDRAWAL FORCE: 1~4KG
- ENVIRONMENTAL:
- THERMAL SHOCK: 10 CYCLE -55° AND +85°C
- COLOR:
- OFF WHITE

WIRE DIAGRAM



DISCLAIMER

ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY: DANIEL CAREY

CHECKED BY: JOHN COLE

APPROVED BY: JEFF MCVICKER

DATE: 8/20/99

DATE: 2/29/00

DATE: 3/1/00

DRAWING TITLE: USB TYPE A TO USB TYPE B CABLE ASSEMBLY

SIZE: A

DWG. NO. SPC4801

SCALE: NTS

ELECTRONIC FILE: 50N154.DWG

REV: A

SHEET: 1 OF 1

SPC TECHNOLOGY

SPC-F005.DWG