




PERFORMANCE CHARACTERISTICS

CURRENT RATING 1.5A AT 20°C (FULLY LOADED)
1 A AT 70°C (FULLY LOADED)
RATED VOLTAGE : 500 V AC (CONT /CONT)
OPERATING TEMPERATURE : -55°C TO 125°C
CONTACT RESISTANCE 20 mΩ MAX
INSERTION FORCE : 0.75N MAX/CONT
EXTRACTION FORCE : 0.15N MIN/CONT
INSULATION RESISTANCE : 10⁴ MΩ MIN

NOTES

1. " " LEAD FREE INDICATOR :LF=LEAD FREE
" " PERFORMANCE LEVEL INDICATION (REF DWG NO.BSC .201844.003)
2. THIS PRODUCT IS CSA APPROVED.
THIS PRODUCT IS UL RECOGNIZED.
3. FOR RECOMMENDED PTH DIMENSIONS REFER DRAWING :BS.A.201572.001
4. THIS PRODUCT (LF) MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008

rev	ecn no	dr	date
A	CONVERSION REVISION 00	KN	14-09-01
B	DG05-0278	Kason	02-08-05
C	DG10-0110	NZ	2010.9.3
-	-	-	-
-	-	-	-
-	-	-	-

Material			Spec ref		
Mat code			✓		
Heat treat			1DEC±0.2 1DEC 2DEC±0.1 2DEC ANGLE±1° HOEKEN		
Plating/Finish			projection		
Dr	W.Panis	22-01-95	size A4		
Eng			Scale 2.000		
Chr			Model Name		
Appr			Model Revision		
Product family MILLIPACS			ECN		
REL Level			REL Level		
FCI			title		
MPACS 5R STR RCP SG PF ASSY TYPE C			dwg no		
Pro/E file			BSC201907003		
catalog no			Rev. C		
HM2S03PE5100---			CUMSTOMER DRAWING		
sheet 1 of 1					