







Copyright FCI.
FCI

PRODUCT NO.
SEE TABLE

HOUSING CONFIGURATION



| | | | | | | | | | | | | |
|--|---------------------------------------|---------|--------|---|---|------------|---|---|-----------------------|----------|----------------|------|
| spec ref | | | | dr | SH TAN | 2004-04-30 | projection  | MM  | size | A3 | scale | 12:1 |
| tolerance std | TOLERANCES UNLESS OTHERWISE SPECIFIED | | | eng | DENNIS GOH | 2010-11-01 | | | ecn no | | ELX-S-001904-1 | |
| | | | | chr | DENNIS GOH | 2010-11-01 | | | rel level Released | | | |
| | | | | appr | JOEY NG | 2010-11-01 | product family | | | | | |
| surface  | linear | 0.X | ±0.20 |  | title COMPRESSION CONNECTOR (1.25 mm PITCH) | | | | dwg no 55527 | rev F | | |
| | | 0.XX | ±0.10 | | | | | | | | | |
| | | 0.XXX | ±0.050 | | | | | | | | | |
| | | angular | 0° | ±2° | www.fci.com | cat. no. | | Product - Customer Drw | | | sheet 2 of 4 | |



Copyright FCI.

D

C

B

A

| PRODUCT NO. | NO. OF POSITIONS | PLATING | DIM A | DIM B | DIM X | DIM Y | PACKAGING |
|---------------|------------------|---------|-------|-------|--------------|-------------|-------------|
| 55527-001 | 18 | NOTE 5 | 3.35 | 0.70 | 11.95 ± 0.05 | 7.00 ± 0.05 | TUBE |
| 55527-001TR | 18 | NOTE 5 | 3.35 | 0.70 | 11.95 ± 0.05 | 7.00 ± 0.05 | TAPE & REEL |
| 55527-101LF | 18 | NOTE 6 | 3.35 | 0.70 | 11.95 ± 0.05 | 7.00 ± 0.05 | TUBE |
| 55527-101TRLF | 18 | NOTE 6 | 3.35 | 0.70 | 11.95 ± 0.05 | 7.00 ± 0.05 | TAPE & REEL |
| 55527-201LF | 18 | NOTE 7 | 3.35 | 0.70 | 11.95 ± 0.05 | 7.00 ± 0.05 | TUBE |
| 55527-201TRLF | 18 | NOTE 7 | 3.35 | 0.70 | 11.95 ± 0.05 | 7.00 ± 0.05 | TAPE & REEL |
| 55527-202LF | 18 | NOTE 7 | 3.45 | 0.80 | 11.95 ± 0.05 | 7.00 ± 0.05 | TUBE |
| 55527-202TRLF | 18 | NOTE 7 | 3.45 | 0.80 | 11.95 ± 0.05 | 7.00 ± 0.05 | TAPE & REEL |
| 55527-302LF | 18 | NOTE 8 | 3.45 | 0.80 | 11.95 ± 0.05 | 7.00 ± 0.05 | TUBE |
| 55527-302TRLF | 18 | NOTE 8 | 3.45 | 0.80 | 11.95 ± 0.05 | 7.00 ± 0.05 | TAPE & REEL |
| 55527-022 | 22 | NOTE 5 | 3.35 | 0.70 | 14.45 ± 0.05 | 7.00 ± 0.05 | TUBE |
| 55527-022TR | 22 | NOTE 5 | 3.35 | 0.70 | 14.45 ± 0.05 | 7.00 ± 0.05 | TAPE & REEL |
| 55527-122LF | 22 | NOTE 6 | 3.35 | 0.70 | 14.45 ± 0.05 | 7.00 ± 0.05 | TUBE |
| 55527-122TRLF | 22 | NOTE 6 | 3.35 | 0.70 | 14.45 ± 0.05 | 7.00 ± 0.05 | TAPE & REEL |









DIAGRAM 1
APPLICABLE TO SELECTIVE PLATING ONLY

| | | | | | | | | | | | | | | |
|---|---------------------------------------|-------|--------|---|------------|--|---|---|--------|----------------|--------------|------|-----|---|
| spec ref | | | | dr | SH TAN | 2004-04-30 | projection  |  | size | A3 | scale | 15:1 | | |
| tolerance std | TOLERANCES UNLESS OTHERWISE SPECIFIED | | | eng | DENNIS GOH | 2010-11-01 | | | ecn no | ELX-S-001904-1 | | | | |
| | | | | chr | DENNIS GOH | 2010-11-01 | | | | | | | | |
| | | | | appr | JOEY NG | 2010-11-01 | product family | | | rel level | Released | | | |
| surface  | linear | 0.X | ±0.20 |  | title | COMPRESSION CONNECTOR (1.25 mm PITCH) | | | dwg no | 55527 | | | rev | F |
| | | 0.XX | ±0.10 | | | | | | | | | | | |
| | | 0.XXX | ±0.050 | | | | | | | | | | | |
| | angular | 0° | ±2° | www.fci.com | cat. no. | Product - Customer Drw | | | | | sheet 3 of 4 | | | |


- NOTES:
- 1. MATERIALS:
HOUSING: HIGH TEMPERATURE PLASTIC, BLACK OR GRAY
CONTACT: COPPER ALLOY
 - 2. CONTACT FORCE:
100g MIN WHEN COMPRESSED TO A WORKING OR STACK HEIGHT
OF 2.90 mm (nominal) FROM DATUM A
 - 3. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY
REGULATIONS AS DESCRIBED IN GS-22-008
 - 4. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE
FOR 10 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW OVEN

- 5. PLATING:
TIN-LEAD OVER NICKEL UNDERPLATE
- 6. PLATING:
TIN (LEAD FREE) OVER NICKEL UNDERPLATE
- 7. PLATING
NICKEL UNDERPLATE OVERALL
2u" MIN TO 5u" MAX GOLD AT CONTACT AND
GOLD FLASH ON SOLDER TAIL
- 8. PLATING
NICKEL UNDERPLATE OVERALL
2u" MIN TO 5u" MAX GOLD AT CONTACT AND
SOLDER TAIL (REFER DIAGRAM 1)







RECOMMENDED CONTACT PAD DIM.
(NO. OF PADS DEPEND ON NO. OF POSITIONS OF THE CONNECTOR)

SCALE 10:1



SCALE 10:1

RECOMMENDED SMT PAD DIM.
(NO. OF PADS DEPEND ON
NO. OF POSITIONS OF THE CONNECTOR)

| | | | | | | | | | | | | | |
|---|---------------------------------------|-------|--------|---|------------|--|---|---|-----------|-------|----------------|----------|---|
| spec ref | | | | dr | SH TAN | 2004-04-30 | projection  | MM  | size | A3 | scale | 4:1 | |
| tolerance std | TOLERANCES UNLESS OTHERWISE SPECIFIED | | | eng | DENNIS GOH | 2010-11-01 | | | ecn no | | ELX-S-001904-1 | | |
| | | | | chr | DENNIS GOH | 2010-11-01 | | | rel level | | | Released | |
| | | | | appr | JOEY NG | 2010-11-01 | product family | | | | | | |
| surface  | linear | 0.X | ±0.20 |  | title | COMPRESSION CONNECTOR (1.25 mm PITCH) | | | dwg no | 55527 | | rev | F |
| | | 0.XX | ±0.10 | | | | | | | | | | |
| | | 0.XXX | ±0.050 | | | | | | | | | | |
| | angular | 0° | ±2° | | | | | | | | | | |