Is Now Part of

ON Semiconductor®

To learn more about ON Semiconductor, please visit our website at
www.onsemi.com

Please note: As part of the Fairchild Semiconductor integration, some of the Fairchild orderable part numbers will need to change in order to meet ON Semiconductor's system requirements. Since the ON Semiconductor product management systems do not have the ability to manage part nomenclature that utilizes an underscore (_), the underscore (_) in the Fairchild part numbers will be changed to a dash (-). This document may contain device numbers with an underscore (_). Please check the ON Semiconductor website to verify the updated device numbers. The most current and up-to-date ordering information can be found at www.onsemi.com. Please email any questions regarding the system integration to Fairchild_questions@onsemi.com.

FAIRCHILD SEMICONDUCTOR™

October 2003
Revised January 2005

NC7NP04
TinyLogic® ULP Triple Inverter

General Description

The NC7NP04 is a triple inverter from Fairchild's Ultra Low Power (ULP) Series of TinyLogic®. Ideal for applications where battery life is critical, this product is designed for ultra low power consumption within the V_{CC} operating range of 0.9V to 3.6V.

The internal circuit is composed of a minimum of inverter stages including the output buffer, to enable ultra low static and dynamic power.

The NC7NP04 is designed for optimized power and speed, and is fabricated with an advanced CMOS technology to achieve high speed, low noise operation while maintaining extremely low CMOS power dissipation.

Features

- Space saving US8 package
- Ultra small MicroPak™ Pb-Free package
- 0.9V to 3.6V V_{CC} supply operation
- 3.6V overvoltage tolerant I/O's at V_{CC} from 0.9V to 3.6V
- t_{PD}
  - 4.0 ns typ for 3.0V to 3.6V V_{CC}
  - 5.0 ns typ for 2.3V to 2.7V V_{CC}
  - 6.0 ns typ for 1.65V to 1.95V V_{CC}
  - 7.0 ns typ for 1.40V to 1.60V V_{CC}
  - 11.0 ns typ for 1.10V to 1.30V V_{CC}
  - 27.0 ns typ for 0.90V V_{CC}
- Power-Off high impedance inputs and outputs
- Static Drive (I_{OH}/I_{OL})
  - ±2.6 mA @ 3.00V V_{CC}
  - ±2.1 mA @ 2.30V V_{CC}
  - ±1.5 mA @ 1.65V V_{CC}
  - ±1.0 mA @ 1.40V V_{CC}
  - ±0.5 mA @ 1.10V V_{CC}
  - ±20 µA @ 0.9V V_{CC}
- Low noise switching using design techniques of Quiet Series™ noise/EMI reduction circuitry
- Ultra low dynamic power

Ordering Code:

Order Number	Package Number	Product Code Top Mark	Package Description	Supplied As
NC7NP04K8X	MAB08A	NP04	8-Lead US8, JEDEC MO-187, Variation CA 3.1mm Wide	3k Units on Tape and Reel
NC7NP04L8X	MAC08A	X5	Pb-Free 8-Lead MicroPak, 1.6 mm Wide	5k Units on Tape and Reel

Pb-Free package per JEDEC J-STD-020B.

Battery Life vs. V_{CC} Supply Voltage



TinyLogic ULP and ULP-A with up to 50% less power consumption can extend your battery life significantly.

Battery Life = ($V_{battery}$ *$I_{battery}$*.9) / (P_{device}) / 24hrs/day

Where, P_{device} = (I_{CC} * V_{CC}) + (C_{PD} + C_L) * V_{CC}^2 * f

Assumes ideal 3.6V Lithium Ion battery with current rating of 900mAH and derated 90% and device frequency at 10MHz, with C_L = 15 pF load

Logic Symbol

IEEE/IEC



Pin Descriptions

Pin Names	Description
A	Input
Y	Output

Function Table

$Y = \overline{A}$

Input	Output
A	**Y**
L	H
H	L

H = HIGH Logic Level
L = LOW Logic Level

Connection Diagrams

Pin Assignments for US8



(Top View)

Pin One Orientation Diagram



AAA represents Product Code Top Mark - see ordering code
Note: Orientation of Top Mark determines Pin One location. Read the Top Product Code Mark left to right, Pin One is the lower left pin (see diagram).

Pad Assignments for MicroPak



(Top Thru View)

Absolute Maximum Ratings (Note 1)

Supply Voltage (V_{CC})	−0.5V to +4.6V
DC Input Voltage (V_{IN})	−0.5V to +4.6V
DC Output Voltage (V_{OUT})	
HIGH or LOW State (Note 2)	−0.5V to V_{CC} +0.5V
V_{CC} = 0V	−0.5V to 4.6V
DC Input Diode Current (I_{IK}) V_{IN} < 0V	±50 mA
DC Output Diode Current (I_{OK})	
V_{OUT} < 0V	−50 mA
V_{OUT} > V_{CC}	+50 mA
DC Output Source/Sink Current (I_{OH}/I_{OL})	± 50 mA
DC V_{CC} or Ground Current per	
Supply Pin (I_{CC} or Ground)	± 50 mA
Storage Temperature Range (T_{STG})	−65°C to +150°C

Recommended Operating Conditions (Note 3)

Supply Voltage	0.9V to 3.6V
Input Voltage (V_{IN})	0V to 3.6V
Output Voltage (V_{OUT})	
HIGH or LOW State	0V to V_{CC}
V_{CC} = 0V	0V to 3.6V
Output Current in I_{OH}/I_{OL}	
V_{CC} = 3.0V to 3.6V	±2.6 mA
V_{CC} = 2.3V to 2.7V	±2.1 mA
V_{CC} = 1.65V to 1.95V	±1.5 mA
V_{CC} = 1.40V to 1.60V	±1.0 mA
V_{CC} = 1.10V to 1.30V	±0.5 mA
V_{CC} = 0.9V	±20 µA
Free Air Operating Temperature (T_A)	−40°C to +85°C
Minimum Input Edge Rate ($\Delta t/\Delta V$)	
V_{IN} = 0.8V to 2.0V, V_{CC} = 3.0V	10 ns/V

Note 1: Absolute Maximum Ratings: are those values beyond which the safety of the device cannot be guaranteed. The device should not be operated at these limits. The parametric values defined in the Electrical Characteristics tables are not guaranteed at the absolute maximum ratings. The "Recommended Operating Conditions" table will define the conditions for actual device operation.

Note 2: I_O Absolute Maximum Rating must be observed.

Note 3: Unused inputs must be held HIGH or LOW. They may not float.

DC Electrical Characteristics

Symbol	Parameter	V_{CC} (V)	T_A = +25°C Min	T_A = +25°C Max	T_A = −40°C to +85°C Min	T_A = −40°C to +85°C Max	Units	Conditions
V_{IH}	HIGH Level Input Voltage	0.90	0.65 x V_{CC}		0.65 x V_{CC}		V	
		1.10 ≤ V_{CC} ≤ 1.30	0.65 x V_{CC}		0.65 x V_{CC}			
		1.40 ≤ V_{CC} ≤ 1.60	0.65 x V_{CC}		0.65 x V_{CC}			
		1.65 ≤ V_{CC} ≤ 1.95	0.65 x V_{CC}		0.65 x V_{CC}			
		2.30 ≤ V_{CC} ≤ 2.70	1.6		1.6			
		3.00 ≤ V_{CC} ≤ 3.60	2.1		2.1			
V_{IL}	LOW Level Input Voltage	0.90		0.35 x V_{CC}		0.35 x V_{CC}	V	
		1.10 ≤ V_{CC} ≤ 1.30		0.35 x V_{CC}		0.35 x V_{CC}		
		1.40 ≤ V_{CC} ≤ 1.60		0.35 x V_{CC}		0.35 x V_{CC}		
		1.65 ≤ V_{CC} ≤ 1.95		0.35 x V_{CC}		0.35 x V_{CC}		
		2.30 ≤ V_{CC} ≤ 2.70		0.7		0.7		
		3.00 ≤ V_{CC} ≤ 3.60		0.9		0.9		
V_{OH}	HIGH Level Output Voltage	0.90	V_{CC} − 0.1		V_{CC} − 0.1		V	I_{OH} = −20 µA
		1.10 ≤ V_{CC} ≤ 1.30	V_{CC} − 0.1		V_{CC} − 0.1			
		1.40 ≤ V_{CC} ≤ 1.60	V_{CC} − 0.1		V_{CC} − 0.1			
		1.65 ≤ V_{CC} ≤ 1.95	V_{CC} − 0.1		V_{CC} − 0.1			
		2.30 ≤ V_{CC} ≤ 2.70	V_{CC} − 0.1		V_{CC} − 0.1			
		3.00 ≤ V_{CC} ≤ 3.60	V_{CC} − 0.1		V_{CC} − 0.1			
		1.10 ≤ V_{CC} ≤ 1.30	0.75 x V_{CC}		0.70 x V_{CC}			I_{OH} = −0.5 mA
		1.40 ≤ V_{CC} ≤ 1.60	1.07		0.99			I_{OH} = −1.0 mA
		1.65 ≤ V_{CC} ≤ 1.95	1.24		1.22			I_{OH} = −1.5 mA
		2.30 ≤ V_{CC} ≤ 2.70	1.95		1.87			I_{OH} = −2.1 mA
		3.00 ≤ V_{CC} ≤ 3.60	2.61		2.55			I_{OH} = −2.6 mA

DC Electrical Characteristics (Continued)

Symbol	Parameter	V_{CC} (V)	$T_A = +25°C$		$T_A = -40°C$ to $+85°C$		Units	Conditions
			Min	Max	Min	Max		
V_{OL}	LOW Level	0.90		0.1		0.1		
	Output Voltage	$1.10 \le V_{CC} \le 1.30$		0.1		0.1		
		$1.40 \le V_{CC} \le 1.60$		0.1		0.1		
		$1.65 \le V_{CC} \le 1.95$		0.1		0.1		$I_{OL} = 20\ \mu A$
		$2.30 \le V_{CC} \le 2.70$		0.1		0.1		
		$3.00 \le V_{CC} \le 3.60$		0.1		0.1	V	
		$1.10 \le V_{CC} \le 1.30$		0.30 x V_{CC}		0.30 x V_{CC}		$I_{OL} = 0.5$ mA
		$1.40 \le V_{CC} \le 1.60$		0.31		0.37		$I_{OL} = 1.0$ mA
		$1.65 \le V_{CC} \le 1.95$		0.31		0.35		$I_{OL} = 1.5$ mA
		$2.30 \le V_{CC} \le 2.70$		0.31		0.33		$I_{OL} = 2.1$ mA
		$3.00 \le V_{CC} \le 3.60$		0.31		0.33		$I_{OL} = 2.6$ mA
I_{IN}	Input Leakage Current	0.90 to 3.60		±0.1		±0.5	μA	$0 \le V_I \le 3.6V$
I_{OFF}	Power Off Leakage Current	0		0.5		0.5	μA	$0 \le (V_I, V_O) \le 3.6V$
I_{CC}	Quiescent Supply Current	0.90 to 3.60		0.9		0.9	μA	$V_I = V_{CC}$ or GND

AC Electrical Characteristics

Symbol	Parameter	V_{CC} (V)	$T_A = +25°C$			$T_A = -40°C$ to $+85°C$		Units	Conditions	Figure Number
			Min	Typ	Max	Min	Max			
t_{PHL}	Propagation Delay	0.90		27.0						
t_{PLH}		$1.10 \le V_{CC} \le 1.30$	3.5	11.0	21.8	3.0	34.3			
		$1.40 \le V_{CC} \le 1.60$	2.5	7.0	14.8	2.0	15.0	ns	$C_L = 10$ pF	Figures
		$1.65 \le V_{CC} \le 1.95$	2.0	6.0	12.0	1.5	12.2		$R_L = 1$ MΩ	1, 2
		$2.30 \le V_{CC} \le 2.70$	1.5	5.0	9.4	1.0	9.9			
		$3.00 \le V_{CC} \le 3.60$	1.0	4.0	8.3	1.0	9.0			
t_{PHL}	Propagation Delay	0.90		30.0						
t_{PLH}		$1.10 \le V_{CC} \le 1.30$	4.0	11.0	22.8	3.5	37.3			
		$1.40 \le V_{CC} \le 1.60$	3.0	8.0	15.5	2.5	16.5	ns	$C_L = 15$ pF	Figures
		$1.65 \le V_{CC} \le 1.95$	2.5	6.0	12.6	2.0	13.6		$R_L = 1$ MΩ	1, 2
		$2.30 \le V_{CC} \le 2.70$	2.0	5.0	9.9	1.5	10.8			
		$3.00 \le V_{CC} \le 3.60$	1.5	4.0	8.7	1.0	9.5			
t_{PHL}	Propagation Delay	0.90		32.0						
t_{PLH}		$1.10 \le V_{CC} \le 1.30$	5.0	13.0	25.9	4.0	46.3			
		$1.40 \le V_{CC} \le 1.60$	4.0	9.0	17.8	3.5	18.2	ns	$C_L = 30$ pF	Figures
		$1.65 \le V_{CC} \le 1.95$	3.0	7.0	14.4	2.0	15.9		$R_L = 1$ MΩ	1, 2
		$2.30 \le V_{CC} \le 2.70$	2.0	6.0	11.3	1.5	12.8			
		$3.00 \le V_{CC} \le 3.60$	1.5	5.0	9.2	1.0	10.7			
C_{IN}	Input Capacitance	0		2.0				pF		
C_{OUT}	Output Capacitance	0		4.0				pF		
C_{PD}	Power Dissipation Capacitance	0.9 to 3.60		8.0				pF	$V_I = 0V$ or V_{CC}, f = 10 MHz	

AC Loading and Waveforms



FIGURE 1. AC Test Circuit



FIGURE 2. AC Waveforms

Symbol	V_{CC}					
	3.3V ± 0.3V	**2.5V ± 0.2V**	**1.8V ± 0.15V**	**1.5V ± 0.10V**	**1.2V ± 0.10V**	**0.9V**
V_{mi}	1.5V	$V_{CC}/2$	$V_{CC}/2$	$V_{CC}/2$	$V_{CC}/2$	$V_{CC}/2$
V_{mo}	1.5V	$V_{CC}/2$	$V_{CC}/2$	$V_{CC}/2$	$V_{CC}/2$	$V_{CC}/2$

Tape and Reel Specification

TAPE FORMAT for US8

Package Designator	Tape Section	Number Cavities	Cavity Status	Cover Tape Status
K8X	Leader (Start End)	125 (typ)	Empty	Sealed
	Carrier	3000	Filled	Sealed
	Trailer (Hub End)	75 (typ)	Empty	Sealed

TAPE DIMENSIONS inches (millimeters)



TAPE FORMAT for MicroPak

Package Designator	Tape Section	Number Cavities	Cavity Status	Cover Tape Status
L8X	Leader (Start End)	125 (typ)	Empty	Sealed
	Carrier	3000	Filled	Sealed
	Trailer (Hub End)	75 (typ)	Empty	Sealed

TAPE DIMENSIONS inches (millimeters)



Tape and Reel Specification (Continued)

REEL DIMENSIONS inches (millimeters)



Tape Size	A	B	C	D	N	W1	W2	W3
8 mm	7.0 (177.8)	0.059 (1.50)	0.512 (13.00)	0.795 (20.20)	2.165 (55.00)	0.331 + 0.059/–0.000 (8.40 + 1.5/–0.00)	0.567 (14.40)	W1 + 0.078/–0.039 (W1 + 2.00/–1.00)

Physical Dimensions inches (millimeters) unless otherwise noted





LAND PATTERN RECOMMENDATION







DETAIL A

NOTES:

A. CONFORMS TO JEDEC REGISTRATION MO-187
B. DIMENSIONS ARE IN MILLIMETERS.
C. DIMENSIONS ARE EXCLUSIVE OF BURRS, MOLD FLASH, AND TIE BAR EXTRUSIONS.
D. DIMENSIONS AND TOLERANCES PER ANSI Y14.5M, 1982.

MAB08AREVC

8-Lead US8, JEDEC MO-187, Variation CA 3.1mm Wide
Package Number MAB08A

Physical Dimensions inches (millimeters) unless otherwise noted (Continued)



Notes:

1. PACKAGE CONFORMS TO JEDEC MO-255 VARIATION UAAD
2. DIMENSIONS ARE IN MILLIMETERS
3. DRAWING CONFORMS TO ASME Y.14M-1994
4. PIN 1 FLAG, END OF PACKAGE OFFSET.

MAC08AREVC

Pb-Free 8-Lead MicroPak, 1.6 mm Wide
Package Number MAC08A

LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF THE PRESIDENT OF FAIRCHILD SEMICONDUCTOR CORPORATION. As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury to the user.
2. A critical component in any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

www.fairchildsemi.com

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:
Literature Distribution Center for ON Semiconductor
19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA
Phone: 303−675−2175 or 800−344−3860 Toll Free USA/Canada
Fax: 303−675−2176 or 800−344−3867 Toll Free USA/Canada
Email: orderlit@onsemi.com

N. American Technical Support: 800−282−9855 Toll Free USA/Canada
Europe, Middle East and Africa Technical Support:
Phone: 421 33 790 2910
Japan Customer Focus Center
Phone: 81−3−5817−1050

ON Semiconductor Website: **www.onsemi.com**

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative