

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [39100-1012](#)
Status: **Active**
Description: 10.00mm Pitch Beau™ Eurostyle™ Two-Screw Terminal Strips, 12 Circuits

Documents:

[3D Model](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Drawing \(PDF\)](#)

Agency Certification

CSA 228650
UL E48521

General

Product Family Terminal Blocks
Series [39100](#)
Application Wire-to-Wire
Component Type One Piece
Product Name Eurostyle™Two Screw
Type Barrier Strip
UPC 822348694334

Physical

Circuits (Loaded) 12
Entry Angle Horizontal
Lock to Mating Part None
Net Weight 29.320/g
Number of Rows 2
Orientation Vertical
PCB Retention Yes
Panel Mount Mounting Holes Between Circuit
Pitch - Mating Interface 10.00mm
Pitch - Termination Interface 10.00mm
Polarized to Mating Part No
Stackable No
Temperature Range - Operating 100°C
Wire Size AWG 10, 12, 14, 16, 18


Electrical

Current - Maximum per Contact 30A
Voltage - Maximum 600V

Material Info

Reference - Drawing Numbers

Sales Drawing SD-39100-004



Series

image - Reference only

EU RoHS

RoHS Compliant by Exemption
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS



Need more information on product environmental compliance?
Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)
Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[39100Series](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[39100-1012](#)