

Power Splitter/Combiner

2 Way-0° 50Ω

2825 to 3700 MHz

SCN-2-35+ SCN-2-35



CASE STYLE: FV1206-1

PRICE: \$ 2.50 ea. QTY (10-49)

\$ 0.99 ea. QTY (100)

Maximum Ratings

Operating Temperature -55°C to 100°C

Storage Temperature -55°C to 100°C

Power Input (as a splitter) 4W* max.

*derate linearly to 1.3W at 100°C ambient, power input as combiner is limited by rating of external 100Ω resistor.

Pin Connections

SUM PORT 2


PORT 1 6

PORT 2 4

GROUND 1,3,5

PORT 1-2 resistor external 100 OHMS

Outline Drawing




Outline Dimensions (inch)

A	B	C	D	E	F
.126	.063	.037	.024	.022	.012
3.20	1.60	0.94	0.61	0.56	0.30

G	H	J	K	wt
.039	.042	.024	.123	grams
0.99	1.07	0.61	3.12	.020

Demo Board MCL P/N: TB-252 Suggested PCB Layout (PL-129)



Features

- isolation resistor, external 100 ohms
- low insertion loss, 0.4 dB typ.
- excellent amplitude unbalance, 0.1 dB typ.
- excellent phase unbalance, 0.8 deg. typ.
- high isolation, 28 dB typ.
- excellent power handling, 4W as splitter
- small size, 0.12"X0.06"X0.035"
- ESD non-sensitive
- temperature stable LTCC technology
- wrap around terminations for excellent solderability
- low cost
- patent pending

Applications




- amateur radio
- defense
- wireless communication

Splitter Electrical Specifications

MODEL NO.	FREQUENCY (MHz)	INSERTION LOSS (dB) ABOVE 3.0 dB		ISOLATION (dB)	PHASE UNBALANCE (Degrees)	AMPLITUDE UNBALANCE (dB)	RETURN LOSS (dB)	
		Typ.	Max.	Typ. Min.	Typ. Max.	Typ. Max.	INPUT Typ.	OUTPUT Typ.
SCN-2-35(+)	2825-3700	0.4	1.3	22 13	1.0 4.0	0.1 0.3	18	20
	3200-3500	0.4	1.0	28 18	0.8 4.0	0.1 0.3	20	23

Typical Performance Data

Frequency (MHz)	Insertion Loss (dB)		Amplitude Unbalance (dB)	Isolation (dB)	Phase Unbalance (deg.)	Return Loss (dB)		
	S-1	S-2				S	1	2
2825.00	3.60	3.54	0.06	14.94	0.28	15.39	47.26	31.96
2900.00	3.58	3.52	0.05	15.70	0.22	16.46	41.52	34.99
3000.00	3.54	3.48	0.05	17.02	0.21	18.99	33.34	47.87
3100.00	3.51	3.46	0.05	18.47	0.17	21.86	29.16	39.50
3200.00	3.50	3.45	0.05	20.26	0.14	26.24	25.93	31.34
3300.00	3.50	3.46	0.04	22.71	0.14	30.10	23.20	26.54
3450.00	3.54	3.51	0.04	27.85	0.12	21.96	20.06	21.98
3500.00	3.57	3.53	0.04	29.97	0.13	20.04	19.24	20.75
3550.00	3.60	3.55	0.04	31.81	0.11	18.22	18.51	19.70
3575.00	3.62	3.57	0.05	32.20	0.09	17.56	18.24	19.31
3600.00	3.63	3.58	0.05	32.06	0.06	17.00	17.98	18.95
3625.00	3.65	3.60	0.05	31.43	0.04	16.42	17.72	18.61
3650.00	3.66	3.62	0.05	30.50	0.01	15.80	17.43	18.26
3675.00	3.68	3.64	0.04	29.47	0.02	15.18	17.13	17.88
3700.00	3.70	3.66	0.04	28.52	0.03	14.65	16.85	17.50



electrical schematic

