



Price* : 123.00 USD



Main

Range of product	Preventa Safety detection
Product or component type	Guard switch
Component name	XCSPL
Material	Plastic
Head type	Turret head rotary lever
Insulation	Double insulated
Type of operator	Straight lever
Operator direction information	Centred
Electrical connection	Terminal
Contacts type and composition	1 NC + 1 NC
Contact operation	Slow-break
Clamping connection capacity	1 x 0.5...2 x 1.5 mm ² with or without cable end
Cable entry	1 entry tapped 1/2" NPT
Number of poles	2

Complementary

Cable outer diameter	0.28...0.39 in (7...10 mm)
Positive opening	With NC contact
Tripping angle	5 °
Mechanical durability	1000000 cycles
Minimum torque for tripping	0.89 lbf.in (0.1 N.m)
Positive opening minimum torque	2.21 lbf.in (0.25 N.m)
Contact code designation	A300, AC-15 (Ue = 120 V, Ie = 6 A)EN/IEC 60947-5-1 A300, AC-15 (Ue = 240 V, Ie = 3 A)EN/IEC 60947-5-1 Q300, DC-13 (Ue = 125 V, Ie = 0.55 A)EN/IEC 60947-5-1 Q300, DC-13 (Ue = 250 V, Ie = 0.27 A)EN/IEC 60947-5-1

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

[Ithe] conventional enclosed thermal current	10 A
[Ui] rated insulation voltage	300 VUL 508 300 VCSA C22.2 No 14 500 V 3)EN/IEC 60947-1
[Uimp] rated impulse withstand voltage	6 kV EN/IEC 60947-5-1
Maximum resistance across terminals	30 mOhm EN/IEC 60947-5-4
Short-circuit protection	10 A cartridge fuse gG (gl)
Safety level	Can reach category 4 with the appropriate monitoring system and correctly wired EN/ISO 13849-1 Can reach PL = e with the appropriate monitoring system and correctly wired EN/ISO 13849-1 Can reach SIL 3 with the appropriate monitoring system and correctly wired IEC 61508
Safety reliability data	B10d = 5000000 value given for a life time of 20 years limited by mechanical or contact wear
Enclosure material	Polyamide PA66 fibre glass impregnated
Lever material	Stainless steel
Width	1.18 in (30 mm)
Height	6.34 in (161 mm)
Maximum Depth	1.18 in (30 mm)
Net weight	0.21 lb(US) (0.095 kg)

Environment

Standards	EN/IEC 60947-5-4 EN/ISO 12100 EN/IEC 60204-1 CSA C22.2 No 14 EN/IEC 60947-5-1 UL 508 EN 1088/ISO 14119
Product certifications	CSA UL BG
Protective treatment	TC TH
Ambient air temperature for operation	-13...158 °F (-25...70 °C)
Ambient air temperature for storage	-40...158 °F (-40...70 °C)
Vibration resistance	50 gn 10...500 Hz)IEC 60068-2-6
Shock resistance	50 gn 11 ms IEC 60068-2-27
Electrical shock protection class	Class II EN/IEC 61140
IP degree of protection	IP67 IEC 60529

Ordering and shipping details

Category	22411 - LIMIT SWITCHES,IEC,XCKJ
Discount Schedule	T
GTIN	00785901866596
Nbr. of units in pkg.	1
Package weight(Lbs)	1 lb(US) (0.45 kg)
Returnability	No
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.26 in (3.2 cm)
Package 1 width	7.87 in (20 cm)
Package 1 Length	1.50 in (3.8 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
--------------------------	-----------------------

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information

Contractual warranty

Warranty	18 months
----------	-----------