







AMPOWER is a registered trademark of AMP Incorporated.

|     |      |           |     |                           |         |     |      |
|-----|------|-----------|-----|---------------------------|---------|-----|------|
| LOC | DIST | REVISIONS |     |                           |         |     |      |
| GP  | 00   | P         | LTR | DESCRIPTION               | DATE    | DWN | APVD |
|     |      |           | S   | REVISED PER ECO-12-005621 | 05SEP12 | KH  | DO   |



- 1 HOUSING MAT'L: POLYESTER
- 2 HOUSING MAT'L: POLYESTER HIGH TEMP
- 3 HOLE DIAMETER AFTER PLATING.
- 4 SOLDER TAIL: TIN-LEAD OVER NICKEL
- 5 SOLDER TAIL: SILVER OVER NICKEL
- 6 PRODUCT AND PROCESSING MUST MEET REQUIREMENTS OF TYCO ELECTRONICS STANDARD 230-702.



|                                                                                       |              |                                                                                       |             |                            |            |
|---------------------------------------------------------------------------------------|--------------|---------------------------------------------------------------------------------------|-------------|----------------------------|------------|
| OBSOLETE                                                                              | WITH EYELETS |  | 5.72 [.225] | 1.57 [.062] TO 4.75 [.187] | 2-765206-2 |
| OBSOLETE                                                                              | WITH EYELETS |  | 4.19 [.165] | 1.57 [.062] TO 3.17 [.125] | 2-765206-1 |
|  | WITH EYELETS |  | 3.15 [.124] | 1.57 [.062] TO 2.36 [.093] | 2-765206-0 |
|  | W/O EYELETS  |  | 5.72 [.225] | 1.57 [.062] TO 4.75 [.187] | 1-765206-9 |
|  | W/O EYELETS  |  | 4.19 [.165] | 1.57 [.062] TO 3.17 [.125] | 1-765206-8 |
|  | W/O EYELETS  |  | 3.15 [.124] | 1.57 [.062] TO 2.36 [.093] | 1-765206-7 |
| OBSOLETE                                                                              |              |                                                                                       | 5.72 [.225] | 4.75 [.187]                | 1-765206-6 |
| OBSOLETE                                                                              |              |                                                                                       | 7.49 [.295] | 6.35 [.250]                | 1-765206-5 |
| OBSOLETE                                                                              |              |  | 4.19 [.165] | 3.17 [.125]                | 1-765206-4 |
|                                                                                       | WITH EYELETS |  | 3.15 [.124] | 1.57 [.062] TO 2.36 [.093] | 1-765206-3 |
| OBSOLETE                                                                              |              |                                                                                       | 5.72 [.225] | 4.75 [.187]                | 1-765206-2 |
| OBSOLETE                                                                              |              |  | 7.49 [.295] | 6.35 [.250]                | 1-765206-1 |
| OBSOLETE                                                                              |              |  | 4.19 [.165] | 3.17 [.125]                | 1-765206-0 |
| OBSOLETE                                                                              |              |                                                                                       | 3.15 [.124] | 1.57 [.062] TO 2.36 [.093] | 765206-9   |
| OBSOLETE                                                                              |              |                                                                                       | 5.72 [.225] | 4.75 [.187]                | 765206-8   |
| OBSOLETE                                                                              |              |                                                                                       | 7.49 [.295] | 6.35 [.250]                | 765206-7   |
|                                                                                       |              |  | 4.19 [.165] | 3.17 [.125]                | 765206-6   |
| OBSOLETE                                                                              | W/O EYELETS  |                                                                                       | 3.15 [.124] | 1.57 [.062] TO 2.36 [.093] | 765206-5   |
| OBSOLETE                                                                              |              |                                                                                       | 5.72 [.225] | 4.75 [.187]                | 765206-4   |
| OBSOLETE                                                                              |              |                                                                                       | 7.49 [.295] | 6.35 [.250]                | 765206-3   |
|                                                                                       |              |  | 4.19 [.165] | 3.17 [.125]                | 765206-2   |
|                                                                                       |              |  | 3.15 [.124] | 1.57 [.062] TO 2.36 [.093] | 765206-1   |
|                                                                                       |              | MATERIAL                                                                              | U           | BOARD THICKNESS            |            |

RECOMMENDED PC BOARD LAYOUT  
2.54 [ .100 ] CENTERLINES

|                                                                                                                |  |                                                                                                                                                                       |  |                                                                                                       |  |
|----------------------------------------------------------------------------------------------------------------|--|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|-------------------------------------------------------------------------------------------------------|--|
| THIS DRAWING IS A CONTROLLED DOCUMENT.                                                                         |  | DWN J.K. DALY 12-08-89<br>CHK CMS 12-14-89<br>APD -                                                                                                                   |  |  TE Connectivity |  |
| DIMENSIONS:<br>INCHES<br> |  | TOLERANCES UNLESS OTHERWISE SPECIFIED:<br>0 PLC ± -<br>2 PLC ± -<br>3 PLC ± 0.05 [.01]<br>4 PLC ± 0.13 [.005]<br>FINISH ± -<br>SILVER ON MATING END, ALL OVER NICKEL. |  | NAME<br>AMPPOWER Wave Crimp System<br>VERTICAL Hopper Assembly<br>2.54 [.100] CENTERLINES             |  |
| MATERIAL<br>CONTACT, COPPER ALLOY                                                                              |  | WEIGHT<br>-                                                                                                                                                           |  | SIZE<br>A1                                                                                            |  |
|                                                                                                                |  | CUSTOMER DRAWING                                                                                                                                                      |  | DRAWING NO<br>C-765206                                                                                |  |
|                                                                                                                |  |                                                                                                                                                                       |  | SCALE 4:1<br>SHEET 1 of 1<br>REV S                                                                    |  |