

Sunday, 02 December 2012

**HIRSCHMANN®**
Test & Measurement
A BRAND OF SKS

www.sks-kontakt.de

News

contact

sitemap

Login

main menu

[home](#)
[products](#)
[skills](#)
[download](#)

online catalogue T&M

[clamp-type test probes](#)
[crocodile clips](#)
[test probes](#)
 ▶ 0,64 mm system
 ▶ 2 mm system
 ▶ 4 mm system
 ▶ 4 mm sliding sleeve system
 ▶ 4 mm safety system
[oscilloscope test probes](#)
[measuring leads](#)
[plugs](#)
[sockets](#)
[sets](#)
[miscellaneous](#)

company

[portrait](#)
[corporate association](#)
[location maps](#)
[fairs and exhibitions](#)
[jobs](#)
[imprint](#)
[terms and conditions](#)[Home](#) ▶ [test probes](#) ▶ [test probes](#) ▶ [PRUEF 1](#)

PRUEF 1

datasheet for PRUEF 1
article number: 931376101[View Full-Size Image](#)

search online catalogue

Search

Messetermine

No events

Newsletter Anmeldung

☒ Test &

Measurement

 First Name Name E-mail

QR-Code



product description:	order number: 931 376-101
description:	Miniature test probe for sampling extremely small measuring points. Shatter-proof grip, may be unscrewed. The stainless steel tip easily penetrates insulation and oxide layers. Solder connection up to 0.5 mm ² .
typ:	PRUEF 1 rot / red
system:	2mm system
order number:	931 376-101
color	
other color versions:	
technical data	
measurement category acc. to IEC 61010:	CAT I
norm	IEC 61010
pin dimensions	1 mm
type of contact:	test tip (unsprung)
type of termination:	solder
rated voltage:	30 VAC / 60 VDC
rated current:	1 A
Please consider derating curve!	
contact resistance:	50 mOhm
material	
contact material:	tip: stainless steel contact part: brass
contact surface material:	nickel
housing material:	PVC - P
environmental conditions:	
temperature range:	-25 °C to +60 °C
drawing	

© 2012 www.sks-kontakt.de

Joomla! is Free Software released under the GNU General Public License.