




F

E

D

C

B

A

F



E

D

C

B

A



SPECIFICATIONS:

- Material:
 - Body: PA46
 - Pin: Brass
- Wire range: N/A
- Electrical rating: 300V, 15A.
- Wire strip length: N/A
- Operating temperature: -40C to +140C.
- Max torque: N/A
- Insulation resistance: DC 500V, 500M.
- Dielectric withstand: AC 2500V for 1 minute.
- Breakdown voltage: 4000V.
- $A = (N \times P) + 2.0\text{mm}$
- $B = (N - 1) \times P$
- $P \text{ (PITCH)} = 5.0\text{mm} \text{ (.197")}$.
- N = Number of positions available 2 through 24.

ENTER DESCRIPTION EC NO: NEO2006-0310 DRAWN: LROTHAUS 2006/01/09 CHKD: CYORK 2006/01/09 APPR: JPAWLICK 2006/01/10 A	DESCRIPTION QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN		SCALE 4:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION		
			mm	INCH	DRAWN BY LROTHAUS	DATE 12/6/05	5.0MM, EURO HEADER, RIGHT ANGLE, HI-TEMP			
		4 PLACES	± ---	±.0015	CHECKED BY C. YORK	DATE 01/06/06				
		3 PLACES	± 0.038	±.005	APPROVED BY	DATE				
		2 PLACES	± 0.13	±.01	molex MOLEX INCORPORATED		MATERIAL NO. DOCUMENT NO. SD-39522-001		SHEET NO. 1 OF 1	
		1 PLACE	± 0.3	± ---						
		ANGULAR ± 2 °								
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE B	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							

