





FRONT VIEW
FEMALE INSERT CONFIGURATION CHART




POLE	MATERIAL NO.	ENGINEERING NO.	FINISHED LENGTH
3	120070	8R3000A16A120	12.0" +.75-0 (.3M +19mm-0)
4	1200700170	8R4000A16M020	6'7"+3.50"-0 (2M +88.9mm-0)
5	1200700246	8R5000A16M010	3'3"+2.19"-0 (1M +55.6mm-0)



CONNECTOR SPECIFICATION:

VOLTAGE RATING 3 - 4 PIN	250V per IEC 60664
VOLTAGE RATING 5 PIN	60V per IEC 60664 250V per UL 2238
AMPERAGE RATING	4 AMPS
PROTECTION	IP67
OPERATING TEMPERATURE	-20°C TO 80°C
UL CERTIFICATIONS	UL LISTED, FILE NO. E152210
CSA CERTIFICATIONS	CSA CERTIFIED, FILE NO. LR6837



KNOCKOUT HOLE

ITEM	COMPONENT	MATERIAL	FINISH
7	LABEL	MYLAR	BLACK/YELLOW
6	LOCKNUT	STEEL	ZINC PLATED
5	O-RING	VITON	BLACK
4	CONTACT SOCKET	COPPER ALLOY	GOLD OVER NICKEL
3	SHELL FM M12x1	DIE CAST ZINC	NICKEL PLATED
2	MALE INSERT	NYLON	BLACK
1	CONDUCTOR- 18 AWG 3-5 CONDUCTOR 300V	PVC	SEE WIRING DIAGRAMM

NEW SALES DOC				QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE		DESIGN UNITS		THIRD ANGLE PROJECTION	
EC NO: IPG2017-0318 DRWN: BBRAUCH 2016/09/21 CHKD: RSILLER 2016/09/21 APPR: RSILLER 2013/02/07								INCH/MM		4:1		INCH		 THIRD ANGLE PROJECTION	
								DRAWN BY DATE		TITLE MICRO CHANGE RECEPTACLE 3-5 POLE FEMALE #18/3-5 AWG PVC WIRING MOLEX INCORPORATED					
								RSTONE 2012/11/05							
								CHECKED BY DATE							
								K JOZWIK 2012/11/28							
								APPROVED BY DATE							
		JFMURPHY 2013/02/07													