




MATERIAL NUMBER	OLD PART NUMBER	FINISHED LENGTH	MATERIAL CABLE	CABLE COLOR
1201140067	BTY801P-FBE-02	6.56' +3.50" -0 [2.0M +88.9 -0]	PVC	YELLOW
1201140068	BTY801P-FBE-05	16.40' +6.50" -0 [5.0M +165.1 -0]	PVC	YELLOW
1201140069	BTY801P-FBE-10	32.81' +12.50" -0 [10.0M +317.5 -0]	PVC	YELLOW
1201140070	BTY801P-FBE-15	49.21' +24.50" -0 [15.0M +622.3 -0]	PVC	YELLOW
1201140071	BTY801P-FBE-20	65.62' +24.50" -0 [20.0M +622.3 -0]	PVC	YELLOW
1201140072	BTY801P-FBP-05	16.40' +6.50" -0 [5.0M +165.1 -0]	PUR	BLACK
1201140073	BTY801P-FBP-10	32.81' +12.50" -0 [10.0M +317.5 -0]	PUR	BLACK
1201140074	BTY801P-FBP-15	49.21' +24.50" -0 [15.0M +622.3 -0]	PUR	BLACK
1201140075	BTY801P-FBP-20	65.62' +24.50" -0 [20.0M +622.3 -0]	PUR	BLACK
1201140076	BTY801P-FBP-25	82.02' +24.50" -0 [25.0M +622.3 -0]	PUR	BLACK
1201140077	BTY801P-FBP-30	98.43' +24.50" -0 [30.0M +622.3 -0]	PUR	BLACK
1201140078	BTY801P-FBP-50	164.04' +24.50" -0 [50.0M +622.3 -0]	PUR	BLACK



ITEM	COMPONENT	MATERIAL	FINISH
1	INSERT	NYLON	BLACK
2	CONTACT SOCKET	COPPER ALLOY	GOLD OVER NICKEL
3	O-RING	VITON	RED
4	RECEPTACLE SHELL	BRASS	NICKEL PLATED
5	HOUSING	PBT	YELLOW
6	LABEL	ABS	WHITE
7	LENS	NYLON	CLEAR
8	CABLE, 18AWG, 3 CONDUCTOR, 22AWG, 8 CONDUCTOR, 300V	SEE TABLE	SEE TABLE

ADD 2 PINS TO TABLE

EC NO: WEU2010-0441

DRWN: BBRAUCH

CH'KD: BWOODMAN

APPR: FPACHER

16.03.10

2010/03/19

REV

QUALITY SYMBOL

=0

=0

GENERAL TOLERANCES (UNLESS SPECIFIED)

	mm	INCH
4 PLACES	±---	±---
3 PLACES	±---	±---
2 PLACES	±---	±.01
1 PLACE	±0.3	±---

ANGULAR ±---°

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

DIMENSION STYLE

IN/MM

DRAWN BY

DATE

CHECKED BY

DATE

APPROVED BY

DATE

MATERIAL NO.

SIZE

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

SCALE

NTS

DESIGN UNITS

METRIC

THIRD ANGLE PROJECTION

TITLE

MICRO-CHANGE MPIS

8 PORT TOP MOUNT PNP

#18/3 + #22/8 CABLE

MOLEX INCORPORATED

DOCUMENT NO.

SD-120114-006

SHEET NO.

1 OF 1