


H-Series



The H-Series toggle switches are heavy-duty, high voltage, high amperage, three-pole switches. These switches have a slow-make, slow-break contact mechanism, are AC rated to 600V, and are available in a wide range of ratings, circuits, terminations and bushing/toggle configurations.

- Specifications
- Certifications*: UL, CSA,
 - Dielectric Strength: 1,000 V (minimum)
 - Insulation Resistance: 100 Megohms (minimum)
 - Base Material: Phenolic
 - Actuator Material: Brass/Nickel Plate or Polycarbonate
 - Bushing Material: Brass/Nickel Plate

* Due to ongoing technological advances, consult factory for certification specifics.



H		K		25		1		-		73	
SERIES		CIRCUIT ¹		TERMINATION/FUNCTION							
H THREE POLE TOGGLE		K ON-NONE-OFF									
		L ON-NONE-ON									
		M ON-OFF-ON									

NOTES:
Shading indicates standard configurations.
For bushing accessories, see pages 69 and 70.
1 Consult factory for additional circuits.
2 Nylon toggles are available with 4-pole base only.
NBL toggle uses black oxide plated metal bushing for standard construction. NWH toggle uses nickel plated metal bushing for standard construction.

TOGGLE STYLE²

	TOGGLE LENGTH	BUSHING LENGTH	SUFFIX NO.	NEOPRENE SEAL
BAT	.687	.465	73	78
	1.25	.343	B2	---
NYLON	.687	.465	NBL3 NWH3	NBL8 NWH8