

# 3M™ Twisted Pair Flat Cable

.050" 28 AWG Stranded, Mass Terminatable, PVC

3782 Series



- Combines the advantages of loose twisted pairs with flat section parts for mass termination
- Loose twisted pairs allow for easy routing
- Twisted pairs help reduce crosstalk for balanced drive applications
- Zippable for branching or discrete termination
- Wires are color-coded for easy identification
- See the Regulatory Information Appendix (RIA) in the "RoHS compliance" section of [www.3Mconnector.com](http://www.3Mconnector.com) for compliance information (RIA E1 & C1 apply)

Date Modified: October 7, 2019

TS-0999-F  
Sheet 1 of 2

## Physical

**Insulation Material:** Polyvinyl Chloride (PVC)

Color: 10 Color Repeat with White Common

**Marking:**

Standard: None

**Conductors:** 28 AWG, 7 x 36 AWG [ 7 x  $\phi$  0.127 mm] Tinned Stranded Copper

---

## Electrical

**Voltage Rating:** USA: 300V EU: <50V

**Insulation Resistance:**  $> 1 \times 10^{10} \Omega/10 \text{ ft.} [ 3 \text{ m} ]$

<b>Characteristic Impedance:</b>	<b>Unbalanced</b> 103 $\Omega$	<b>Balanced</b> 137 $\Omega$
----------------------------------	-----------------------------------	---------------------------------

**Capacitance:** 14.8 pF/ft [ 48.5 pF/m ] 11.1 pF/ft [ 36.3 pF/m ]

**Inductance:** 0.16  $\mu\text{H}/\text{ft}$  [ 0.52  $\mu\text{H}/\text{m}$  ] 0.21  $\mu\text{H}/\text{ft}$  [ 0.69  $\mu\text{H}/\text{m}$  ]

**Propagation Delay:** 1.52 ns/ft [ 4.99 ns/m ] 1.52 ns/ft [ 4.99 ns/m ]

**Velocity of Propagation:** 67% 67%

Note: Unbalanced is measured between ground-signal-ground conductors. Balanced is measured between signal conductors within a pair.

---

## Environmental

**Temperature Rating:** USA: -20° C to +80° C

**Flammability Rating:** USA: VW-1

---

UL File No.: E42769, Style No.: 20488

**3M**

Electronics Materials Solutions Division

Interconnect Solutions

<http://www.3M.com/interconnect>


3M is a trademark of 3M Company.  
For technical, sales or ordering information call  
**800-225-5373**

# 3M™ Twisted Pair Flat Cable


.050" 28 AWG Stranded, Mass Terminatable, PVC

3782 Series

Number of Pairs	3M Part Number	Dimension A	Dimension B
5	3782-5P-XXXX 100FT	0.50 [12.70]	0.450 ± .010 [ 11.43 ]
7	3782-7P-XXXX 100FT	0.70 [17.80]	0.650 ± .010 [ 16.51 ]
8	3782-8P-XXXX 100FT	0.80 [20.30]	0.750 ± .010 [ 19.50 ]
10	3782-10P-XXXX 100FT	1.00 [25.40]	0.950 ± .020 [ 24.13 ]
12	3782-12P-XXXX 100FT	1.20 [30.50]	1.150 ± .020 [ 29.21 ]
13	3782-13P-XXXX 100FT	1.30 [33.00]	1.250 ± .020 [ 31.75 ]
17	3782-17P-XXXX 100FT	1.70 [43.20]	1.650 ± .020 [ 41.91 ]
20	3782-20P-XXXX 100FT	2.00 [50.80]	1.950 ± .020 [ 49.53 ]
25	3782-25P-XXXX 100FT	2.50 [63.50]	2.450 ± .020 [ 62.23 ]
32	3782-32P-XXXX 100FT	3.20 [81.30]	3.150 ± .020 [ 80.01 ]



\* 10 Color Repeat  
 Brown/White  
 Red/White  
 Orange/White  
 Yellow/White  
 Green/White  
 Blue/White  
 Violet/White  
 Gray/White  
 Pink/White  
 Black/White



Tolerance Unless Noted			
	.0	.00	.000
Inch	±.1	±.01	±.005

[ ] Dimensions for Reference Only

Note:

1. Brown conductor indicates conductor number 1.

2. RIA E1 & C1 apply for all cables listed

## Ordering Information

**3782-XXP-XXXX**

270 = 270 mm repeat

Number of Pairs  
(See Table)

Note: Available in standard 100 ft rolls. Contact 3M for availability of additional conductor counts and/or custom roll lengths.

TS-0999-F  
Sheet 2 of 2

**3M**

Electronics Materials Solutions Division  
 Interconnect Solutions  
<http://www.3M.com/interconnect>

3M is a trademark of 3M Company.  
 For technical, sales or ordering information call  
**800-225-5373**

Regulatory: For regulatory information about this product, visit 3M.com/regs or contact your 3M representative.

Technical Information: The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed.

Product Use: Many factors beyond 3M's control and uniquely within user's control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.

Warranty, Limited Remedy, and Disclaimer: Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OR TRADE.

If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.

3M Business Center  
Electronics Materials Solutions Division  
13011 McCallen Pass, Bldg. C  
Austin, TX 78753-5380  
1-800-225-5373  
[www.3M.com/interconnect](http://www.3M.com/interconnect)



**Electronics Materials Solutions Division**  
**Interconnect Solutions**  
<http://www.3M.com/interconnect>

Please recycle. Printed in USA.  
© 3M 2019. All rights reserved.  
RIA-2217B-E

3M is a trademark of 3M Company.