



MATERIALS

CONNECTORS	PASSIVATED STAINLESS STEEL
CONTACT	GOLD PLATED
INSULATOR	PTFE
HEAT SINK	ANODIZED ALUMINUM
COUPLING NUT	BRASS NICKEL PLATED



SPECIFICATIONS

FREQUENCY RANGE: DC TO 18 GHz
 ATTENUATION: 40 dB
 IMPEDANCE: 50 OHMS
 ACCURACY: ± 2.0 dB
 VSWR: 1.45:1 MAXIMUM
 AVG. POWER HANDLING CAPABILITY: 50 WATTS



PASTERNACK ENTERPRISES, INC.

P.O BOX 16759, IRVINE, CA 92623
 PHONE (949) 261-1920 FAX (949) 261-7451

WEB ADDRESS: www.pasternack.com
 E-MAIL ADDRESS: sales@pasternack.com

COAXIAL & FIBER OPTICS

DWG TITLE

PE7020-40

DES.

SMA ATTENUATOR 50 WATTS FREQUENCY
 RANGE: DC TO 18 GHz

SIZE A

FSCM NO. 53919

CAD FILE

042005

SCALE N/A

127

NOTES:

1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.