


4

3

2

1


LOC	DIST	REVISIONS				
GP	00	P	LTR	DESCRIPTION	DATE	APVD
			B	REVISED PER RTS 645225	03/MAY/12	ECC JDM



1. PRODUCT AND PROCESSING MUST MEET REQUIREMENTS OF
TE CONNECTIVITY STANDARD TEC-138-702.
2. CABLE ASSEMBLY TO BE 100% ELECTRICALLY TESTED FOR OPENS,
SHORTS AND CONTINUITY.

HI-HOT: 200 VDC FOR 100ms
INSULATION RESISTANCE: 500M OHMS MIN
CONTINUITY RESISTANCE: 2 OHMS MAX
FREQUENCY RANGE: DC TO 6 GHz
VSWR: 1.5:1 MAX

2.0	26.0	2015698-8
2.0	140.0	2015698-5
2.0	50.0	2015698-4
3.0	200.0	2015698-3
2.0	100.0	2015698-2
2.0	39.0	2015698-1
"T" TOLERANCE	"A" LENGTH	TE P/N

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN E.C. CLAYBAUGH 18/DEC/07		 TE Connectivity							
DIMENSIONS: mm		CHK J. ORNER 18/DEC/07		NAME CABLE ASSY, UMCC R/A TO UMCC R/A, TYPE II, 0.80mm CABLE —							
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD J. ORNER 18/DEC/07								
	0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± —		PRODUCT SPEC —								
MATERIAL —		FINISH —		APPLICATION SPEC —		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
				WEIGHT —		A3	00779	C-2015698	—		
CUSTOMER DRAWING						SCALE	N.T.S.	SHEET	1 OF 1	REV	B