


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
G	14		L3	REVISED PER ECO-11-013501	30JUN11	HMR	DR

AMP

WIRE RANGE

8 AWG
SOLID OR STRANDED



- 1
- STAMP AMP 8W* APPROX AS SHOWN

2

3

4

5

6

7

8

9

10

4 5	25	LOOSE PIECE	170°C[338°F]	6	8-34318-3
4 5	1000	LOOSE PIECE	170°C[338°F]	6	2-34318-3
---	100	LOOSE PIECE	343°C[650°F]	7	2-34318-1
---	100	LOOSE PIECE	260°C[500°F]	9	34318-3
---	100	LOOSE PIECE	170°C[338°F]	8	34318-1
4 5	500	LOOSE PIECE	170°C[338°F]	6	34318
APPROVALS		QTY	PACKAGE TYPE	MAX OPERATING TEMP	PART NO
THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN TA BRINKMAN 4-5-93	TE Connectivity	
DIMENSIONS: mm [INCHES]			CHK DA PATTERSON 4-5-93		
TOLERANCES UNLESS OTHERWISE SPECIFIED:			APVD DA PATTERSON 4-5-93	NAME SPLICE, PARALLEL, SOLISTRAND	
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -			PRODUCT SPEC		
FINISH			APPLICATION SPEC	SIZE A2 CAGE CODE 00779 DRAWING NO C-34318 RESTRICTED TO -	
MATERIAL - 3			WEIGHT -		
CUSTOMER DRAWING				SCALE 10:1	SHEET 1 OF 1
				REV L3	

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: SEE TABLE
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: N/A
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	CIRCULAR MIL AREA: 6.64-10.5mm²[13,100-20,800] SOLID OR STRANDED
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.