

MC10129

Quad Bus Receiver

The MC10129 data inputs are compatible with, and accept TTL logic levels as well as levels compatible with IBM-type buses. The clock, strobe, and reset inputs accept MECL 10,000 logic levels.

The data inputs accept the bus levels, and storage elements are provided to yield temporary latch storage of the information after receiving it from the bus. The outputs can be strobed to allow accurate synchronization of signals and/or connection to MECL 10,000 level buses. When the clock is low, and the reset input is disabled, the outputs will follow the D inputs. The latches will store the data on the rising edge of the clock. The outputs are enabled when the strobe input is high. Unused D inputs must be tied to V_{CC} or Gnd. The clock, strobe, and reset inputs each have 50 k ohm pulldown resistors to V_{EE} . They may be left floating, if not used.

The MC10129 will operate in either of two modes. The first mode is obtained by tying the hysteresis control input to V_{EE} . In this mode, the input threshold points of the D inputs are fixed. The second mode is obtained by tying the hysteresis control input to ground. In this mode, input hysteresis is achieved as shown in the test table. This hysteresis is desirable where extra noise margin is required on the D inputs. The outer input pins are unaffected by the mode of operation used.

The MC10129 is especially useful in interface applications for central processors, mini-computers, and peripheral equipment.


- $P_D = 750$ mW typ/pkg (No Load)
- $t_{pd} = 10$ ns typ
- V_{CC} Max = 7.0 Vdc





ON Semiconductor

<http://onsemi.com>


MARKING DIAGRAMS




**CDIP-16
L SUFFIX
CASE 620**



**PDIP-16
P SUFFIX
CASE 648**



**PLCC-20
FN SUFFIX
CASE 775**





A = Assembly Location
WL = Wafer Lot
YY = Year
WW = Work Week

ORDERING INFORMATION

Device	Package	Shipping
MC10129L	CDIP-16	25 Units / Rail
MC10129P	PDIP-16	25 Units / Rail
MC10129FN	PLCC-20	46 Units / Rail

MC10129



Pin assignment is for Dual-in-Line Package.
For PLCC pin assignment, see the Pin Conversion
Tables on page 18 of the ON Semiconductor MECL
Data Book (DL122/D).

TRUTH TABLE

D	C	STROBE	RESET	Q _n + 1
X	X	L	X	L
X	H	X	H	L
L	L	H	X	L
X	H	H	L	Q _n
H	L	H	X	H

ELECTRICAL CHARACTERISTICS

Characteristic	Symbol	Pin Under Test	Test Limits							Unit
			−30°C		+25°C			+85°C		
			Min	Max	Min	Typ	Max	Min	Max	
Negative Power Supply Drain Current	I _E	8 8		167 189			152 172		167 189	mAdc
Positive Power Supply Drain Current	I _{CC}	9		8.0			8.0		8.0	mAdc
Input Current	I _{inH}	4		150			95		95	μAdc
		6		150			95		95	
		7		150			95		95	
		10		720			450		450	
		11		390			245		245	
		12		390			245		245	
		13		150			95		95	
	I _{CBO} (1.)	4		1.5			−1.0		1.0	μAdc
		6		1.5			−1.0		1.0	
7			1.5			−1.0		1.0		
13				−1.0						
I _{inL}	10		0.5		0.5			0.3	μAdc	
	11		0.5		0.5			0.3		
	12		0.5		0.5			0.3		
Output Voltage Logic 1	V _{OH}	2	−1.060	−0.890	−0.960		−0.810	−0.890	−0.700	Vdc
		3	−1.060	−0.890	−0.960		−0.810	−0.890	−0.700	
		2	−1.060	−0.890	−0.960		−0.810	−0.890	−0.700	
		3	−1.060	−0.890	−0.960		−0.810	−0.890	−0.700	
Output Voltage Logic 0	V _{OL}	2	−1.890	−1.675	−1.850		−1.650	−1.825	−1.615	Vdc
		3	−1.890	−1.675	−1.850		−1.650	−1.825	−1.615	
		2	−1.890	−1.675	−1.850		−1.650	−1.825	−1.615	
		3	−1.890	−1.675	−1.850		−1.650	−1.825	−1.615	
Threshold Voltage Logic 1	V _{OHA}	2 (2.)	−1.080		−0.980			−0.910		Vdc
		2	−1.080		−0.980			−0.910		
		2	−1.080		−0.980			−0.910		
		2	−1.080		−0.980			−0.910		
		2 (3.)	−1.080		−0.980			−0.910		
		2 (4.)	−1.080		−0.980			−0.910		
Threshold Voltage Logic 0	V _{OLA}	2 (2.)		−1.655			−1.630		−1.595	Vdc
		2		−1.655			−1.630		−1.595	
		2 (2.)		−1.655			−1.630		−1.595	
		2		−1.655			−1.630		−1.595	
		2 (3.)		−1.655			−1.630		−1.595	
		2 (4.)		−1.655			−1.630		−1.595	
Switching Times									ns	
Propagation Delay										
Data Input	t ₇₊₁₄₊	14	3.7	15	3.7	10	15	3.7		30
	t _{7−14−}	14	3.7	15	3.7	10	15	3.7		40
Clock Input	t _{11−14+}	14	2.7	11	2.7	5.0	9.0	2.7		11
	t _{11−14−}	14	2.7	11	2.7	5.0	9.0	2.7		11
Strobe Input	t ₁₂₊₁₄₊	14	1.6	8.0	1.6	4.0	7.0	1.6		8.0
	t _{12−14−}	14	1.6	8.0	1.6	4.0	7.0	1.6		8.0
Reset Input	t _{10+14−}	14	2.0	8.0	2.0	5.0	6.5	2.0		8.0
Hysteresis Mode	t ₇₊₁₄₊	14	6.6	30	6.7	18	25	6.6		30
	t _{7−14−}	14	3.7	17	3.7	10	15	3.7		40
Setup Time	t _{setup}	14	30		2.7	15		30		
Hold Time	t _{hold}	14	0		−2.0	15		−2.0		
Rise Time	t ₊	14	1.5	5.0	1.5	2.0	4.3	1.5		5.0
Fall Time	t _−	14	1.5	5.0	1.5	2.0	4.3	1.5		5.0

1. Pin 5 to V_{EE} , V_{IL} to Data input one at a time.

2. Output latched to logic high state prior to test. V_{IHA}' , V_{ILA}' are standard logic 1 and logic 0 M TTL threshold voltages. V_{IHA}'' , V_{ILA}'' , V_{IHA}''' and V_{ILA}''' are logic 1 and logic 0 threshold voltages in the hysteresis mode as shown in Figure 1 on page 3.

3. Input level on data input taken from +0.4V up to voltage level given.

4. Input level on data input taken from +4.0V down to voltage level given.

5. Operation and limits shown also apply for $V_{CC} = +6.0V$.




Figure 1. Hysteresis Mode Threshold Voltage

ELECTRICAL CHARACTERISTICS

@ Test Temperature			TEST VOLTAGE VALUES (Volts)								
			MECL 10,000 INPUT LEVELS				TTL INPUT LEVELS (6.)				
			V _{IHmax}	V _{ILmin}	V _{IHAmin}	V _{ILAmx}	V _{IH}	V _{IL}	V _{IHA'}	V _{ILA'}	
			−0.890	−1.890	−1.155	−1.500	3.000	0.400	2.000	0.800	
			−0.810	−1.850	−1.105	−1.475	3.000	0.400	2.000	0.800	
−30°C			−0.810	−1.850	−1.105	−1.475	3.000	0.400	2.000	0.800	
+25°C			−0.810	−1.850	−1.105	−1.475	3.000	0.400	2.000	0.800	
+85°C			−0.700	−1.825	−1.035	−1.440	3.000	0.400	2.000	0.800	
Characteristic	Symbol	Pin Under Test	TEST VOLTAGE APPLIED TO PINS LISTED BELOW								Gnd
			V _{IHmax}	V _{ILmin}	V _{IHAmin}	V _{ILAmx}	V _{IH}	V _{IL}	V _{IHA'}	V _{ILA'}	
Negative Power Supply Drain Current	I _E	8 8	11 11	12 12							1,5,16 1,16
Positive Power Supply Drain Current	I _{CC}	9						4,6,7,13			1,16
Input Current	I _{inH}	4 6 7 10 11 12 13	10,11 11 12				4 6 7 13				1,16 1,16 1,16 1,16 1,16 1,16 1,16
	I _{CBO} (1.)	4 6 7 13						4 6 7 13			1,16 1,16 1,16 1,16
	I _{inL}	10 11 12		10 11 12							1,16 1,16 1,16
Output Voltage Logic 1	V _{OH}	2	12	10,11			4				1,16
		3	12	10,11			6				1,16
		2	12	10,11			4				1,5,16
		3	12	10,11			6				1,5,16
Output Voltage Logic 0	V _{OL}	2	12	10,11				4			1,16
		3	12	10,11				6			1,16
		2	12	10,11				4			1,5,16
		3	12	10,11				6			1,5,16
Threshold Voltage Logic 1	V _{OHA}	2 (2.)	11,12			10	4				1,16
		2					4				1,16
		2	10,12		12				4		1,16
		2	12	10,11							1,16
		2 (3.)	12	10,11							1,5,16
2 (4.)	12	10,11								1,5,16	
Threshold Voltage Logic 0	V _{OLA}	2 (2.)	11,12		10		4				1,16
		2		10,11			4				1,16
		2 (2.)	10,12		11		4				1,16
		2	12	10,11						4	1,16
		2 (3.)	12	10,11							1,5,16
		2 (4.)	12	10,11							1,5,16
Switching Times Propagation Delay			+1.11V	+0.31V	Pulse In	Pulse Out	+5.0V	+2.40V	Figure	+2.0V	
Data Input	t ₇₊₁₄₊ t _{7−14−}	14 14	12	10,11	7	14			Figure 3	1,16	
			12	10,11	7	14			Figure 3	1,16	
Clock Input	t _{11−14+} t _{11−14−}	14 14	12	10	7,11	14			Figure 6	1,16	
			12	10	7,11	14			Figure 6	1,16	
Strobe Input	t ₁₂₊₁₄₊ t _{12−14−}	14 14		10,11	12	14	7		Figure 4	1,16	
				10,11	12	14	7		Figure 4	1,16	
Reset Input	t _{10+14−}	14	12		10,11	14	7	7	Figure 5	1,16	
Hysteresis Mode	t ₇₊₁₄₊ t _{7−14−}	14 14	12	10,11	7	14			Figure 3	1,5,16	
			12	10,11	7	14			Figure 3	1,5,16	
Setup Time	t _{setup}	14	12	10	7,11	14			Figure 7	1,16	
Hold Time	t _{hold}	14	12	10	7,11	14			Figure 7	1,16	
Rise Time	t ₊	14	12	10,11	7	14			Figure 3	1,16	
Fall Time	t _−	14	12	10,11	7	14			Figure 3	1,16	

1. Pin 5 to V_{EE}, V_{IL} to Data input one at a time.2. Output latched to logic high state prior to test. V_{IHA'}, V_{ILA'} are standard logic 1 and logic 0 MTTL threshold voltages. V_{IHA''}, V_{ILA''}, V_{IHA'''} and V_{ILA'''} are logic 1 and logic 0 threshold voltages in the hysteresis mode as shown in Figure 1 on page 3.

3. Input level on data input taken from +0.4V up to voltage level given.

4. Input level on data input taken from +4.0V down to voltage level given.

5. Operation and limits shown also apply for V_{CC} = +6.0V.

6. When testing, choose either TTL or IBM input levels.

ELECTRICAL CHARACTERISTICS

@ Test Temperature			TEST VOLTAGE VALUES (Volts)															
			IBM INPUT LEVELS (6.)				HYSTERESIS MODE											
			V _{IH}	V _{IL}	V _{IHA'}	V _{ILA'}	V _{IHA''}	V _{ILA''}	V _{IHA'''}	V _{ILA'''}	V _{CC} (5.)	V _{EE}						
			–30°C	3.11	0.150			2.90	2.00	2.20	1.30	+5.0		–5.2				
			+25°C	3.11	0.150	1.700	0.70	2.60	1.70	1.90	1.00	+5.0		–5.2				
+85°C	3.11	0.150			2.30	1.40	1.60	0.70	+5.0	–5.2								
Characteristic	Symbol	Pin Under Test	TEST VOLTAGE APPLIED TO PINS LISTED BELOW										Gnd					
			V _{IH}	V _{IL}	V _{IHA'}	V _{ILA'}	V _{IHA''}	V _{ILA''}	V _{IHA'''}	V _{ILA'''}	V _{CC} (5.)	V _{EE}						
Negative Power Supply Drain Current	I _E	8 8									9 9	8 5,8	1,5,16 1,16					
Positive Power Supply Drain Current	I _{CC}	9		4,6, 7,13							9 9	5,8 5,8	1,16 1,16					
Input Current	I _{inH}	4 6 7 10 11 12 13	4 6 7 13								9 9 9 9 9 9 9	8 8 8 8 8 8 8	1,16 1,16 1,16 1,16 1,16 1,16 1,16					
		I _{CBO} (1.)	4 6 7 13	4 6 7 13								9 9 9 9	8 8 8 8	1,16 1,16 1,16 1,16				
			I _{inL}	10 11 12									9 9 9	8 8 8	1,16 1,16 1,16			
				Output Voltage Logic 1	2 3 2 3	4 6 4 6								9 9 9 9	5,8 5,8 8 8	1,16 1,16 1,5,16 1,5,16		
		Output Voltage Logic 0			2 3 2 3	4 6 4 6								9 9 9 9	5,8 5,8 8 8	1,16 1,16 1,5,16 1,5,16		
			Threshold Voltage Logic 1		V _{OHA}	2 (2.) 2 2 2 2 (3.) 2 (4.)	4 4 4		4		4		4		9 9 9 9 9 9	5,8 5,8 5,8 5,8 8 8	1,16 1,16 1,16 1,16 1,5,16 1,5,16	
Threshold Voltage Logic 0	V _{OLA}			2 (2.) 2 2 (2.) 2 2 (3.) 2 (4.)		4 4 4		4		4		4		9 9 9 9 9 9	5,8 5,8 5,8 5,8 8 8	1,16 1,16 1,16 1,16 1,5,16 1,5,16		
		Switching Times Propagation Delay						Figure										
																+5.0V	+2.40V	
		Data Input		t ₇₊₁₄₊ t _{7–14–}		14 14			Figure 3 Figure 3							9 9	5,8 5,8	1,16 1,16
		Clock Input		t _{11–14+} t _{11–14–}		14 14			Figure 6 Figure 6							9 9	5,8 5,8	1,16 1,16
		Strobe Input	t ₁₂₊₁₄₊ t _{12–14–}	14 14	7 7		Figure 4 Figure 4							9 9	5,8 5,8	1,16 1,16		
Reset Input	t _{10+14–}	14	7		Figure 5							9	5,8	1,16				
Hysteresis Mode	t ₇₊₁₄₊ t _{7–14–}	14 14			Figure 3 Figure 3							9 9	8 8	1,5,16 1,5,16				
	t _{setup}	14			Figure 7							9	5,8	1,16				
Hold Time	t _{hold}	14			Figure 7							9	5,8	1,16				
Rise Time	t ₊	14			Figure 3							9	5,8	1,16				
Fall Time	t _–	14			Figure 3							9	5,8	1,16				

1. Pin 5 to V_{EE}, V_{IL} to Data input one at a time.2. Output latched to logic high state prior to test. V_{IHA'}, V_{ILA'} are standard logic 1 and logic 0 MTTL threshold voltages. V_{IHA''}, V_{ILA''}, V_{IHA'''} and V_{ILA'''} are logic 1 and logic 0 threshold voltages in the hysteresis mode as shown in Figure 1 on page 3.

3. Input level on data input taken from +0.4V up to voltage level given.


4. Input level on data input taken from +4.0V down to voltage level given.

5. Operation and limits shown also apply for V_{CC} = +6.0V.

6. When testing, choose either TTL or IBM input levels.

MC10129

Figure 2. SWITCHING TIME TEST CIRCUIT AND WAVEFORMS @ 25°C



NOTE: All power supplies and logic levels are shifted 2 volts positive.

Figure 3 – DATA to OUTPUT
(Clock and Reset are low, Strobe is high)




Figure 4 – STROBE to OUTPUT
(Data is high, Clock and Reset are low)




Figure 5 – RESET to OUTPUT
(Data and Strobe are high)




Figure 6 – CLOCK to OUTPUT
(Reset is low, Strobe is high)






Figure 7 – TSET UP AND THOLD WAVEFORMS



MC10129

PACKAGE DIMENSIONS

PLCC-20
FN SUFFIX
PLASTIC PLCC PACKAGE
CASE 775-02
ISSUE C




NOTES:

- DATUMS -L-, -M-, AND -N- DETERMINED WHERE TOP OF LEAD SHOULDER EXITS PLASTIC BODY AT MOLD PARTING LINE.
- DIMENSION G1, TRUE POSITION TO BE MEASURED AT DATUM -T-, SEATING PLANE.
- DIMENSIONS R AND U DO NOT INCLUDE MOLD FLASH. ALLOWABLE MOLD FLASH IS 0.010 (0.250) PER SIDE.
- DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
- CONTROLLING DIMENSION: INCH.
- THE PACKAGE TOP MAY BE SMALLER THAN THE PACKAGE BOTTOM BY UP TO 0.012 (0.300). DIMENSIONS R AND U ARE DETERMINED AT THE OUTERMOST EXTREMES OF THE PLASTIC BODY EXCLUSIVE OF MOLD FLASH, TIE BAR BURRS, GATE BURRS AND INTERLEAD FLASH, BUT INCLUDING ANY MISMATCH BETWEEN THE TOP AND BOTTOM OF THE PLASTIC BODY.
- DIMENSION H DOES NOT INCLUDE DAMBAR PROTRUSION OR INTRUSION. THE DAMBAR PROTRUSION(S) SHALL NOT CAUSE THE H DIMENSION TO BE GREATER THAN 0.037 (0.940). THE DAMBAR INTRUSION(S) SHALL NOT CAUSE THE H DIMENSION TO BE SMALLER THAN 0.025 (0.635).

DIM	INCHES		MILLIMETERS	
	MIN	MAX	MIN	MAX
A	0.385	0.395	9.78	10.03
B	0.385	0.395	9.78	10.03
C	0.165	0.180	4.20	4.57
E	0.090	0.110	2.29	2.79
F	0.013	0.019	0.33	0.48
G	0.050 BSC		1.27 BSC	
H	0.026	0.032	0.66	0.81
J	0.020	—	0.51	—
K	0.025	—	0.64	—
R	0.350	0.356	8.89	9.04
U	0.350	0.356	8.89	9.04
V	0.042	0.048	1.07	1.21
W	0.042	0.048	1.07	1.21
X	0.042	0.056	1.07	1.42
Y	—	0.020	—	0.50
Z	2 °	10 °	2 °	10 °
G1	0.310	0.330	7.88	8.38
K1	0.040	—	1.02	—


MC10129

PACKAGE DIMENSIONS



- NOTES:
1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
 2. CONTROLLING DIMENSION: INCH.
 3. DIMENSION L TO CENTER OF LEAD WHEN FORMED PARALLEL.
 4. DIMENSION F MAY NARROW TO 0.76 (0.030) WHERE THE LEAD ENTERS THE CERAMIC BODY.

DIM	INCHES		MILLIMETERS	
	MIN	MAX	MIN	MAX
A	0.750	0.785	19.05	19.93
B	0.240	0.295	6.10	7.49
C	—	0.200	—	5.08
D	0.015	0.020	0.39	0.50
E	0.050 BSC		1.27 BSC	
F	0.055	0.065	1.40	1.65
G	0.100 BSC		2.54 BSC	
H	0.008	0.015	0.21	0.38
K	0.125	0.170	3.18	4.31
L	0.300 BSC		7.62 BSC	
M	0°	15°	0°	15°
N	0.020	0.040	0.51	1.01



- NOTES:
1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
 2. CONTROLLING DIMENSION: INCH.
 3. DIMENSION L TO CENTER OF LEADS WHEN FORMED PARALLEL.
 4. DIMENSION B DOES NOT INCLUDE MOLD FLASH.
 5. ROUNDED CORNERS OPTIONAL.

DIM	INCHES		MILLIMETERS	
	MIN	MAX	MIN	MAX
A	0.740	0.770	18.80	19.55
B	0.250	0.270	6.35	6.85
C	0.145	0.175	3.69	4.44
D	0.015	0.021	0.39	0.53
F	0.040	0.70	1.02	1.77
G	0.100 BSC		2.54 BSC	
H	0.050 BSC		1.27 BSC	
J	0.008	0.015	0.21	0.38
K	0.110	0.130	2.80	3.30
L	0.295	0.305	7.50	7.74
M	0°	10°	0°	10°
S	0.020	0.040	0.51	1.01

Notes

Notes

ON Semiconductor and  are trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer.

PUBLICATION ORDERING INFORMATION

North America Literature Fulfillment:

Literature Distribution Center for ON Semiconductor
P.O. Box 5163, Denver, Colorado 80217 USA
Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada
Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada
Email: ONlit@hibbertco.com

N. American Technical Support: 800-282-9855 Toll Free USA/Canada

EUROPE: LDC for ON Semiconductor – European Support

German Phone: (+1) 303-308-7140 (M–F 2:30pm to 5:00pm Munich Time)
Email: ONlit-german@hibbertco.com
French Phone: (+1) 303-308-7141 (M–F 2:30pm to 5:00pm Toulouse Time)
Email: ONlit-french@hibbertco.com
English Phone: (+1) 303-308-7142 (M–F 1:30pm to 5:00pm UK Time)
Email: ONlit@hibbertco.com

ASIA/PACIFIC: LDC for ON Semiconductor – Asia Support

Phone: 303-675-2121 (Tue–Fri 9:00am to 1:00pm, Hong Kong Time)
Toll Free from Hong Kong 800-4422-3781
Email: ONlit-asia@hibbertco.com

JAPAN: ON Semiconductor, Japan Customer Focus Center
4-32-1 Nishi-Gotanda, Shinagawa-ku, Tokyo, Japan 141-8549

Phone: 81-3-5740-2745
Email: r14525@onsemi.com

Fax Response Line: 303-675-2167
800-344-3810 Toll Free USA/Canada

ON Semiconductor Website: <http://onsemi.com>

For additional information, please contact your local Sales Representative.