

[HOME](#)[ABOUT US](#)[INDUSTRIES](#)[PRODUCTS & APPLICATIONS](#)[NEWS & EVENTS](#)[CONTACT & SUPPORT](#)[Speed, Position  
& Current](#)[Thermal](#)[Pressure,  
Force & Flow](#)[Relays](#)[Switches &  
Equipment Health](#)[Potentiometers  
& Resistors](#)[Safety  
Products](#)[Vehicle Cont  
& Monitoring](#)

## Honeywell Sensing and Control

[Where to buy?](#)[Interactive  
Catalog Home](#)[Product Family  
Information](#)[Specification  
Search](#)[Search  
Help](#)

Representative photograph,  
actual product appearance  
may vary.

- [Dimensions](#)
- [Specifications](#)
- [Engineering  
Drawings On-Line](#)

[Click here for a print friendly version of this datasheet.](#)

## CSNL281-006

**CSN Series closed loop current sensor, measures AC, DC or impulse current, 300 A nominal,  $\pm 750$  amp range, Molex gold pin conn 2000 turn**

### Features

- Current sensing up to 1200 amps
- Measures ac, dc and impulse currents
- Competitive cost/performance ratio
- Rapid response
- High overload capability
- High level of electrical isolation between primary and secondary circuits
- Industrial operating temperature range
- Small size and weight

### Typical Applications

- Variable speed drives
- Overcurrent protection
- Ground fault detectors
- Current feedback control systems
- Robotics
- UPS and telecommunication power supplies
- Welding power supplies
- Automotive - Battery management systems
- Wattmeters

### Description

The CSN Series of closed loop current sensors are based on the principle of the Magnetoresistive or Hall effects, and the null balance or zero magnetic flux method (feedback system). The magnetic flux in the sensor core is constantly controlled at zero. The amount of current required to balance the zero flux is the measure of the primary current flowing through the conductor, multiplied by the ratio of the primary to secondary windings. The closed loop current is the output from the device and presents an impedance that is the primary current reduced by the number of secondary turns at any given time. This current can be expressed as a voltage by passing it through a resistor.

Product Specifications	
Sensor Type	Closed Loop Linear
Sensed Current Type	ac or dc
Sensed Current Range	$\pm 750$ A
Package Style	PCB Attached
Output Type	Current

<b>Maximum Continuous Current</b>	± 400 A
<b>Supply Current</b>	± 22 mA + output
<b>Supply Voltage</b>	± 24.0 Vdc
<b>Offset Current</b>	< ± 0.3 mA
<b>Offset Current Drift</b>	< ± 0.5 mA
<b>Coil Resistance @ 70 °C</b>	25 Ohm
<b>Response Time</b>	< 0.5 μs
<b>Coil Turns</b>	2000
<b>Output Nominal</b>	150 mA
<b>Operating Temperature Range</b>	-40 °C to 85 °C [-40 °F to 185 °F]
<b>Storage Temperature Range</b>	-40 °C to 90 °C [-40 °F to 194 °F]
<b>Minimum Measuring Resistance</b>	20 Ohm
<b>Maximum Measuring Resistance</b>	80 Ohm
<b>Housing Material</b>	Unfilled PBT (UL94-V0)
<b>Mounting</b>	Panel
<b>Pinout Style</b>	Molex (3-way)
<b>Accuracy</b>	± 0.5 %
<b>Availability</b>	Global
<b>Comment</b>	Extended measuring range and gold pin Molex connect
<b>UNSPSC Code</b>	411121
<b>UNSPSC Commodity</b>	411121 Transducers
<b>Series Name</b>	CSN Series

*Due to regional agency approval requirements, some products may not be available in your area.  
Please contact your regional Honeywell office regarding your product of choice.*