

2 and 3-Wire Receptacles, Front Mount, 1/4-18 NPT Threads

- NEMA 1, 3, 4, 6P
- IEC IP67 Protection
- 250 V, 4 A



Housing Style	Female Part Number	Male Part Number	Features	Pinout
FKB ... Typical panel cutout is 14.3 mm.	FKB 2-*/18.25	FSB 2-*/18.25	2x18 AWG, 105°C	Female Male
	FKB 3-*/18.25	FSB 3-*/18.25	3x22 AWG, 105°C	Female
	FKB 3-*/18.25/S690	FSB 3-*/18.25/S690	3x18 AWG 105°C	Female
		FSB 3-*/18.25/S649	3x22 AWG 105°C	Female
	FKB 3-*/18.25/S662	FSB 3-*/18.25/S662	3x18 AWG 105°C	Male
		FSB 3-*/18.25/S881	3x22 AWG 105°C	Male

microfast

* Length in meters. Standard lead length is 0.5 Meters. Consult factory for other lengths.
Standard housing material is nickel plated brass. "FSB ..". "FSBV.." indicates stainless steel housing.
To specify PVC jacketed cable, add "/S717" to the end of the part number.