




SECTION T-T

4805 (1/15)

8

7

6

5

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
—	—	SEE SHEET 1	—	—	—

1

HOUSING MATERIAL: THERMOPLASTIC.

2

CONTACT MATERIAL: COPPER ALLOY

3

FINISH:
MATING AREA: MEETS THE PERFORMANCE REQUIREMENTS OF PRODUCT SPECIFICATION 108–9063; BASED ON TELCORDIA DR–1217–CORE APPLICATIONS IN UNCONTROLLED ENVIRONMENTS.
TIN PLATED POSTS.

4

SOLDER PIN POST RECOMMENDED P.C. BOARD HOLE SIZES ARE 0.94–1.09 [.037–.043]; RECOMMENDED PAD DIA IS 1.52 [.060].

5

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

5

OBSOLETE

5

OBSOLETE

	187.96 [7.400]	74	191.77 [7.550]	201.93 [7.950]	209.55 [8.250]	150	1–5532430–4
	137.16 [5.400]	54	140.97 [5.550]	151.13 [5.950]	158.75 [6.250]	110	1–5532430–0
	73.66 [2.900]	29	77.47 [3.050]	87.63 [3.450]	95.25 [3.750]	60	5532430–5
	48.26 [1.900]	19	52.07 [2.050]	62.23 [2.450]	69.85 [2.750]	40	5532430–3
	35.56 [1.400]	14	39.37 [1.550]	49.53 [1.950]	57.15 [2.250]	30	5532430–2
	E	D	C	B	A	POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

0 PLC
1 PLC
2 PLC
3 PLC
4 PLC
ANGLES

± –
± –
± –
± 0.13 [.005]
± –
± –

MATERIAL

1

2

DWN
J. POLIGNONE
CHK
A. SHARPE
APVD
A. SHARPE

23FEB05
18JUL05
18JUL05

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

SCALE 4:1

SHEET 2 OF 2

REV A1

TE

TE Connectivity

NAME

ASSEMBLY, PIN, VERTICAL, HDI, LEAD–FREE,
2 ROW, WITHOUT GUIDES,
4.83[.190] SOLDER POSTS

SIZE

A1

CAGE CODE

00779

DRAWING NO

5532430

RESTRICTED TO

—

4805 (1/15)