


Molded Shielded Inductors, Axial Leads, High Frequency and Noise Suppression Applications



These inductors have copper winding on magnetic core structure.


FEATURES

- Depending on inductance value core is either iron powder or ferrite
- Shielding gives a 3 % coupling limitation between two inductors
- Material categorization: For definitions of compliance please see www.vishay.com/doc?99912



RoHS
COMPLIANT

DIMENSIONS in millimeters (± 0.5)



STANDARD ELECTRICAL SPECIFICATIONS

MODEL	INDUCTANCE RANGE μH	RATED POWER $P_{70^\circ\text{C}}$ W	LIMITING ELEMENT VOLTAGE V_{RMS}	TOLERANCE (1) $\pm \%$	Q RANGE	I RANGE mA
TRB023	0.1 to 1200	300	500	10	35 to 55	110 to 4300

MECHANICAL SPECIFICATIONS

Coating	Molded epoxy compound
Weight	1.3 g

PACKAGING

Standard: Tape and reel 500 pieces, code R10 (R)
On request: 250 pieces tape in box "ammopack", code A15 (B)

ENVIRONMENTAL SPECIFICATIONS

Operating temperature range	+ 70 °C
Temperature limits	- 55 °C + 125 °C

MARKING

Standard:
Print marked-manufacturer, inductance value, tolerance

ORDERING INFORMATION (Part Number)

T	R	B	0	2	3	4	R	7	K	A	1	5					
MODEL			STYLE			VALUE			TOLERANCE			PACKAGING			SPECIAL		
TRB			023			From 1 μH to 1200 μH 4R7 = 4.7 μH			K: $\pm 10 \%$ On request: G: $\pm 2 \%$ J: $\pm 5 \%$			R10 = Reel 500 pieces On request: A15 = Ammopack 250 pieces			Special code given by Vishay		

PART NUMBER DESCRIPTION (for information only)

TRB	023	4 μH 7	10 %	B		e1
MODEL	STYLE	VALUE	TOLERANCE	PACKAGING	SPECIAL	LEAD (Pb)-FREE



STANDARD VALUES						
INDUCTANCE VALUE μH	TOLERANCE %	Q MIN.	TEST FREQUENCY MHz	RESISTANCE MAX. Ω	SRF MIN. MHz	I MAX. mA
0.10	$\pm 10\%$	40	25	0.008	250	4300
0.12	$\pm 10\%$	40	25	0.010	250	3880
0.15	$\pm 10\%$	40	25	0.025	250	3440
0.18	$\pm 10\%$	40	25	0.030	250	3160
0.22	$\pm 10\%$	40	25	0.036	250	2880
0.27	$\pm 10\%$	40	25	0.045	250	2680
0.33	$\pm 10\%$	35	25	0.065	250	2110
0.39	$\pm 10\%$	35	25	0.075	250	2000
0.47	$\pm 10\%$	35	25	0.10	230	1730
0.56	$\pm 10\%$	35	25	0.13	220	1620
0.68	$\pm 10\%$	35	25	0.20	195	1220
0.82	$\pm 10\%$	35	25	0.26	180	1070
1	$\pm 10\%$	35	25	0.06	145	1210
1.2	$\pm 10\%$	35	7.9	0.08	135	1930
1.5	$\pm 10\%$	35	7.9	0.10	118	1730
1.8	$\pm 10\%$	35	7.9	0.12	110	1580
2.2	$\pm 10\%$	35	7.9	0.14	100	1460
2.7	$\pm 10\%$	35	7.9	0.16	85	1360
3.3	$\pm 10\%$	35	7.9	0.22	75	1160
3.9	$\pm 10\%$	35	7.9	0.25	70	1090
4.7	$\pm 10\%$	35	7.9	0.30	63	1000
5.6	$\pm 10\%$	35	7.9	0.62	58	755
6.8	$\pm 10\%$	35	7.9	0.70	54	655
8.2	$\pm 10\%$	35	7.9	0.82	48	605
10	$\pm 10\%$	35	7.9	0.90	45	575
12	$\pm 10\%$	40	2.5	0.85	40	560
15	$\pm 10\%$	40	2.5	0.72	36	545
18	$\pm 10\%$	40	2.5	0.82	32	605
22	$\pm 10\%$	40	2.5	0.96	28	680
27	$\pm 10\%$	40	2.5	1.1	25	620
33	$\pm 10\%$	40	2.5	1.2	22	600
39	$\pm 10\%$	40	2.5	1.8	20	408
47	$\pm 10\%$	40	2.5	2	18	386
56	$\pm 10\%$	40	2.5	2.2	17	362
68	$\pm 10\%$	40	2.5	2.5	16	348
82	$\pm 10\%$	40	2.5	3.6	11	290
100	$\pm 10\%$	35	2.5	3	10	300
120	$\pm 10\%$	35	0.79	3.5	9	290
150	$\pm 10\%$	40	0.79	4.1	8	270
180	$\pm 10\%$	40	0.79	4.4	6.5	260
220	$\pm 10\%$	45	0.79	4.9	5.2	245
270	$\pm 10\%$	45	0.79	6.4	5	215
330	$\pm 10\%$	40	0.79	7.4	4.8	205
390	$\pm 10\%$	40	0.79	8	4.3	195
470	$\pm 10\%$	55	0.79	12	4	155
560	$\pm 10\%$	50	0.79	13.8	3.5	145
680	$\pm 10\%$	45	0.79	16	3.3	140
820	$\pm 10\%$	40	0.79	16.5	3.1	135
1000	$\pm 10\%$	35	0.79	23	2.9	115
1200	$\pm 10\%$	35	0.25	27	2.5	110



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Material Category Policy

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.