

3-terminal Filters, SMD Array

For signal line

MEA series

Type:	MEA1608L	1608[0603 inch]*
	MEA2010L	2010[0804 inch]
* Dimensions Code JIS[EIA]		

Issue date: November 2011

- All specifications are subject to change without notice.
- Conformity to RoHS Directive: This means that, in conformity with EU Directive 2002/95/EC, lead, cadmium, mercury, hexavalent chromium, and specific bromine-based flame retardants, PBB and PBDE, have not been used, except for exempted applications.

3-terminal Filters, SMD Array For Signal Line

Conformity to RoHS Directive

MEA Series MEA1608L

FEATURES

- 4-line LC filter are built in one chip for high-density circuit design.
- 0.5mm low profile.
- It is effective as a sensitivity suppression technique for mobile phones.
- This product is suitable for the LCD signal lines in mobile phone.

APPLICATIONS

RGB and signal lines of data terminals, computing and communications devices, color liquid crystal displays, printers, DVDs, electronic games, portable audio-visual equipment, etc.

TEMPERATURE RANGES

Operating	-40 to +85°C
Storage(After mount)	-40 to +85°C

PRODUCT IDENTIFICATION


MEA	1608	L	50R0	T	
(1)	(2)	(3)	(4)	(5)	(6)

- (1)Series name (5)Packaging style T:Taping
 (2)Dimensions L×W (6)TDK internal code
 (3)Type name
 (4)Cutoff frequency
 50R0: 50MHz



PACKAGING STYLE AND QUANTITIES

Packaging style	Quantity
Taping	4000 pieces/reel

SHAPES AND DIMENSIONS/CIRCUIT DIAGRAM/RECOMMENDED PC BOARD PATTERN (REFLOW)



Weight: 3.5mg
Dimensions in mm




ELECTRICAL CHARACTERISTICS

Part No.	Cutoff frequency (MHz)typ.	Attenuation 20dB frequency range (MHz)	Rated voltage (V)max.	Rated current (mA)max.
MEA1608L50R0	50	500 to 2000	6.3	100
MEA1608L75R0	75	600 to 2000	6.3	100
MEA1608L101R	100	800 to 2000	6.3	100


TYPICAL ELECTRICAL CHARACTERISTICS

ATTENUATION vs. FREQUENCY CHARACTERISTICS



RECOMMENDED SOLDERING CONDITION

REFLOW SOLDERING



- Conformity to RoHS Directive: This means that, in conformity with EU Directive 2002/95/EC, lead, cadmium, mercury, hexavalent chromium, and specific bromine-based flame retardants, PBB and PBDE, have not been used, except for exempted applications.
- Please contact our Sales office when your application is considered the following:
The device's failure or malfunction may directly endanger human life (e.g. application for automobile/aircraft/medical/nuclear power devices, etc.)

• All specifications are subject to change without notice.

3-terminal Filters, SMD Array For Signal Line

Conformity to RoHS Directive

MEA Series MEA2010L

FEATURES

- This array type MEA2010L consists of 4-line SMD filters in one chip.
- Due to small low-profile size(L2.0×W1.0×T0.7mm), it is possible to correspond to the set of the compact size and high-density mounting.
- This type corresponds to a lead-free soldering method.

APPLICATIONS

Noise suppression for PCs, LCD panels, printers, game machines, cellular phones, DVCs, etc.

TEMPERATURE RANGES

Operating	−40 to +85°C
Storage(After mount)	−40 to +85°C

PRODUCT IDENTIFICATION


MEA	2010	L	101R	T	
(1)	(2)	(3)	(4)	(5)	(6)

- (1)Series name (5)Packaging style T:Taping
 (2)Dimensions L×W (6)TDK internal code
 (3)Type name
 (4)Cutoff frequency
 101R: 100MHz

PACKAGING STYLE AND QUANTITIES

Packaging style	Quantity
Taping	4000 pieces/reel

SHAPES AND DIMENSIONS/CIRCUIT DIAGRAM/RECOMMENDED PC BOARD PATTERN (REFLOW)




ELECTRICAL CHARACTERISTICS

Part No.	Cutoff frequency (MHz)typ.	Attenuation 20dB frequency range (MHz)	Rated voltage (V)max.	Rated current (mA)max.
MEA2010L50R0	50	500 to 2000	10	100
MEA2010L75R0	75	600 to 2000	10	100
MEA2010L101R	100	800 to 2000	10	100


TYPICAL ELECTRICAL CHARACTERISTICS

ATTENUATION vs. FREQUENCY CHARACTERISTICS



RECOMMENDED SOLDERING CONDITION

REFLOW SOLDERING



- Conformity to RoHS Directive: This means that, in conformity with EU Directive 2002/95/EC, lead, cadmium, mercury, hexavalent chromium, and specific bromine-based flame retardants, PBB and PBDE, have not been used, except for exempted applications.

- Please contact our Sales office when your application is considered the following:

The device's failure or malfunction may directly endanger human life (e.g. application for automobile/aircraft/medical/nuclear power devices, etc.)

- All specifications are subject to change without notice.