

| PART NUMBER |          | TAB SIZE                                                 | AWG WIRE RANGE (mm <sup>2</sup> ) | HOUSING COLOR | MAX WIRE INSUL DIA | DIMENSIONS in. |              |              |               |
|-------------|----------|----------------------------------------------------------|-----------------------------------|---------------|--------------------|----------------|--------------|--------------|---------------|
| PREFIX      | PK       |                                                          |                                   |               |                    | A±.03 (.8)     | B±.02 (.5)   | W±.01 (.3)   | X±.03 (.8)    |
| DNFR18-250B | -L<br>-M | .250 X .032<br>(6,3 X 0,8)                               | 22-18<br>(0,5-1,0)                | RED           | .130<br>(3,30)     | .78<br>(19,8)  | .20<br>(5,1) | .36<br>(9,1) | .62<br>(15,7) |
| DNFR14-250B | -L<br>-M | .250 X .032<br>(6,3 X 0,8)                               | 16-14<br>(1,5-2,5)                | BLUE          | .155<br>(3,94)     | .78<br>(19,8)  | .20<br>(5,1) | .36<br>(9,1) | .63<br>(16,0) |
| DNFR18-205B | -L<br>-M | .205 X .032 (5,2 X 0,8)<br>OR<br>.187 X .032 (4,8 X 0,8) | 22-18<br>(0,5-1,0)                | RED           | .130<br>(3,30)     | .78<br>(19,8)  | .20<br>(5,1) | .36<br>(9,1) | .62<br>(15,7) |
| DNFR14-205B | -L<br>-M | .205 X .032 (5,2 X 0,8)<br>OR<br>.187 X .032 (4,8 X 0,8) | 16-14<br>(1,5-2,5)                | BLUE          | .155<br>(3,94)     | .78<br>(19,8)  | .20<br>(5,1) | .36<br>(9,1) | .63<br>(16,0) |
| DNFR18-206B | -L<br>-M | .205 X .020 (5,2 X 0,5)<br>OR<br>.187 X .020 (4,8 X 0,5) | 22-18<br>(0,5-1,0)                | RED           | .130<br>(3,30)     | .78<br>(19,8)  | .20<br>(5,1) | .36<br>(9,1) | .62<br>(15,7) |
| DNFR14-206B | -L<br>-M | .205 X .020 (5,2 X 0,5)<br>OR<br>.187 X .020 (4,8 X 0,5) | 16-14<br>(1,5-2,5)                | BLUE          | .155<br>(3,94)     | .78<br>(19,8)  | .20<br>(5,1) | .36<br>(9,1) | .63<br>(16,0) |




LISTED  
20H3  
E78522



CERTIFIED  
LR31212

## NOTES:

- USED FOR:
  - 600V MAX VOLTAGE RATING
  - 221°F (105°C) MAX INSULATION TEMP. RATING
  - STRANDED COPPER WIRE ONLY
- FIRST INSERTION FORCE - 12 LB. (53N) MAX  
FIRST WITHDRAWAL FORCE - 12 LB. (53N) MAX  
6 LB. (27N) MIN
- INSTALLATION TOOLS:  
A. CT-1525
- WIRE STRIP LENGTH: 9/32 <sup>+1/32</sup><sub>-0</sub> (7.1 <sup>+0.8</sup><sub>-0</sub>)
- MATERIAL USED:  
A. TERMINAL STAMPING: .018 (.46) (THK) TIN PLATED BRASS  
B. HOUSING : NYLON
- PACKAGING QTY:  
A. STD : -L = 50  
B. BULK : -M = 1000
- DIMENSIONS IN BRACKETS ARE IN MILLIMETERS OR mm<sup>2</sup>



**PANDUIT**

CORP.

TINLEY PARK, ILLINOIS

MOLDED NYLON INSULATED RIGHT ANGLE  
FEMALE DISCONNECTS, BUTTED SEAM

07 1/11 SRB CHANGED PACKAGING CODE FROM C=100 TO L=50

REV DATE BY DESCRIPTION

DRAWN BY DAW CHK'D RLS SCALE NONE DRAWING NO. A41329