


Molded Parts
Specification Control Drawing

Part Number : 602A114-X-08
Description : Boot Straight 5 Entry

NOTES

1. All dimensions are in $\frac{\text{inches}}{\text{millimeters}}$
2. Dimensions appearing in table are as follows:
 - a - As Supplied
 - b - After Unrestricted Recovery
3. Coating is optional. As supplied dimensions appearing in table are for uncoated parts. When coating is added, entry diameters will be reduced by .06 max.



PART NUMBER	H		J		P ±10% b	R ±10% b	JO ±10% b	HW ±20% b	JW ±20% b
	Min a	Max b	Min a	Max b					
	602A114-X-08	<u>2.75</u> [69,8]	<u>1.00</u> [25,4]	<u>.85</u> [21,6]					

If this document is printed it becomes uncontrolled.
Check for the latest revision.



Revision : B
Date : 7/18/03


Part Number : 602A114-X-08
Description : Boot Straight 5 Entry

Molded Parts
Specification Control Drawing

Part Number : 602A114-X-08
Description : Boot Straight 5 Entry

COMPATABILITY CHART					
MATERIAL DASH NO.	MATERIAL DESCRIPTION	Mil Spec.	COATING SLASH NO.	COATING S NO.	COATING DESCRIPTION
-152	Polyolefin, Flexible	MIL-I-81765/1A	/42	S-1017	Adhesive

ORDERING INFORMATION



THIS DRAWING IS SUBJECT TO CHANGE WITHOUT NOTICE; CONSULT YOUR
NEAREST FIELD REPRESENTATIVE FOR CURRENT REVISION



Revision : B
Date : 7/18/03

Part Number : 602A114-X-08
Description : Boot Straight 5 Entry