




DRAWING MADE IN THIRD ANGLE PROJECTION

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION , 19
© COPYRIGHT 19 BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED

REVISIONS					
P	F	ZONE	LTR	DESCRIPTION	DATE
✓			Q	RELEASE OF NEW PRODUCT	03/94

DESCRIPTION	MATERIAL	FINISH
GROMMET	FLUOROSILICONE 40/50 BLEND PER MIL-R-25988	COLOR: BLUE
SPLICE ASSEMBLY HOUSING	EPOXY	COLOR: BLACK
CONTACT FEMALE SOCKET	BERYLLIUM COPPER PER QQ-C-533	GOLD PLATE PER MIL-G-45204
CLIP CONTACT RETAINING	BERYLLIUM COPPER PER QQ-C-533 OR STAINLESS STEEL PER QQ-S-766	NONE
SHRINK TUBE	PER MIL-1-23053/8	COLOR TRANSPARENT
CONTACTS △3	PER M39029/1-102	GOLD PLATE PER MIL-G-45204



△6 PART NO. 592584-3 IS MARKED WITH "A" & "B" IN TWO LOCATIONS
EACH .060 MINIMUM HIGH CHARACTERS AT APPROXIMATE AREA SHOWN.

5. AMP PART NO. 592584-1 WAS FORMERLY MATRIX PART NO. MWS16D-1.

△4 MARK WIRE SPLICE BUSSING ARRANGEMENT BOTH ENDS AS SHOWN.

△3 A QUANTITY OF 4 CONTACTS ARE SUPPLIED WITH WIRE SPLICE.

△2 PART NO. 592584-2 IS MARKED WITH CUSTOMER PART NO. 5224212-1
.060 MINIMUM HIGH CHARACTERS AT APPROXIMATE AREA SHOWN.

△1 MARK WIRE SPLICE WITH "AMP", AMP PART NO. AND DATE CODE
.060 MINIMUM HIGH CHARACTERS AT APPROXIMATE AREA SHOWN.

THIS DRAWING IS A CONTROLLED DOCUMENT FOR
AMP INCORPORATED. IT IS SUBJECT TO CHANGE
AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DO NOT SCALE PRINT.
UNLESS OTHERWISE
SPECIFIED DIMENSIONS
ARE IN INCHES.
TOLERANCES ON:
2 PLC DEC ± .02
3 PLC DEC ± .01
ANGLES ± .01

MATERIAL

FINISH

CONTRACT NO

DR N. FRITZ
02/6/94

CHK R. RYAN
03/21/94

APPD R. RYAN
03/21/94

APPD R. RYAN
03/21/94

DSGN APPD

OTHER APPD

AMP | AMP INCORPORATED
Harrisburg, Pa. 17105

NAME

WIRE SPLICE, DOUBLE
SIZE 16 ASSEMBLY TJ

SIZE

FSCM NO

00779

DRAWING NO

592584

SCALE

4 : 1

SHEET 1 OF 1

CUSTOMER DRAWING