





PRODUCT NUMBER	SERIES NAME	PITCH
20020010-CXXXXXXLF	02-350	3.50 mm



2p to 6p with wedge, above 7p
without wedge (including 7p)






N = Number of poles
Dim A = $N \times 3.5$ [.138]
Dim B = $(N-1) \times 3.5$ [.138]


POLES	TOLERANCE
2-6p	± 0.15 [.006]
7-12p	± 0.20 [.008]
13-18p	± 0.25 [.010]
19-24p	± 0.30 [.012]

mat'l. code				surface ASME Y14.5 ✓	tolerance ASME Y14.5	projection MM [INCH]	product family TERMINAL BLOCK
ltr	ecn no	dr	date	tolerances unless otherwise specified			title
F				angles X $\pm 1^\circ$	X ± 0.5 X.X ± 0.3 X.XX ± 0.1	scale	TERMINAL BLOCK PLUGGABLE PLUG, BACK SIDE HOOK
dr	JASON HSU	120909		enr	JASON HSU	120909	dwg no
chr	GARY HSIEH	120909		appd	JOSEPH HSIA	120909	sheet 2 of 5 size
sheet index	revision sheet						20020010 A4
							type CUSTOMER Drawing

PRODUCT NUMBER	SERIES NAME	PITCH
20020010-DXXXXXXLF	02-381	3.81 mm



2p to 6p with wedge, above 7p
without wedge (including 7p)






N = Number of poles
Dim A = $N \times 3.81$ [.150]
Dim B = $(N-1) \times 3.81$ [.150]

POLES	TOLERANCE
2-6p	± 0.15 [.006]
7-12p	± 0.20 [.008]
13-18p	± 0.25 [.010]
19-24p	± 0.30 [.012]



mat'l. code				surface ASME Y14.5 ✓	tolerance ASME Y14.5	projection 	product family TERMINAL BLOCK
ltr	ecn	no	dr	date			title
F							TERMINAL BLOCK
				angles	$X \pm 0.5$	MM [INCH]	PLUGGABLE PLUG, BACK SIDE HOOK
				linear	$X.X \pm 0.3$		
				$X \pm 1^\circ$	$X.XX \pm 0.1$	scale	
			dr	JASON HSU	120909		dwg no
			enr	JASON HSU	120909		sheet 3 of 5 size
			chr	GARY HSIEH	120909		20020010 A4
			appd	JOSEPH HSIA	120909		type
sheet	revision						CUSTOMER Drawing
index	sheet						

PRODUCT NUMBER	SERIES NAME	PITCH
20020010-GXXXXXXLF	02-500	5.00 mm



N = Number of poles
Dim A = $N \times 5.0 [0.197]$
Dim B = $(N-1) \times 5.0 [0.197]$

POLES	TOLERANCE
2-6p	$\pm 0.15 [0.006]$
7-12p	$\pm 0.25 [0.010]$
13-18p	$\pm 0.30 [0.012]$
19-24p	$\pm 0.40 [0.016]$






SECTION P-P

mat'l. code				surface ASME Y14.5	tolerance ASME Y14.5	projection	product family TERMINAL BLOCK
ltr	ecn no	dr	date	tolerances unless otherwise specified		MM [INCH]	title
F				angles	X.±0.5 X.X±0.3 X.XX±0.1		TERMINAL BLOCK PLUGGABLE PLUG, BACK SIDE HOOK
		dr	JASON HSU	120909		scale	dwg no
		enr	JASON HSU	120909			sheet 4 of 5
		chr	GARY HSIEH	120909			20020010
		appd	JOSEPH HSIA	120909			A4
sheet index	revision sheet						type CUSTOMER Drawing




PRODUCT NUMBER	SERIES NAME	PITCH
20020010-HXXXXXXLF	02-508	5.08 mm




N = Number of poles
Dim A = $N \times 5.08$ [.200]
Dim B = $(N-1) \times 5.08$ [.200]

POLES	TOLERANCE
2-6p	± 0.15 [.006]
7-12p	± 0.25 [.010]
13-18p	± 0.30 [.012]
19-24p	± 0.40 [.016]



SECTION P-P



mat'l. code				surface ASME Y14.5 ✓		tolerance ASME Y14.5		projection 		product family TERMINAL BLOCK													
ltr		ecn no		dr		date		tolerances unless otherwise specified				title											
F								angles				linear		MM [INCH]		TERMINAL BLOCK PLUGGABLE PLUG, BACK SIDE HOOK							
								X.±0.5															
								X.X±0.3															
								X°±1°				X.XX±0.1		scale									
								dr		JASON HSU		120909				dwg no				sheet 5 of 5		size	
								enr		JASON HSU		120909				20020010				A4			
								chr		GARY HSIEH		120909											
								appd		JOSEPH HSIA		120909											
sheet index		revision sheet																type		CUSTOMER Drawing			