


## PANELS FOR JUNCTION BOXES



Steel panels are 14 gauge, finished with white polyester powder paint or with a conductive, corrosion-resistant coating. Stainless steel panels are 14 gauge Type 304 and have a commercial #2B finish which is protected on one side with a plastic film. Aluminum panels are 5052-H32 aluminum alloy 0.080-in. (2-mm) thick and protected on one side with a plastic film. Panel mounting hardware is furnished with all enclosures which accept these panels.

### BULLETIN: PNLJ, PNLWM



| Catalog Number | Material         | Panel Size D x E (in.) | Panel Size D x E (mm) | V (in.) | V (mm) |
|----------------|------------------|------------------------|-----------------------|---------|--------|
| A6P4           | Painted steel    | 4.88 x 2.88            | 124 x 73              | 0.31    | 8      |
| A6P4G          | Conductive steel | 4.88 x 2.88            | 124 x 73              | 0.31    | 8      |
| A6P4SS         | Stainless Steel  | 4.88 x 2.88            | 124 x 73              | 0.31    | 8      |
| A6P4AL         | Aluminum         | 4.88 x 2.88            | 124 x 73              | 0.31    | 8      |
| A6P6           | Painted steel    | 4.88 x 4.88            | 124 x 124             | 0.31    | 8      |
| A6P6G          | Conductive steel | 4.88 x 4.88            | 124 x 124             | 0.31    | 8      |
| A6P6SS         | Stainless Steel  | 4.88 x 4.88            | 124 x 124             | 0.31    | 8      |
| A6P6AL         | Aluminum         | 4.88 x 4.88            | 124 x 124             | 0.31    | 8      |
| A8P6           | Painted steel    | 6.75 x 4.88            | 171 x 124             | 0.25    | 6      |
| A8P6G          | Conductive steel | 6.75 x 4.88            | 171 x 124             | 0.25    | 6      |
| A8P6SS         | Stainless Steel  | 6.75 x 4.88            | 171 x 124             | 0.25    | 6      |
| A8P6AL         | Aluminum         | 6.75 x 4.88            | 171 x 124             | 0.25    | 6      |
| A8P8           | Painted steel    | 6.75 x 6.88            | 171 x 175             | 0.25    | 6      |
| A8P8AL         | Aluminum         | 6.75 x 6.88            | 171 x 175             | 0.25    | 6      |
| A10P8          | Painted steel    | 8.75 x 6.88            | 222 x 175             | 0.25    | 6      |
| A10P8G         | Conductive steel | 8.75 x 6.88            | 222 x 175             | 0.25    | 6      |
| A10P8SS        | Stainless Steel  | 8.75 x 6.88            | 222 x 175             | 0.25    | 6      |
| A10P8AL        | Aluminum         | 8.75 x 6.88            | 222 x 175             | 0.25    | 6      |
| A10P10         | Painted steel    | 8.75 x 8.88            | 222 x 226             | 0.25    | 6      |
| A10P10G        | Conductive steel | 8.75 x 8.88            | 222 x 226             | 0.25    | 6      |
| A10P10AL       | Aluminum         | 8.75 x 8.88            | 222 x 226             | 0.25    | 6      |
| A12P6          | Painted steel    | 10.75 x 4.88           | 273 x 124             | 0.25    | 6      |
| A12P6G         | Conductive steel | 10.75 x 4.88           | 273 x 124             | 0.25    | 6      |
| A12P10         | Painted steel    | 10.75 x 8.88           | 273 x 226             | 0.25    | 6      |
| A12P10G        | Conductive steel | 10.75 x 8.88           | 273 x 226             | 0.25    | 6      |
| A12P10SS       | Stainless Steel  | 10.75 x 8.88           | 273 x 226             | 0.25    | 6      |
| A12P10AL       | Aluminum         | 10.75 x 8.88           | 273 x 226             | 0.25    | 6      |
| A12P12         | Painted steel    | 10.75 x 10.88          | 273 x 276             | 0.25    | 6      |
| A12P12G        | Conductive steel | 10.75 x 10.88          | 273 x 276             | 0.25    | 6      |
| A12P12SS       | Stainless Steel  | 10.75 x 10.88          | 273 x 276             | 0.25    | 6      |
| A14P8          | Painted steel    | 12.75 x 6.88           | 324 x 175             | 0.25    | 6      |
| A14P8G         | Conductive steel | 12.75 x 6.88           | 324 x 175             | 0.25    | 6      |
| A14P12         | Painted steel    | 12.75 x 10.88          | 324 x 276             | 0.25    | 6      |
| A14P12G        | Conductive steel | 12.75 x 10.88          | 324 x 276             | 0.25    | 6      |
| A14P12SS       | Stainless Steel  | 12.75 x 10.88          | 324 x 276             | 0.25    | 6      |
| A14P12AL       | Aluminum         | 12.75 x 10.88          | 324 x 276             | 0.25    | 6      |
| A16P10         | Painted steel    | 14.75 x 8.88           | 375 x 226             | 0.25    | 6      |
| A16P10G        | Conductive steel | 14.75 x 8.88           | 375 x 226             | 0.25    | 6      |
| A16P14         | Painted steel    | 14.75 x 12.88          | 375 x 327             | 0.25    | 6      |
| A16P14G        | Conductive steel | 14.75 x 12.88          | 375 x 327             | 0.25    | 6      |
| A16P14SS       | Stainless Steel  | 14.75 x 12.88          | 375 x 327             | 0.25    | 6      |
| A16P14AL       | Aluminum         | 14.75 x 12.88          | 375 x 327             | 0.25    | 6      |
| A18P16         | Painted steel    | 16.75 x 14.88          | 425 x 378             | 0.25    | 6      |
| A18P16G        | Conductive steel | 16.75 x 14.88          | 425 x 378             | 0.25    | 6      |
| A18P16SS       | Stainless Steel  | 16.75 x 14.88          | 425 x 378             | 0.25    | 6      |
| A18P16AL       | Aluminum         | 16.75 x 14.88          | 425 x 378             | 0.25    | 6      |