

SPI-6631M

Features

- Power supply voltages, V_{BB} : 13 V to 33 V
- Signal power supply configuration
- Output current I_{out} : 3 A (max)... repetitive current (normal-operation current)
- Built-in current recirculation diode
- Built-in UVLO, TSD and OCP protection
- Built-in dead time function that prevents through current upon phase switching
- Built-in error sense flag output
- HSOP16-pin package

Absolute Maximum Ratings

Parameter	Symbol	Ratings	Unit	Conditions
Main Supply Voltage	V_{BB}	35	V	
MOSFET Output Breakdown Voltage	V_{DSS}	35	V	DutyCycle=100%*
Output Current	I_{out}	± 3	A	
Input Voltage	V_{IN}	-0.3 to 6.5	V	
S Terminal Voltage	V_{SEN}	-2 to 2	V	
Alarm Terminal Voltage	V_{ALARM}	6.5	V	
Alarm Input Current	I_{ALARM}	1	mA	
Power Dissipation	P_D	2.6	W	When using a Sanken evaluation board
Junction Temperature	T_J	150	$^{\circ}C$	
Storage Temperature	T_{STG}	-30 to 150	$^{\circ}C$	
Operating Ambient Temperature	T_A	-20 to 85	$^{\circ}C$	

*: Output current value may be limited, depending on the duty ratio, ambient temperature, and heating conditions. Do not exceed the rated current or maximum junction temperature ($T_J = 150^{\circ}C$).

Electrical Characteristics

($T_A=25^{\circ}C$, $V_{BB}=24V$, unless otherwise specified)

Parameter	Symbol	Ratings			Unit	Conditions
		min.	typ.	max.		
Main Supply Voltage	V_{BB}	13	-	33	V	In operation
Main Supply Current	I_{BB}	-	-	23	mA	
Maximum Clock Pulse Width	t_w	-	-	3	μs	
Input Voltage	V_{IL}	-	-	0.8	V	
	V_{IH}	2.0	-	-	V	
Input Current	I_{IL}	-	± 8	-	μA	$V_{IN(0)}$, $V_{IN}=0.8V$
	I_{IH}	-	± 20	-	μA	$V_{IN(1)}$, $V_{IN}=2.0V$
Crossover Dead Time	T_{delay}	100	500	1200	ns	
VB Terminal Breakdown Voltage	V_B	-	$V_{BB}+5$	-	V	Breakdown voltage between VB and GND
VB-OUT Breakdown Voltage	V_{B-OUT}	-	5	-	V	
VB Terminal Current	I_B	-	-	3	mA	$V_{B-OUT}=5V$
Output Leakage Current	I_{DSS}	-	-	800	μA	$V_{OUT}=V_{BB}=35V$
		-800	-	-	μA	$V_{OUT}=0V$
MOSFET ON Resistance	$R_{DS(ON)}$	-	0.4	0.7	Ω	$I_{OUT}=-1A$, Between V_{BB} and OUT $I_{OUT}=1A$, Between OUT and S
MOSFET Diode Forward Voltage	V_{SD}	-	-	2.2	V	$I_{SD}=1A$
Overcurrent Sense Current	I_{OCP}	7	-	-	A	Short between Out and Out
Overcurrent Protection Blank Time	t_{blank}	0.7	1.2	4	μs	
Overcurrent Protection Delay Time	t_{ocp}	0.5	1	2.2	ms	
Thermal Protection Operation Temperature	T_J	-	170	-	$^{\circ}C$	
Thermal Protection Hysteresis	ΔT_J	-	15	-	$^{\circ}C$	
Low Voltage Protection Operation Voltage	UVLO	4.0	4.5	5.0	V	V_{BB} voltage
Low Voltage Protection Hysteresis	$\Delta UVLO$	0.4	0.45	0.5	V	
Alarm Output Voltage	V_{ALARM}	-	-	0.5	V	$I=1mA$

