





(B) SEE NOTE 5




(B) SEE NOTE 4

NOTES:


1. MATERIAL: SEE TABLE
2. FINISHES: SEE TABLE
3. MATES WITH: RIBBON CABLE
(B) 4. END CAP MOUNT SCREW TORQUE: 0.5 N-m (4.4 lbf-in) MINIMUM
0.6 N-m (5.3 lbf-in) MAXIMUM
(B) 5. TERMINAL BLOCK SCREW TORQUE: 0.8 N-m (7.1 lbf-in)
6. 39170-1050 IS ROHS COMPLIANT, ALL OTHERS NOT REQUIRED.

3	2	DIN RAIL ADAPTOR UNIT	THERMOPLASTIC	BLACK
2	1	RIBBON CABLE TO 5.08 FIXED, PC BOARD ASSY.	-	-
1	1	5.08 FIXED DUAL LEVEL BTS	SEE SD-39880-006	BLACK
ITEM	QTY.	DESCRIPTION	MATERIAL	FINISH



16 POSITION SHOWN

NO. OF CIRCUITS	DIM. "A"	MATERIAL NUMBER
14	50.8 [2.00]	39170-1014
16	53.3 [2.10]	39170-1016
20	61.0 [2.40]	39170-1020
26	76.2 [3.00]	39170-1026
34	95.0 [3.74]	39170-1034
40	111.5 [4.39]	39170-1040
50	135.6 [5.34]	39170-1050



TYPICAL SCHEMATIC
(16 POSITION SHOWN)

ADD SCREW TORQUE EC NO: ETC2007-0331 DRWN:CLYORK 2007/03/12 CHKD:JMACNEIL 2007/03/14 APPR:JMACNEIL 2007/03/15				DESCRIPTION REV	QUALITY SYMBOLS ▽=0 ◻=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN		SCALE 1:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION			
		mm	INCH			DRAWN BY C. YORK		DATE 2004/11/10		TITLE DIN RAIL INTERFACE MODULE, RIBBON CABLE TO 5.08MM DUAL LEV. FIXED MOLEX INCORPORATED					
4 PLACES		± ---	± ---			CHECKED BY R. STONE		DATE 2004/11/16							
3 PLACES		± ---	± .005												
2 PLACES		± 0.13	± .01												
1 PLACE		± 0.3	± ---												
ANGULAR ± 2 °						APPROVED BY G. ROBERTSON		DATE 2004/11/16		MOLEX INCORPORATED					
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS						MATERIAL NO.		DOCUMENT NO.						SHEET NO.	
						SEE CHART		SD-39170-005						1 OF 1	
SIZE B						THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									