



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AF	50		H1	REVISED PER ECO-13-006421	12APR13	JR	PD

SUGGESTED MATING TAB



- MATL: 1/2H BRASS OR NICKEL PL STEEL.
 - NO BURRS PERMISSIBLE AT HOLE.
 - MUST BE FLAT WITHIN 0.076 [.003] OVER THIS LENGTH.
 - TIN PLATING IS REQUIRED ON BRASS WHEN TERMINAL TEMP. IS OVER 225°F, 105° C
 - HOLE MUST BE SYMMETRICAL ABOUT TAB Q̄ WITHIN 0.076 [.003]
- * TO BE USED ONLY WHEN SHOULDER IS ELIMINATED.



- CONTINUOUS STRIP ON REELS.
- PREPRODUCTION - FASR REQUIRED

PRE-TIN PL.	1.52-2.54 [.060-.100] DIA	[#22-#18] AWG	△ 63933-6
TIN PLATE	1.52-2.54 [.060-.100] DIA	[#22-#18] AWG	63933-2
-	1.52-2.54 [.060-.100] DIA	[#22-#18] AWG	63933-1
FINISH	INSULATION RANGE	WIRE SIZE	PART NO.
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 9/4/96 CHK MS FEHER 9/4/96 APVD J GILLISPIE 9/4/96	TE Connectivity
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	PRODUCT SPEC	
	0 PLC ± - 1 PLC ± - 2 PLC ± 0.25 [.010] 3 PLC ± - 4 PLC ± - ANGLES ± -	APPLICATION SPEC	RECEPTACLE, POSITIVE LOCK, 6.35 [.250] SERIES
	FINISH SEE TABLE	114-2061	
MATERIAL BRASS		WEIGHT -	SIZE A2 CAGE CODE 00779 DRAWING NO C-63933 RESTRICTED TO -
CUSTOMER DRAWING		SCALE 5:1	SHEET 1 OF 1 REV H1