
HA17393/A Series

Dual Comparators

HITACHI

ADE-204-066A (Z)

Rev. 1

Mar. 2001

Description

The HA17393A and HA17393 series products are comparators designed for general purpose, especially for power control systems.

These ICs operate from a single power-supply voltage over a wide range of voltages, and feature a reduced power-supply current since the supply current is independent of the supply voltage.

These comparators have the merit which ground is included in the common-mode input voltage range at a single-voltage power supply operation. These products have a wide range of applications, including limit comparators, simple A/D converters, pulse/square-wave/time delay generators, wide range VCO circuits, MOS clock timers, multivibrators, and high-voltage logic gates.


Features

- Wide supply voltage: 2 to 36 V
- Very low supply current: 0.8 mA
- Small input bias: 25 nA
- Small input offset current: 3 nA
- Small input offset voltage: 2 mV
- Common mode input voltage range including ground.
- Small output saturation voltage: 1 mV (5 μ A)
70 mV (1 mA)
- Output voltage is compatible with CMOS logic system.

HA17393/A Series

Features only for “A” series


- Low electro-magnetic susceptibility




Ordering Information

Type No.	Application	Package
HA17393APS	Industrial use	DP-8B
HA17393ARP	Commercial use	FP-8DC
HA17393AFP		FP-8D
HA17393	Commercial use	DP-8B
HA17393F		FP-8D

Pin Arrangement



Circuit Schematic (1/2)



Absolute Maximum Ratings (Ta = 25°C)

Item	Symbol	Ratings					Unit
		17393APS	17393AFP	17393ARP	17393	17393F	
Power supply voltage	V _{CC}	36	36	36	36	36	V
Differential input voltage	V _{in} (diff)	V _{CC}	V _{CC}	V _{CC}	V _{CC}	V _{CC}	V
Input voltage	V _{in}	−0.3 to +V _{CC}	−0.3 to +V _{CC}	−0.3 to +V _{CC}	−0.3 to +V _{CC}	−0.3 to +V _{CC}	V
Output short current	I _{os} *3	constant	constant	constant	constant	constant	
Allowable power dissipation	P _T	570 *1	385 *2	385 *2	570 *1	385 *2	mW
Operating temperature	Topr	−40 to +85	−40 to +85	−40 to +85	−20 to +75	−20 to +75	°C
Storage temperature	Tstg	−55 to +125	−55 to +125	−55 to +125	−55 to +125	−55 to +125	°C

- Notes:
- 1. These are the allowable values up to Ta = 55°C. Derate by 8.3mW/°C above that temperature.
 - 2. These are the allowable values up to Ta = 25°C mounting in air.
When it is mounted on glass epoxy board of 40 mm × 40 mm × 1.5 mmt with 30% wiring density, the allowable value is 570 mW up to Ta = 45°C. If Ta > 45°C, derate by 7.14 mW/°C.
 - 3. Short circuit between the output and V_{CC} will be a cause to destroy the circuit. The maximum output current is about 20 mA for any supply voltage.

Electrical Characteristics ($V_{CC} = 5\text{ V}$, $T_a = 25^\circ\text{C}$)

Item	Symbol	Min	Typ	Max	Unit	Test condition
Input offset voltage ^{*1}	V_{IO}	—	2.0	5.0	mV	
Input bias current ^{*2}	I_{IB}	—	25	250	nA	$I_{IN(+)} \text{ or } I_{IN(-)}$
Input offset current	I_{IO}	—	3	50	nA	$ I_{IN(+)} - I_{IN(-)} $
Common mode input voltage ^{*3}	V_{CM+}	3.5	—	—	V	
	V_{CM-}	—	—	0	V	
Supply current	I_{CC}	—	0.8	2.0	mA	All comparators: $R_L = \infty$, All channels on
Voltage gain	A_V	—	200	—	V/mV	$V_{CC} = 15\text{V}$, $R_L \geq 15\text{k}\Omega$
Response time ^{*4}	t_R	—	1.3	—	μs	$V_{RL} = 5\text{V}$, $R_L = 5.1\text{k}\Omega$
Large signal response time	t_{RI}	—	300	—	ns	$V_{IN} = \text{TTL Threshold width}$, $V_{REF} = 1.4\text{V}$
Out put sink current	I_{osink}	6	16	—	mA	$V_{IN(-)} \geq 1\text{V}$, $V_{IN(+)} = 0$, $V_O \leq 1.5\text{V}$
Output saturation voltage	$V_O(\text{sat})$	—	—	400	mA	$V_{IN(-)} \geq 1\text{V}$, $V_{IN(+)} = 0$, $I_{osink} = 4\text{mA}$
Output leak current	I_{LO}	—	0.1	—	nA	$V_{IN(-)} = 0$, $V_{IN(+)} \geq 1\text{V}$, $V_O = 5\text{V}$

Notes: 1. $V_{REF} = 1.4\text{ V}$ and $R_S = 50\ \Omega$, when $V_O = 1.4\text{ V}$ at output switching point.


2. Under linear operation.

3. Common mode input voltage or each one of the input signal should not be less than -0.3 V .


4. This is a value to 100 mV input step voltage with 5 mV over drive.

Characteristic Curves


Supply Current vs. Ambient Temperature




Output Sink Current vs. Ambient Temperature




Output Sink Current vs. Output Voltage




Output Saturation Voltage vs. Ambient Temperature




Voltage Gain vs. Ambient Temperature




Input Offset Voltage vs. Ambient Temperature





Input Bias Current vs. Ambient Temperature





Response Time vs. Ambient Temperature






Hitachi Code	DP-8B
JEDEC	Conforms
EIAJ	Conforms
Mass (reference value)	0.51 g

Technical drawing of a square plate. The overall width is 5.25 Max, with a dimension of 4.85 shown for the top section. The overall height is 4.4. The plate has a central square hole with a diameter of 1. The top edge has a series of small rectangular features, and the bottom edge has a series of small rectangular features. The distance from the top edge to the center of the hole is 8, and the distance from the center of the hole to the bottom edge is 5.



Hitachi Code	FP-8D
JEDEC	—
EIAJ	Conforms
Mass (reference value)	0.10 g

Unit: mm



*Dimension including the plating thickness
Base material dimension

Hitachi Code	FP-8DC
JEDEC	Conforms
EIAJ	—
Mass (reference value)	0.085 g

Cautions

1. Hitachi neither warrants nor grants licenses of any rights of Hitachi’s or any third party’s patent, copyright, trademark, or other intellectual property rights for information contained in this document. Hitachi bears no responsibility for problems that may arise with third party’s rights, including intellectual property rights, in connection with use of the information contained in this document.

2. Products and product specifications may be subject to change without notice. Confirm that you have received the latest product standards or specifications before final design, purchase or use.

3. Hitachi makes every attempt to ensure that its products are of high quality and reliability. However, contact Hitachi’s sales office before using the product in an application that demands especially high quality and reliability or where its failure or malfunction may directly threaten human life or cause risk of bodily injury, such as aerospace, aeronautics, nuclear power, combustion control, transportation, traffic, safety equipment or medical equipment for life support.

4. Design your application so that the product is used within the ranges guaranteed by Hitachi particularly for maximum rating, operating supply voltage range, heat radiation characteristics, installation conditions and other characteristics. Hitachi bears no responsibility for failure or damage when used beyond the guaranteed ranges. Even within the guaranteed ranges, consider normally foreseeable failure rates or failure modes in semiconductor devices and employ systemic measures such as fail-safes, so that the equipment incorporating Hitachi product does not cause bodily injury, fire or other consequential damage due to operation of the Hitachi product.

5. This product is not designed to be radiation resistant.

6. No one is permitted to reproduce or duplicate, in any form, the whole or part of this document without written approval from Hitachi.

7. Contact Hitachi’s sales office for any questions regarding this document or Hitachi semiconductor products.

HITACHI

Hitachi, Ltd.

Semiconductor & Integrated Circuits.
Nippon Bldg., 2-6-2, Ohte-machi, Chiyoda-ku, Tokyo 100-0004, Japan
Tel: Tokyo (03) 3270-2111 Fax: (03) 3270-5109

URL	NorthAmerica	:	http://semiconductor.hitachi.com/
	Europe	:	http://www.hitachi-eu.com/hel/ecg
	Asia	:	http://sicapac.hitachi-asia.com
	Japan	:	http://www.hitachi.co.jp/Sicd/idx.htm

For further information write to:

Hitachi Semiconductor (America) Inc. 179 East Tasman Drive, San Jose, CA 95134 Tel: <1> (408) 433-1990 Fax: <1> (408) 433-0223	Hitachi Europe Ltd. Electronic Components Group. Whitebrook Park Lower Cookham Road Maidenhead Berkshire SL6 8YA, United Kingdom Tel: <44> (1628) 585000 Fax: <44> (1628) 585200 Hitachi Europe GmbH Electronic Components Group Dornacher Straße 3 D-85622 Feldkirchen, Munich Germany Tel: <49> (89) 9 9180-0 Fax: <49> (89) 9 29 30 00	Hitachi Asia Ltd. Hitachi Tower 16 Collyer Quay #20-00, Singapore 049318 Tel: <65>-538-6533/538-8577 Fax: <65>-538-6933/538-3877 URL : http://www.hitachi.com.sg Hitachi Asia Ltd. (Taipei Branch Office) 4/F, No. 167, Tun Hwa North Road, Hung-Kuo Building, Taipei (105), Taiwan Tel: <886>-(2)-2718-3666 Fax : <886>-(2)-2718-8180 Telex : 23222 HAS-TP URL : http://www.hitachi.com.tw	Hitachi Asia (Hong Kong) Ltd. Group III (Electronic Components) 7/F., North Tower, World Finance Centre, Harbour City, Canton Road Tsim Sha Tsui, Kowloon, Hong Kong Tel : <852>-(2)-735-9218 Fax : <852>-(2)-730-0281 URL : http://semiconductor.hitachi.com.hk
--	---	--	---

Copyright © Hitachi, Ltd., 2001. All rights reserved. Printed in Japan.

Colophon 3.0