

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0757576231

Status:

Active

Overview:

MX150™ Unshrouded Header

Description:

MX150 Dual Row Header, Vertical, 6 Circuits, 1.25µm Nickel (Ni) Overall, 2.50µm Minimum Select Matte Tin (Sn) Plating on Tail, 0.05µm Minimum Select Gold (Au) Contact Area, 27.77mm Mating Pin Length, 3.05mm

Documents:

3D Model

Drawing (PDF)

Product Specification PS-75757-000 (PDF)

Product Specification PS-75757-000-001 (PDF)

Packaging Specification PK-36518-340 (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	PCB Headers
Series	75757
3D Viewer	Yes
Application	Power, Wire-to-Board
CURRENT-MAX-NUMERIC	17.0
Overview	MX150™ Unshrouded Header
PITCH-MATING-NUMERIC	3.50
Product Name	MX150
UPC	883906570620
Physical	
Breakaway	No
Circuits (Loaded)	6
Circuits (maximum)	6
Color - Resin	Black
Durability (mating cycles max)	25
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	2.502/g
Number of Rows	2
Orientation	Vertical
PC Tail Length	3.05mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.57mm
Packaging Type	Tube
Pitch - Mating Interface	3.50mm
Pitch - Termination Interface	3.50mm
Plating min - Mating	0.051µm
Polarized to Mating Part	No
Polarized to PCB	No
Shrouded	No
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-40° to +125°C
Termination Interface: Style	Through Hole

Electrical



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per - ED/71/2019 (16 July 2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

75757 Series

Mates With

33472 Dual Row MX150 Receptacles

Current - Maximum per Contact	17.0A
Voltage - Maximum	500V DC

Solder Process Data

Duration at Max. Process Temperature (seconds)	005
Lead-freeProcess Capability	WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	245

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-36518-340
Product Specification	PS-75757-000, PS-75757-000-001
Sales Drawing	SD-75757-003-001

This document was generated on 08/21/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION