


THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	2006
© COPYRIGHT 2006	BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.	

POS. PER ROW	L ±0.5	ORDER - NO. BESTELL - NR.	
1	2.54	9-1 740 617-9	3
24	60.96	2-1 740 617-4	
25	63.50		3

PART 9-1740617-9


3 CONDITION OF DELIVERY
LIEFERZUSTAND

1:1


PART 9-1740617-9



1:1

1 MIN. 3 µm TIN OVER 1.27 µm NICKEL
TIPS UNPLATEDMIN. 3 µm ZINN ÜBER 1.27 µm NICKEL
STIFTSPITZEN BLANK2 60 PCS. WITH ANTISTATIC BAG IN
CARDBOARD BOX 185x140x5760 STÜCK MIT ANTISTATISCHER BEUTEL
IN KARTON 185x140x573 DELIVERED AS STICK WITH 25 POSITIONS PER ROW
WIRD ALS 25-POLIGER STREIFEN GELIEFERT

1	CONTACT PIN KONTAKTSTIFT	Cu Sn	2
COLOUR, GREEN	PINHOUSING STIFTGEHAEUSE	PBT GV	1
REMARK	DESCRIPTION BEZEICHNUNG	MATERIAL	ITEM LFD. NR.

PC BOARD LAYOUT
LEITERPLATTENANSCHLUSSBILD
2:1

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN G. ACKERMANN 05DEC2005	tyco Electronics		tyco Electronics AMP GmbH D - 67346 Speyer	
DIMENSIONS: mm		CHK M. SCHAARSCHMIDT 05DEC2005			NAME AMPMODU II SOLDER STRAP LOETBRUECKE	
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD G. FELDMEIER	PRODUCT SPEC		SIZE A3	
	0 PLC ±0.2 1 PLC ±0.2 2 PLC ±0.2 3 PLC ± 4 PLC ± ANGLES ±2°	APPLICATION SPEC	-		CAGE CODE 00779	
MATERIAL	FINISH	WEIGHT	-		DRAWING NO C=1740617	
CUSTOMER DRAWING		SCALE 5:1		SHEET 1 OF 1		REV B3